

RECORD ARKANSAS flat files

Type 9010

LAPPORT
SCHLEIFTECHNIK

Application:

For machining of cutting tools, knives, instruments, engraving and clock-making tools, and similar

Execution:

- For use with oil or petroleum
- Synthetic honing stones, manufactured according to a special ceramic process

Delivery:

In cardboard box



Art. no.	69442 020
Brand	LAPPORT
Manufacturer Part Number	100407
Length	100 mm
Surface structure	Very fine
Number of pieces per packet	6 PCS
Binding	Ceramically bound
Width	8 mm
Thickness	4 mm
Form	Flat
Suitable for finishing	1 - very suitable
Suitable for main machining	3 - less suitable
Suitable for surface inspection	1 - very suitable
Suitable for surface care	1 - very suitable
Suitable for material rubber	3 - less suitable
Suitable for material cast iron	3 - less suitable
Suitable for material HSS	1 - very suitable
Suitable for material carbide	3 - less suitable
Suitable for material ceramic	3 - less suitable
Suitable for material plastics	3 - less suitable
Suitable for material non-ferrous metals	3 - less suitable
Suitable for material steel (hardened)	1 - very suitable
Suitable for material steel (unhardened)	2 - suitable
Suitable for material tool steel	2 - suitable
ISO	525
Length x width	100 x 8 mm
Length x width x thickness	100 x 8 x 4 mm
Type description	RECORD-ARKANSAS
Material of abrasive medium	Fused aluminium oxide
Gross Weight	0.008 kg
Product Group	6HL