

SHP-TS Super SHP-TS 250W E40 SLV 0020713



Product features

- A range of tubular High Pressure Sodium lamps with exceptional starting reliability throughout lamp life and superior system efficiency



PRODUCT OVERVIEW

Product name	SHP-TS 250W E40 SLV
Technology	HID
Watt (Rated) (W)	260
Type	SHP-TS
Cap/Base	E40
Lamp finish	Clear
Fixture rating	Open
General application	Logistics & Industry
ETIM Class	EC000821
E-number FI	4845512
E-number SE	8358015
E-number Norway	3825259
Luminous flux (lm)	32500
Colour temperature (K)	2050
CRI (Ra)	20
Colour Variation Initial (SDCM)	N/A
Photobiological Risk Group	Not applicable
Wattage (W)	260
Product Voltage (V)	100
Dimmable	No
Dimming method	Mains: leading / trailing edge
Average life (Nominal) (h)	32000
Product EAN number	5410288207131

DATA TABLE

General data

Product name	SHP-TS 250W E40 SLV
Technology	HID
Watt (Rated) (W)	260
Type	SHP-TS
Cap/Base	E40
Lamp finish	Clear
Fixture rating	Open
General application	Logistics & Industry

SHP-TS Super

SHP-TS 250W E40 SLV
0020713

ETIM Class	EC000821
E-number FI	4845512
E-number SE	8358015
E-number Norway	3825259

Optical data

Luminous flux (lm)	32500
Luminous flux (Rated) (lm)	32500
Ambient temperature for maximum luminous flux (°C)	25
Colour temperature (K)	2050
CRI (Ra)	20
Colour Variation Initial (SDCM)	N/A
Adjustable chromaticity	N
Photobiological Risk Group	Not applicable
Rated lumen maint. factor (%) at 4000 h 50Hz	96
Rated lumen maint. factor (%) at 6000 h 50Hz	94
Rated lumen maint. factor (%) at 8000 h 50Hz	93
Rated lumen maint. factor (%) at 12000 h 50Hz	91
Rated lumen maint. factor (%) at 16000 h 50Hz	90
Rated lumen maint. factor (%) at 20000 h 50Hz	89

Electrical data

Wattage (W)	260
Current (A)	2.95
Product Voltage (V)	100
Control gear required	Yes
Transformer required	No
Dimmable	No
Dimming method	Mains: leading / trailing edge
Lamp Energy Label (class)	E
kWh per 1000 hours burning time	281

Lifetime data

Average life (Nominal) (h)	32000
Average life (Rated) (h)	32000
Life T90	16000
Rated survival factor (%) at 2000 h 50Hz	100
Rated survival factor (%) at 4000 h 50Hz	100
Rated survival factor (%) at 6000 h 50Hz	99
Rated survival factor (%) at 8000 h 50Hz	99
Rated survival factor (%) at 12000 h 50Hz	96
Rated survival factor (%) at 16000 h 50Hz	90

SHP-TS Super SHP-TS 250W E40 SLV 0020713

Rated survival factor (%) at 20000 h
50Hz 81

Physical data

Nominal Product Length (mm)	250
Nominal Product Diameter (mm)	46
Max. Lamp Diameter (mm) - D	48
Weight (kg)	0.178


Packaging

Single packaging type	Carton
Product EAN number	5410288207131
Packaging single length / height (cm)	30.5
Packaging single width (cm)	5.0
Packaging single depth (cm)	5.0
DUN14 (outer)	15410288207138
Units per outer package	12
Packaging outer length / height (cm)	28.0
Packaging outer width (cm)	23.0
Packaging outer depth (cm)	33.0


Safety data

Lamp mercury content (mg)	21.60
Breakage cleaning instructions	Applicable
Recommendation for disposal at end of life	Applicable
Special purpose lamp	No
Suitable for household illumination	No

PHOTOMETRY




TECHNICAL DRAWINGS



SYLVANIA

SHP-TS Super
SHP-TS 250W E40 SLV
0020713



260
kWh/1000h




2019/2015

SYLVANIA

SHP-TS Super
SHP-TS 250W E40 SLV
0020713



0020713



260
kWh/1000h



2019/2015