

Fixed centring point

With full point



Application:

For centring and supporting long and narrow workpieces on lathes and grinding machines.

Execution:

- Tip angle 60°.
- Taper hardened and precision-ground.
- Carbide-tipped.
- Concentricity tolerance on cemented carbide $\leq 0.8 \mu\text{m}$.
- Precision machining to roughing.

Advantage:

- Wear-resistant carbide tip.

Delivery:

1x centring point MK 1.



Art. no.	22112 040
Brand	BRUCKNER
Manufacturer Part Number	2804H
Morse taper size	MK 4
Diameter	14 mm
Programming size	57.5 mm
Concentricity tolerance	0.008 mm
DIN	806
Gross Weight	0.790 kg
Product Group	2AA