

angular milling cutter, 90°, with thread
for indexable milling inserts LN.X 1006..

ATORN®

Application

4 flutes per indexable milling insert and special chip breaker geometry for profitability and high cutting rates when milling faces, milling corners, trimming and milling grooves.

Version

- wear-proof, nickel-plated design
- with internal cooling

Advantage

- 4 cutting edges on double-sided indexable insert
- special chip breaker geometry enables low power consumption
- large panel thickness



Art. No.	16016 316
Cutting edge diameter	32 mm
Clearance length	43 mm
Thread dimension	M16
max. ap	10 mm
Number of cutting edges	4 PCS

EAN-Code

4050293539875