

Indexable insert countersink, single tooth cutter

for universal use up to 1300 N/mm² with CC..06 and CC..09..

ATORN[®]

Application

180° countersinks with CC.. indexable inserts in the diameter range from 10.00–33.00 mm, in the material groups steel, stainless steel, non-ferrous metals, cast materials and special alloys for use in single part and series production.



Version

- backing material made from high-grade steel with clamping surface in line with DIN 1835B

Advantage

- precisely fitting inserts ensure optimum machining results even under difficult conditions
- universal use in all material groups
- cost-efficient tool in comparison with mono-block solutions

Art. No.	11240 510
Number of cutting edges	1 PCS
Tool holding device	HB parallel shank
Cutting edge diameter	21 mm
Cantilever length	42 mm
Length	95 mm
Min. pilot hole diameter	5 mm
Shaft diameter	16 mm
Suitable for indexable inserts	CC..09

EAN-Code

4050293112276