Product Safety Data Sheet

1. Product And Company Identification

Product:	Aristowax Wood Silk - 250ml		
Marketing Company	Aristowax Products of Norwich Green Lane House Green Lane North Thorpe End Norwich Norfolk NR13 5BB United Kingdom	Phone Number: Fax Number: e mail	00+44 (0)1603 439391 00+44 (0)1603 300385 sales@aristowax.com

2. Hazards Identification

F+ Extremely Flammable. Pressurised Container.

3. Composition/Information on Components

Classification according to Regulation (EC) No 1272/2008

Contains: White Mineral Oil (Petroleum) n-Butane, Isobutane, Propane mixture	EINECS Number 232-455-8 270-704-2	CAS Number 8042-47-5 68476-85-7	% Wt/Wt >30 15 - 30	Classification Asp. tox. cat 1: H304 Flammable Gas, Category 1 H220; Gases under pressure H280
Hydrocarbons, C10-C13, n-alkanes, isoalkanes, cyclics, < 2% aromatics	918-481-9		5 - 15	Asp. Tox. 1 H304, EUH066

Classification according to EU Directive 67/548/EEC / 1999/45 EC

Contains:	EINECS Number	CAS Number	% Wt/Wt	Classification
White Mineral Oil (Petroleum)	232-455-8	8042-47-5	>30	Not Classified
n-Butane, Isobutane, Propane mixture	270-704-2	68476-85-7	15 - 30	F+; R12
Hydrocarbons, C10-C13, n-alkanes, isoalkanes, cyclics, < 2% aromatics	918-481-9		5 - 15	Xn, R65, R66

Also contains Fragrance, Benzyl Salicylate, Linalool and Beeswax.

4. First-Aid Measures

Eyes:	Rinse with water for 15 minutes.
Skin:	Wash with soap and water.
Inhalation:	Remove the person to fresh air. If breathing has stopped administer artificial respiration. Obtain medical
	attention.
Ingestion:	Wash out mouth with water. Do not induce vomiting. Give water to drink. Seek medical attention.

5. Fire-Fighting Measures

Use foam, carbon dioxide or dry powder extinguishers.

6. Accidental Release Measures

Absorb with any inert material. Ensure adequate ventilation. Remove sources of ignition.

7. Handling and Storage

Keep away from sources of ignition. Do not smoke while using. Keep at temperature not exceeding 50°C. Protect from sunlight. Keep out of the reach of children. Intentional misuse by deliberately inhaling the contents can be harmful or fatal.

8. Exposure Controls/Personal Protection

Use only as directed on the can. Avoid contact with the skin and eyes.

9. Physical and Chemical Properties

Appearance:	Pale yellow Liquid
Odour:	As fragrance
pH:	6.0 - 8.0

10. Stability and Reactivity

As with all aerosol cans, protect from sunlight and do not expose to temperatures exceeding 50°C.

11. Toxicological Information

Eyes:	May cause irritation.
Skin:	May irritate sensitive skin.
Ingestion:	May cause nausea and vomiting.
Inhalation:	May cause dizziness, stupor or unconsciousness depending on the extent of exposure.

12. Ecological Information

Not expected to cause significant environmental impact.

13. Disposal Considerations

Do not pierce or burn even after use. Dispose according to national and local authority guidelines.

14. Transport Information

Transport Type	ADR (Road/Rail)	SEA	AIR
UN Number	UN 1950	UN 1950	UN 1950
Class	2.1	2.1	2.1
Proper shipping name	Aerosols	Aerosols	Aerosols, flammable
Packing group	None	None	None
Marine pollutant	N/A	No	N/A
Other information	'Limited quantity' provisions	'Limited quantity' provisions	'Limited quantity' provisions
	apply.	apply.	apply.
	No Tremcard required.		Hazard label required:
			Flammable Gas.

15. Regulatory Information

Symbol:

Symbol.	
Classification	H222 Danger Extremely Flammable Aerosol
	H229 Pressurised container: May burst if heated.
Precautionary statements	P102 Keep out of reach of children.
	P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources.
	P211 Do not spray on an open flame or other ignition source.
	P251 Do not pierce or burn, even after use.
	P410 + P412 Protect from sunlight. Do not expose to temperatures exceeding 50°C.

16. Other information

R and H phrases used in this document

R12 Extremely Flammable

R65 Harmful: may cause lung damage if swallowed. R66 Repeated exposure may cause skin dryness or cracking. H220 Extremely flammable gas. H280 Contains gas under pressure; may explode if heated. H304 May be fatal if swallowed and enters airways EUH066: Repeated exposure may cause skin dryness or cracking.

This Safety Data does not constitute the users own assessment of workplace risk.