

INDIGA round files

Type 9030

LAPPORT
SCHLEIFTECHNIK

Application:

For sharpening and reworking tools for wood, metal and plastic processing, e.g. scrapers, machine and plane knives, steels, reamers and gauges as well as measuring instruments.

Execution:

- Best used with thin-bodied oil, petroleum or water
- Machined and wetted on all sides after burning

Advantage:

- High endurance and grinding force



Art. no.	69344 215
Brand	LAPPORT
Manufacturer Part Number	100417
Binding	Ceramically bound
Surface structure	Medium
Grid size	150
Form	Round
Length	100 mm
Width	8 mm
Number of pieces per packet	6 PCS
Diameter	8 mm
Material of abrasive medium	Corundum
Diameter x length	8 x 100 mm
Suitable for finishing	2 - suitable
Suitable for main machining	2 - suitable
Suitable for surface inspection	3 - less suitable
Suitable for surface care	2 - suitable
Suitable for material rubber	3 - less suitable
Suitable for material cast iron	2 - suitable
Suitable for material HSS	3 - less suitable
Suitable for material carbide	3 - less suitable
Suitable for material ceramic	3 - less suitable
Suitable for material plastics	3 - less suitable
Suitable for material non-ferrous metals	3 - less suitable
Suitable for material steel (hardened)	2 - suitable
Suitable for material steel (unhardened)	1 - very suitable
Suitable for material tool steel	2 - suitable
ISO	525
Length x width	100 x 8 mm
Type description	Corundum
Gross Weight	0.016 kg
Product Group	6HL