

## SVVC steel boring bar, positive left

For longitudinal and copy turning with VC indexable insert

**ATORN**<sup>®</sup>



### Application

For longitudinal and copy turning with VC indexable insert 55°

### Version

- Precision-manufactured boring bar, **steel**, with internal cooling, type V, pitch angle 72.5°, tip angle 35°, clearance angle 7°

### Advantage

- Slender geometry for longitudinal and copy turning
- Positive geometry for the body ensures low cutting forces

<b>Art. No.</b>	<b>17827 382</b>
<b>ISO name</b>	A 08F SVVC R/L 05
<b>Min. bore diameter</b>	9.7 mm
<b>Shaft diameter</b>	8 mm
<b>Clearance length</b>	15 mm
<b>Length</b>	80 mm
<b>Clamping surface height</b>	7 mm
<b>Programming size</b>	3.5 mm
<b>Suitable for indexable inserts</b>	VC.. 0501..
<b>Tool design</b>	Right

### EAN-Code

4050293449600