



Classic filament LEDbulbs

LED classic-giant 40W E27 T65 GOLD DIM

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General information		Wattage Equivalent	
Cap-Base	E27 [E27]		40 W
EU RoHS compliant	Yes	Starting Time (Nom)	0.5 s
Nominal Lifetime (Nom)	15000 h	Warm Up Time to 60% Light (Nom)	0.5 s
Switching Cycle	20000X	Power Factor (Nom)	0.7
		Voltage (Nom)	220-240 V
Light technical		Temperature	
Color Code	818 [CCT of 1800K]	T-Case Maximum (Nom)	45 °C
Luminous Flux (Nom)	470 lm		
Color Designation	1800	Controls and dimming	
Correlated Color Temperature (Nom)	1800 K	Dimmable	Yes
Luminous Efficacy (rated) (Nom)	67.00 lm/W		
Color Consistency	<6	Mechanical and housing	
Color Rendering Index (Nom)	80	Bulb Finish	Amber
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Shape	T65 [T 65mm]
Operating and electrical		Approval and application	
Input Frequency	50 to 60 Hz	Energy Consumption kWh/1000 h	7 kWh
Power (Nom)	7 W		
Lamp Current (Nom)	43 mA		


Classic filament LEDbulbs

Product data

Full product code	871951431380400
Order product name	LED classic-giant 40W E27 T65 GOLD DIM
EAN/UPC - Product	8719514313804
Order code	929002983701
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	2
Material Nr. (12NC)	929002983701
Net Weight (Piece)	0.196 kg


Dimensional drawing




LED classic-giant 40W E27 T65 GOLD DIM

Product	D	C
LED classic-giant 40W E27 T65 GOLD DIM	66 mm	273 mm


Photometric data



LEDbulb SLR 7W T65 E27 818 Amber-POC



LEDbulb SLR T65 7W E27 818 Amber-LDD



LEDbulb SLR 7W T65 E27 818 Amber-GUL

Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram

