



## SAFETY DATA SHEET

JENOLITE MEDIUM STRENGTH THREADLOCKER

Page: 1

Compilation date: 13/11/2019

Revision No: 2

### Section 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

**Product name:** JENOLITE MEDIUM STRENGTH THREADLOCKER

**Product code:** 89032

**Synonyms:** 301277

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

**Use of substance / mixture:** PC1: Adhesives, sealants.

#### 1.3. Details of the supplier of the safety data sheet

**Company name:** Jenolite UK Ltd

Chater Lea Buildings

Letchworth

Hertfordshire

SG6 1WT

**Tel:** 01462 480764 **Email:**

[Sales@Jenolite.com](mailto:Sales@Jenolite.com)

#### 1.4. Emergency telephone number

**Emergency tel:** 01462 480764

(office hours only)

### Section 2: Hazards identification

#### 2.1. Classification of the substance or mixture

**Classification under CLP:** Aquatic Acute 1: H400; Aquatic Chronic 2: H411; Eye Irrit. 2: H319; Skin Irrit. 2: H315; Skin Sens. 1: H317; STOT SE 3: H335; -: EUH208

**Most important adverse effects:** Contains 1-acetyl-2-phenylhydrazine. May produce an allergic reaction. Causes skin irritation. May cause an allergic skin reaction. Causes serious eye irritation. May cause respiratory irritation. Very toxic to aquatic life. Toxic to aquatic life with long lasting effects.

#### 2.2. Label elements

##### Label elements:

**Hazard statements:** EUH208: Contains 1-acetyl-2-phenylhydrazine. May produce an allergic reaction.  
H315: Causes skin irritation.  
H317: May cause an allergic skin reaction.  
H319: Causes serious eye irritation.  
H335: May cause respiratory irritation.  
H400: Very toxic to aquatic life.  
H411: Toxic to aquatic life with long lasting effects.

[cont...]

## SAFETY DATA SHEET

### JENOLITE MEDIUM STRENGTH THREADLOCKER

Page: 2

**Hazard pictograms:** GHS07: Exclamation mark  
GHS09: Environmental



**Signal words:** Warning

**Precautionary statements:** P261: Avoid breathing vapours.  
P264: Wash contaminated skin thoroughly after handling.  
P271: Use only outdoors or in a well-ventilated area.  
P273: Avoid release to the environment.  
P280: Wear protective gloves/protective clothing/eye protection/face protection.  
P302+P352: IF ON SKIN: Wash with plenty of water.  
P304+P340: IF INHALED: Remove person to fresh air and keep comfortable for breathing.  
P305+P351+P338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.  
P312: Call a POISON CENTRE or doctor if you feel unwell.  
P321: Specific treatment (see information on this label)  
P332+P313: If skin irritation occurs: Get medical advice/attention.  
P337+P313: If eye irritation persists: Get medical advice/attention.  
P403+P233: Store in a well-ventilated place. Keep container tightly closed.  
P501: Dispose of contents/container to comply with Local, National and International regulations.

**Haz. ingredients (label):** POLYGLYCOL DIMETHACRYLATE; BIS(ISOPROPYL)NAPHTHALENE; HYDROXYALKYL METHACRYLATE; ACRYLIC ACID

#### 2.3. Other hazards

**PBT:** This product is not identified as a PBT/vPvB substance.

#### Section 3: Composition/information on ingredients

##### 3.2. Mixtures

###### Hazardous ingredients:

TRIETHYLENE GLYCOL DIMETHACRYLATE

EINECS	CAS	PBT / WEL	CLP Classification	Percent
203-652-6	109-16-0	-	Skin Sens. 1: H317	30-50%

[cont...]

## SAFETY DATA SHEET

### JENOLITE MEDIUM STRENGTH THREADLOCKER

Page: 3

#### BIS(ISOPROPYL)NAPHTHALENE

254-052-6	38640-62-9	-	Aquatic Acute 1: H400; Aquatic Chronic 2: H411	10-30%
-----------	------------	---	--	--------

#### HYDROXYALKYL METHACRYLATE

248-666-3	27813-02-1	-	STOT SE 3: H335; Eye Irrit. 2: H319; Skin Sens. 1: H317	2.9-10%
-----------	------------	---	---	---------

#### CUMENE HYDROPEROXIDE

201-254-7	80-15-9	-	Org. Perox. EF: H242; Acute Tox. 3: H331; Acute Tox. 4: H312; Acute Tox. 4: H302; STOT RE 2: H373; Skin Corr. 1B: H314; Aquatic Chronic 2: H411	1-2.9%
-----------	---------	---	---	--------

#### ACRYLIC ACID

201-177-9	79-10-7	-	Flam. Liq. 3: H226; Acute Tox. 4: H332; Acute Tox. 4: H312; Acute Tox. 4: H302; Skin Corr. 1A: H314; Aquatic Acute 1: H400	<1%
-----------	---------	---	--	-----

#### 1-ACETYL-2-PHENYLHYDRAZINE

204-055-3	114-83-0	-	Acute Tox. 3: H301+H311; Skin Irrit. 2: H315; STOT SE 3: H335; Aquatic Chronic 1: H410; Eye Irrit. 2: H319; Skin Sens. 1B: H317	<1%
-----------	----------	---	---	-----

#### 2,6-DI-TERT-BUTYL-P-CRESOL

204-881-4	128-37-0	-	Aquatic Chronic 1: H410	<1%
-----------	----------	---	-------------------------	-----

#### N,N-DIMETHYL-P-TOLUIDINE

202-805-4	99-97-8	-	Acute Tox. 3: H331; Acute Tox. 3: H311; Acute Tox. 3: H301; STOT RE 2: H373; Aquatic Chronic 3: H412	<1%
-----------	---------	---	--	-----

## Section 4: First aid measures

### 4.1. Description of first aid measures

**Skin contact:** Remove all contaminated clothes and footwear immediately unless stuck to skin. Wash immediately with plenty of soap and water.

**Eye contact:** Bathe the eye with running water for 15 minutes. Consult a doctor.

**Ingestion:** Wash out mouth with water. Consult a doctor.

**Inhalation:** Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor.

### 4.2. Most important symptoms and effects, both acute and delayed

**Skin contact:** There may be irritation and redness at the site of contact.

**Eye contact:** There may be irritation and redness. The eyes may water profusely.

**Ingestion:** There may be soreness and redness of the mouth and throat.

[cont...]

## SAFETY DATA SHEET

### JENOLITE MEDIUM STRENGTH THREADLOCKER

Page: 4

**Inhalation:** There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

**Delayed / immediate effects:** Immediate effects can be expected after short-term exposure.

#### 4.3. Indication of any immediate medical attention and special treatment needed

**Immediate / special treatment:** Eye bathing equipment should be available on the premises.

### Section 5: Fire-fighting measures

#### 5.1. Extinguishing media

**Extinguishing media:** Suitable extinguishing media for the surrounding fire should be used. Use water spray to cool containers.

#### 5.2. Special hazards arising from the substance or mixture

**Exposure hazards:** In combustion emits toxic fumes.

#### 5.3. Advice for fire-fighters

**Advice for fire-fighters:** Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

### Section 6: Accidental release measures

#### 6.1. Personal precautions, protective equipment and emergency procedures

**Personal precautions:** Refer to section 8 of SDS for personal protection details. If outside do not approach from downwind. If outside keep bystanders upwind and away from danger point. Mark out the contaminated area with signs and prevent access to unauthorised personnel. Turn leaking containers leak-side up to prevent the escape of liquid.

#### 6.2. Environmental precautions

**Environmental precautions:** Do not discharge into drains or rivers. Contain the spillage using bunding.

#### 6.3. Methods and material for containment and cleaning up

**Clean-up procedures:** Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

#### 6.4. Reference to other sections

**Reference to other sections:** Refer to section 8 of SDS.

### Section 7: Handling and storage

#### 7.1. Precautions for safe handling

**Handling requirements:** Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area. Do not handle in a confined space. Avoid the formation or spread of mists in the air.

#### 7.2. Conditions for safe storage, including any incompatibilities

**Storage conditions:** Store in a cool, well ventilated area. Keep container tightly closed. The floor of the storage room must be impermeable to prevent the escape of liquids.

[cont...]

**SAFETY DATA SHEET**  
JENOLITE MEDIUM STRENGTH THREADLOCKER

Page: 5

**7.3. Specific end use(s)**

**Specific end use(s):** No data available.

**Section 8: Exposure controls/personal protection**

**8.1. Control parameters**

**Hazardous ingredients:**

**ACRYLIC ACID**

**Workplace exposure limits:**

**Respirable dust**

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	30 mg/m <sup>3</sup>	60 mg/m <sup>3</sup>	-	-

**2,6-DI-TERT-BUTYL-P-CRESOL**

UK	10 mg/m <sup>3</sup>	-	-	-
----	----------------------	---	---	---

**DNEL/PNEC Values**

**DNEL / PNEC** No data available.

**8.2. Exposure controls**

**Engineering measures:** Ensure there is sufficient ventilation of the area. The floor of the storage room must be impermeable to prevent the escape of liquids.

**Respiratory protection:** Self-contained breathing apparatus must be available in case of emergency.

**Hand protection:** Protective gloves.

**Eye protection:** Safety glasses. Ensure eye bath is to hand.

**Skin protection:** Protective clothing.

**Section 9: Physical and chemical properties**

**9.1. Information on basic physical and chemical properties**

**State:** Liquid

**Colour:** Blue

**Odour:** Perceptible odour

**Evaporation rate:** No data available.

**Oxidising:** No data available.

**Solubility in water:** Insoluble

**Viscosity:** No data available.

**Boiling point/range°C:** >35

**Melting point/range°C:** No data available.

**Flammability limits %: lower:** No data available.

**upper:** No data available.

**Flash point°C:** >93

**Part.coeff. n-octanol/water:** No data available.

**Autoflammability°C:** No data available.

**Vapour pressure:** No data available.

**Relative density:** 1.07

**pH:** No data available.

**VOC g/l:** No data available.

[cont...]

**SAFETY DATA SHEET**  
JENOLITE MEDIUM STRENGTH THREADLOCKER

Page: 6

**9.2. Other information**

**Other information:** No data available.

**Section 10: Stability and reactivity**

**10.1. Reactivity**

**Reactivity:** Stable under recommended transport or storage conditions.

**10.2. Chemical stability**

**Chemical stability:** Stable under normal conditions.

**10.3. Possibility of hazardous reactions**

**Hazardous reactions:** Hazardous reactions will not occur under normal transport or storage conditions.

Decomposition may occur on exposure to conditions or materials listed below.

**10.4. Conditions to avoid**

**Conditions to avoid:** Heat.

**10.5. Incompatible materials**

**Materials to avoid:** Strong oxidising agents. Strong acids.

**10.6. Hazardous decomposition products**

**Haz. decomp. products:** In combustion emits toxic fumes.

**Section 11: Toxicological information**

**11.1. Information on toxicological effects**

**Hazardous ingredients:**

**CUMENE HYDROPEROXIDE**

ORL	MUS	LDLO	5	gm/kg
ORL	RAT	LD50	382	mg/kg
SCU	RAT	LD50	382	mg/kg

**ACRYLIC ACID**

IPR	RAT	LD50	22	mg/kg
ORL	MUS	LD50	830	mg/kg
ORL	RAT	LD50	1250	mg/kg
SCU	MUS	LD50	1590	mg/kg

**N,N-DIMETHYL-P-TOLUIDINE**

IPR	MUS	LD50	212	mg/kg
-----	-----	------	-----	-------

[cont...]

**SAFETY DATA SHEET**  
JENOLITE MEDIUM STRENGTH THREADLOCKER

Page: 7

**Relevant hazards for product:**

Hazard	Route	Basis
Skin corrosion/irritation	DRM	Hazardous: calculated
Serious eye damage/irritation	OPT	Hazardous: calculated
Respiratory/skin sensitisation	DRM	Hazardous: calculated
STOT-single exposure	INH	Hazardous: calculated

**Symptoms / routes of exposure**

**Skin contact:** There may be irritation and redness at the site of contact.

**Eye contact:** There may be irritation and redness. The eyes may water profusely.

**Ingestion:** There may be soreness and redness of the mouth and throat.

**Inhalation:** There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

**Delayed / immediate effects:** Immediate effects can be expected after short-term exposure.

**Section 12: Ecological information**

**12.1. Toxicity**

**Hazardous ingredients:**

**2,6-DI-TERT-BUTYL-P-CRESOL**

ALGAE	96H ErC50	0.758	mg/l
Daphnia magna	48H EC50	0.48	mg/l
FISH	96H LC50	0.199	mg/l

**12.2. Persistence and degradability**

**Persistence and degradability:** Not biodegradable.

**12.3. Bioaccumulative potential**

**Bioaccumulative potential:** Bioaccumulation potential.

**12.4. Mobility in soil**

**Mobility:** Readily absorbed into soil.

**12.5. Results of PBT and vPvB assessment**

**PBT identification:** This product is not identified as a PBT/vPvB substance.

**12.6. Other adverse effects**

**Other adverse effects:** Toxic to aquatic organisms. Toxic to soil organisms.

**Section 13: Disposal considerations**

**13.1. Waste treatment methods**

**Disposal operations:** Transfer to a suitable container and arrange for collection by specialised disposal company.

[cont...]

## SAFETY DATA SHEET

### JENOLITE MEDIUM STRENGTH THREADLOCKER

Page: 8

**NB:** The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

#### Section 14: Transport information

##### 14.1. UN number

**UN number:** UN3082

##### 14.2. UN proper shipping name

**Shipping name:** ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S.  
(BIS(ISOPROPYL)NAPHTHALENE)

##### 14.3. Transport hazard class(es)

**Transport class:** 9

##### 14.4. Packing group

**Packing group:** III

##### 14.5. Environmental hazards

**Environmentally hazardous:** Yes

**Marine pollutant:** No

##### 14.6. Special precautions for user

**Special precautions:** No special precautions.

**Tunnel code:** E

**Transport category:** 3

#### Section 15: Regulatory information

##### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

**Specific regulations:** Not applicable.

##### 15.2. Chemical Safety Assessment

#### Section 16: Other information

##### Other information

**Other information:** This safety data sheet is prepared in accordance with Commission Regulation (EU) No 2015/830.

\* indicates text in the SDS which has changed since the last revision.

**Phrases used in s.2 and s.3:** EUH208: Contains 1-acetyl-2-phenylhydrazine. May produce an allergic reaction.

H226: Flammable liquid and vapour.

H242: Heating may cause a fire.

H301: Toxic if swallowed.

H301+H311: Toxic if swallowed or in contact with skin

H302: Harmful if swallowed.

H311: Toxic in contact with skin.

[cont...]

## SAFETY DATA SHEET

### JENOLITE MEDIUM STRENGTH THREADLOCKER

Page: 9

H312: Harmful in contact with skin.  
H314: Causes severe skin burns and eye damage.  
H315: Causes skin irritation.  
H317: May cause an allergic skin reaction.  
H319: Causes serious eye irritation.  
H331: Toxic if inhaled.  
H332: Harmful if inhaled.  
H335: May cause respiratory irritation.  
H373: May cause damage to organs through prolonged or repeated exposure.  
H400: Very toxic to aquatic life.  
H410: Very toxic to aquatic life with long lasting effects.  
H411: Toxic to aquatic life with long lasting effects.  
H412: Harmful to aquatic life with long lasting effects.

**Legal disclaimer:** The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.