

Pneumatic straight grinder G 120 H

**MANNESMANN
DEMAG**

Application:

For heavy deburring work. Ideal for brushing.

Delivery:

Includes hose unit and collet chuck keys



Art. no.	75061 085
Brand	MANNESMANN DEMAG
Manufacturer Part Number	60026695
Model	G 120 H
Valve design	Lever valve
Max. idle speed	12000 rpm
Min./max. idle speed	0-12000 rpm
Power output	400 W
Air consumption	12 l/s
Connection thread	G 1/4 inch
Sound-pressure level	74 dB
Length	205 mm
Diameter of housing	39 mm
Collet chuck diameter	6 mm
Suitable for max. sanding block diameter	32 mm
Max. HM rotating milling cutter diameter	12 mm
Weight	0.88 kg
Gross Weight	0.880 kg
Product Group	7AA

EAN

4251757301247