



3 YEAR
WARRANTY



ENGLISH

Datasheet

RS PRO LED Rework Station AC 220 - 240 V, 700 W, UK Type G and Euro Type F Plug

RS Stock no: 124-4133



Replacement Nozzle- 137-2236

Specifications:

Model Number	124-4133
Plug type	B and C
Primary Application Category	Soldering
Input Voltage	220 V to 240 V
Output Power	700 W
Nozzle	φ4.3 mm / φ7.4 mm / φ11.2 mm
Maximum Operating Temperature	450 °C
Minimum Operating Temperature	100 °C
Number of Outputs	1
Display Type	LED
Equipment noise	45 dD
Air-Volume	120 L / min (Max)
Height	170 mm
Width	140mm
Depth	170mm
Weight	1.35 kg

Type G and Euro Type F Plug



Replacement Accessory:

Stock Number	Description
137-2236	Replacement nozzles (3 sizes) ϕ 4.3 mm / ϕ 7.4 mm / ϕ 11.2 mm for 124-4133

Features:

Hot air SMD rework station with heat gun holder

Microprocessor temperature controlled with closed circuit sensor design, provide high power and quick warm up times.

Time to heat up to 160°C: 30 seconds. Time to heat up to 300°C: 15 seconds

Adjustable air flow, air volume and temperature control

Auto-sleep and work mode

Temperature display

Brushless motor design, quiet operation, equipment noise less than 45 dB

Automatic cool-off process to prolong the life of heating element

The wires are AWG 20 (0.5 mm²) UL certified

Metal case design adds to durability

Supplied with 3 nozzles: 4.3 mm, 7.4 mm and 11.2 mm

Complies with CE standard. Conform to RoHS.