

## Industrial scales IFS

high resolution

**KERN**

### Application:

For professional weighing and counting in industrial environments, also suitable for continuous use in production and manufacturing.

### Execution:

- Dual range scales with automatic switch-over
- Display: Total weight, reference weight in g, total quantity
- Removable display unit with 1.5 m cable
- Large LCD display with 13/16 mm digit size and backlight
- Tolerance range: Input upper/lower limit values. Optical and acoustic signals support sorting, portioning etc. in count mode
- Functions: Reference quantity, reference weight and PRE-TARE for manual prior subtraction of known container weights
- Counting total memory for adding up measured values
- Automatic reference optimisation
- Options: Battery operation approx. 40 h without backlight



### Delivery:

Tabletop feet and wall bracket for display device and power pack

<b>Art. no.</b>	<b>44619 240</b>
<b>Brand</b>	KERN
<b>Manufacturer Part Number</b>	IFS 100K-3
<b>Type description</b>	IFS 100K-3
<b>Max. weight measuring range</b>	75 kg
<b>Max. weight measuring range 2</b>	150 kg
<b>Digit increment, weight</b>	1 g
<b>Digit increment 2, weight</b>	2 g
<b>Plate size</b>	500 x 400 mm
<b>With unit counting</b>	Yes
<b>Min. item weight</b>	2.5 g
<b>Data transmission type</b>	RS232
<b>Housing dimensions (LxWxH)</b>	500 x 810 x 137 mm
<b>Gross Weight</b>	14.000 kg
<b>Product Group</b>	447

### EAN

4045761144835