Version: N°1 (28/02/2018)

GISS

INSECTICIDE RAMPANTS - 863359

Date: 01/03/2018 Page 1/10 Revision: N° 10 (28/02/2018)

SAFETY DATA SHEET

(REACH regulation (EC) n° 1907/2006 - n° 2015/830)

SECTION 1 : IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1. Product identifier

Product name: INSECTICIDE RAMPANTS

Product code: 863359

1.2. Relevant identified uses of the substance or mixture and uses advised against

BIOCIDE

1.3. Details of the supplier of the safety data sheet

Registered name company: IPH BRANDS

Address: 31 rue de la Baume, 75008 Paris, France

Telephone: +33 1-44-86-08-10

infoclient@giss.fr http://www.giss.fr

1.4. Emergency telephone number: +33 (0)1.45.42.59.59.

Association/Organisation: INRS/ORFILA http://www.centres-antipoison.net.

SECTION 2: HAZARDS IDENTIFICATION

2.1. Classification of the substance or mixture

In compliance with EC regulation No. 1272/2008 and its amendments.

Aerosol, Category 1 (Aerosol 1, H222 - H229).

Repeated exposure may cause skin dryness or cracking (EUH066).

Hazardous to the aquatic environment - Acute hazard, Category 1 (Aquatic Acute 1, H400). Hazardous to the aquatic environment - Chronic hazard, Category 1 (Aquatic Chronic 1, H410).

2.2. Label elements

Biocidal mixture (see section 15).

Mixture for spray application.

Mixture for aerosol application.

In compliance with EC regulation No. 1272/2008 and its amendments.

Hazard pictograms:





GHS09

GHS02

Signal Word : DANGER

Hazard statements:

H222 Extremely flammable aerosol.

H229 Pressurised container: May burst if heated.
H410 Very toxic to aquatic life with long lasting effects.
EUH066 Repeated exposure may cause skin dryness or cracking.

Precautionary statements - General:

P101 If medical advice is needed, have product container or label at hand.

P102 Keep out of reach of children.

 $Precaution ary\ statements\ -\ Prevention:$

P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition

sources. No smoking.

P211 Do not spray on an open flame or other ignition source.

P251 Do not pierce or burn, even after use.

Version: N°1 (28/02/2018)

GISS

Date: 01/03/2018 Page 2/10 Revision: N° 10 (28/02/2018)

INSECTICIDE RAMPANTS - 863359

P270 Do not eat, drink or smoke when using this product.

P273 Avoid release to the environment.

Precautionary statements - Storage:

P410 + P412 Protect from sunlight. Do no expose to temperatures exceeding 50 oC/122oF.

Precautionary statements - Disposal:

P501 Dispose of contents/container in accordance with national regulations.

Other information:

Keep away from food, drink and animal feedingstuffs.

2.3. Other hazards

The mixture does not contain substances classified as 'Substances of Very High Concern' (SVHC) >= 0.1% published by the European CHemicals Agency (ECHA) under article 57 of REACH: http://echa.europa.eu/fr/candidate-list-table

The mixture fulfils neither the PBT nor the vPvB criteria for mixtures in accordance with annexe XIII of the REACH regulations EC 1907/2006.

SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

3.2. Mixtures

Composition:

Identification	(EC) 1272/2008	Note	%
INDEX: A9184819	GHS08		25 <= x % < 50
EC: 918-481-9	Dgr		
REACH: 01-2119457273-39	Asp. Tox. 1, H304		
	EUH:066		
HYDROCARBURE, C10-C13, N-ALCANES,			
ISOALCANES, CYCLIQUES, <2%			
AROMATIQUE			
INDEX: 601_004_00_0	GHS02, GHS04	С	25 <= x % < 50
CAS: 106-97-8	Dgr	[1]	
EC: 203-448-7	Flam. Gas 1, H220	[7]	
REACH: 01-2119474691-32	Press. Gas, H280		
BUTANE			
INDEX: 603-117-00-0	GHS02, GHS07	[1]	2.5 <= x % < 10
CAS: 67-63-0	Dgr		
EC: 200-661-7	Flam. Liq. 2, H225		
REACH: 01-2119457558-25	Eye Irrit. 2, H319		
	STOT SE 3, H336		
PROPAN-2-OL			
INDEX: C8042475	GHS08		1 <= x % < 2.5
CAS: 8042-47-5	Dgr		
EC: 232-455-8	Asp. Tox. 1, H304		
REACH: 01-2119487078-27			
HUILE MINÉRALE BLANCHE (PÉTROLE)			
INDEX: A2544845	GHS07, GHS09		0 <= x % < 1
CAS: 39515-40-7	Wng		
EC: 254-484-5	Acute Tox. 4, H302		
CVENTENTOTALDA	Aquatic Acute 1, H400		
CYPHENOTHRIN	M Acute = 1000		
(2,2-DIMETHYL-3-(2-METHYLPROP-1-	Aquatic Chronic 1, H410		
ENYL	M Chronic = 1000		
)CYCLOPROPANECARBOXYLATE DE			
ALPHA-CYANO-3-PHENOXYBENZYLE)			

Version: N°1 (28/02/2018)

GISS

INSECTICIDE RAMPANTS - 863359

Date: 01/03/2018 Page 3/10 Revision: N° 10 (28/02/2018)

INDEX: A1166467	GHS09	0 <= x % < 1
CAS: 1166-46-7	Wng	
EC: 214-619-0	Aquatic Acute 1, H400	
	M Acute = 100	
D-TETRAMETHRINE	Aquatic Chronic 1, H410	
	M Chronic = 100	

Information on ingredients:

- [7] Propellant gas
- [1] Substance for which maximum workplace exposure limits are available.

SECTION 4: FIRST AID MEASURES

As a general rule, in case of doubt or if symptoms persist, always call a doctor.

NEVER induce swallowing by an unconscious person.

4.1 . Description of first aid measures

In the event of splashes or contact with eyes:

Wash thoroughly with fresh, clean water for 15 minutes holding the eyelids open.

In the event of splashes or contact with skin:

Remove contaminated clothing and wash the skin thoroughly with soap and water or a recognised cleaner.

Watch out for any remaining product between skin and clothing, watches, shoes, etc.

In the event of swallowing:

In the event of swallowing, if the quantity is small (no more than one mouthful), rinse the mouth with water and consult a doctor.

Keep the person exposed at rest. Do not force vomiting.

Seek medical attention, showing the label.

4.2. Most important symptoms and effects, both acute and delayed

No data available.

4.3 . Indication of any immediate medical attention and special treatment needed

No data available.

SECTION 5: FIREFIGHTING MEASURES

Flammable.

Chemical powders, carbon dioxide and other extinguishing gas are suitable for small fires.

${\bf 5.1.}$ Extinguishing media

In the event of fire, use specifically suitable extinguishing agents. Never use water.

Keep packages near the fire cool, to prevent pressurised containers from bursting.

Suitable methods of extinction

In the event of a fire, use:

- sprayed water or water mist
- water with AFFF (Aqueous Film Forming Foam) additive
- halon
- foam
- multipurpose ABC powder
- BC powder
- carbon dioxide (CO 2)

Prevent the effluent of fire-fighting measures from entering drains or waterways.

Unsuitable methods of extinction

In the event of a fire, do not use:

- water
- water jet

${\bf 5.2}$. Special hazards arising from the substance or mixture

A fire will often produce a thick black smoke. Exposure to decomposition products may be hazardous to health.

Do not breathe in smoke.

In the event of a fire, the following may be formed :

- carbon monoxide (CO)

GISS

Revision : N° 10 (28/02/2018)

Date: 01/03/2018 Page 4/10

INSECTICIDE RAMPANTS - 863359

- carbon dioxide (CO 2)

5.3. Advice for firefighters

Due to the toxicity of the gas emitted on thermal decomposition of the products, fire-fighting personnel are to be equipped with autonomous insulating breathing apparatus.

SECTION 6: ACCIDENTAL RELEASE MEASURES

6.1. Personal precautions, protective equipment and emergency

procedures Consult the safety measures listed under headings 7

For non first aid worker

Because of the organic solvents contained in the mixture, eliminate sources of ignition and ventilate the area.

Avoid any contact with the skin and eyes.

For first aid worker

First aid workers will be equipped with suitable personal protective equipment (See section 8).

6.2. Environmental precautions

Contain and control the leaks or spills with non-combustible absorbent materials such as sand, earth, vermiculite, diatomaceous earth in drums for waste disposal.

Prevent any material from entering drains or waterways.

If the product contaminates waterways, rivers or drains, alert the relevant authorities in accordance with statutory procedures Use drums to dispose of collected waste in compliance with current regulations (see section 13).

6.3. Methods and material for containment and cleaning up

Clean preferably with a detergent, do not use solvents.

The elimination must be carried out by a registrated salvage professionnal.

6.4. Reference to other sections No data available.

SECTION 7: HANDLING AND STORAGE

Requirements relating to storage premises apply to all facilities where the mixture is handled.

7.1. Precautions for safe handling

Always wash hands after handling.

Remove and wash contaminated clothing before re-using.

Ensure that there is adequate ventilation, especially in confined areas.

Remove contaminated clothing and protective equipment before entering eating areas.

Fire prevention:

Handle in well-ventilated areas.

Vapours are heavier than air. They can spread along the ground and form mixtures that are explosive with air.

Prevent the formation of flammable or explosive concentrations in air and avoid vapor concentrations higher than the occupational exposure limits.

Do not spray on a naked flame or any incandescent material.

Do not pierce or burn, even after use.

Use the mixture in premises free of naked flames or other sources of ignition and ensure that electrical equipment is suitably protected.

Keep packages tightly closed and away from sources of heat, sparks and naked flames.

Do not use tools which may produce sparks. Do not smoke.

Prevent access by unauthorised personnel.

Recommended equipment and procedures:

For personal protection, see section 8.

Observe precautions stated on label and also industrial safety regulations.

Never pour water into this mixture.

Do not breathe in aerosols.

Where the personnel must carry out work in a booth, whether for spraying or otherwise, the ventilation may be inadequate to control particles and solvent vapors in every case.

GISS

Revision : N° 10 (28/02/2018)

Date: 01/03/2018 Page 5/10

INSECTICIDE RAMPANTS - 863359

It is therefore recommended that personnel wear masks with a compressed air supply during spraying operations until the concentration of particles and solvent vapors has fallen below the exposure limits.

Packages which have been opened must be reclosed carefully and stored in an upright position.

Prohibited equipment and procedures:

No smoking, eating or drinking in areas where the mixture is used.

Never open the packages under pressure.

7.2. Conditions for safe storage, including any incompatibilities

No data available.

Storage

Keep out of reach of children.

Keep the container tightly closed in a dry, well-ventilated place.

Keep away from all sources of ignition - do not smoke.

Keep well away from all sources of ignition, heat and direct sunlight.

The floor must be impermeable and form a collecting basin so that, in the event of an accidental spillage, the liquid cannot spread beyond this area.

Pressurised container: protect from sunlight and do not expose to temperatures exceeding 50°C.

Packaging

Always keep in packaging made of an identical material to the original.

7.3 . Specific end use(s)

No data available.

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1. Control parameters

Occupational exposure limits:

- France (INRS - ED984:2012):

CAS	VME-ppm:	VME-mg/m3:	VLE-ppm:	VLE-mg/m3:	Notes:	TMP No:
106-97-8	800	1900	-	-	-	-
67-63-0	-	-	400	980	-	84

- UK / WEL (Workplace exposure limits, EH40/2005, 2007) :

CAS	TWA:	STEL:	Ceiling:	Definition:	Criteria:
106-97-8	600 ppm 1450 mg/m3	750 ppm 1810 mg/m 3		Carc	
67-63-0	400 ppm 999 mg/m3	500 ppm 1250 mg/m 3			

8.2. Exposure controls

Personal protection measures, such as personal protective equipment

Use personal protective equipment that is clean and has been properly maintained.

Store personal protective equipment in a clean place, away from the work area.

Never eat, drink or smoke during use. Remove and wash contaminated clothing before re-using. Ensure that there is adequate ventilation, especially in confined areas.

- Eye / face protection Avoid contact with eyes.

Use eye protectors designed to protect against liquid splashes

Before handling, wear safety goggles in accordance with standard EN166.

- Hand protection

Use suitable protective gloves that are resistant to chemical agents in accordance with standard EN374.

Gloves must be selected according to the application and duration of use at the workstation.

Protective gloves need to be selected according to their suitability for the workstation in question: other chemical products that may be handled, necessary physical protections (cutting, pricking, heat protection), level of dexterity required.

Type of gloves recommended:

Version: N°1 (28/02/2018)

GISS

INSECTICIDE RAMPANTS - 863359

Date: 01/03/2018 Page 6/10 Revision: N° 10 (28/02/2018)

- Nitrile rubber (butadiene-acrylonitrile copolymer rubber (NBR)) PVA (Polyvinyl alcohol) Recommended properties :
- Impervious gloves in accordance with standard EN 374

- Body protection

Avoid skin contact.

Wear suitable protective clothing.

Suitable type of protective clothing:

In the event of spraying, wear protective clothing against chemical risks and against sprayed liquid (type 4) in accordance with EN14605 to prevent skin contact.

Work clothing worn by personnel shall be laundered regularly.

After contact with the product, all parts of the body that have been soiled must be washed.

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

9.1. Information on

basic physical and chemical properties General information:

Physical state : Fluid liquid.

Spray.

Important health, safety and environmental information

pH: Not relevant. Boiling point/boiling range: 82 °C.

Vapour pressure (50°C): Below 110 kPa (1.10 bar).

Density: < 1

Water solubility:

Melting point/melting range:

Self-ignition temperature:

Decomposition point/decomposition range:

Chemical combustion heat:

Insoluble.

Not specified.

250 °C.

250 °C.

>= 30 kJ/g.

9.2. Other

information No data

available.

SECTION 10: STABILITY AND REACTIVITY

10.1. Reactivity No data available.

10.2. Chemical stability

This mixture is stable under the recommended handling and storage conditions in section 7.

10.3. Possibility of hazardous reactions

When exposed to high temperatures, the mixture can release hazardous decomposition products, such as carbon monoxide and dioxide, fumes and nitrogen oxide.

10.4. Conditions to avoid

Any apparatus likely to produce a flame or to have a metallic surface at high temperature (burners, electric arcs, furnaces etc.) must not be allowed on the premises. Avoid:

- heating
- heat
- humidity
- accumulation of electrostatic charges.
- flames and hot surfaces

Protect from moisture. Reaction with water can cause an exothermic reaction.

10.5. Incompatible materials

Keep away from:

- water
- strong oxidising agents

Version: N°1 (28/02/2018)

GISS

INSECTICIDE RAMPANTS - 863359

Date: 01/03/2018 Page 7/10 Revision: N° 10 (28/02/2018)

- strong acids

10.6 . Hazardous decomposition products The

thermal decomposition may release/form:

- carbon monoxide (CO)
- carbon dioxide (CO 2)

SECTION 11: TOXICOLOGICAL INFORMATION

11.1 . Information on toxicological effects

Exposure to vapours from solvents in the mixture in excess of the stated occupational exposure limit may result in adverse health effects such as mucous membrane and respiratory system irritation and adverse effects on kidney, liver and central nervous system.

Symptoms produced will include headaches, numbness, dizziness, fatigue, muscular asthenia and, in extreme cases, loss of consciousness.

Repeated or prolonged contact with the mixture may cause removal of natural oil from the skin resulting in non-allergic contact dermatitis and absorption through the skin.

Splashes in the eyes may cause irritation and reversible damage 11.1.1

. Substances

Acute toxicity:

D-TETRAMETHRINE (CAS: 1166-46-7)

Oral route: LD50 > 5000 mg/kg Species: Rat

(recommended by the CLP)

Dermal route : LD50 > 5000 mg/kg Species : Rat

(recommended by the CLP)

 $Inhalation \ route \ (n/a): \qquad LC50 > 1.18 \ mg/l$

Species: Rat (recommended by the CLP)

CYPHENOTHRIN (2,2-DIMETHYL-3-(2-METHYLPROP-1-ENYL)CYCLOPROPANECARBOXYLATE DE

ALPHA-CYANO-3-PHENOXYBENZYLE) (CAS: 39515-40-7)

Oral route : LD50 = 350 mg/kg

Species: Rat (recommended by the CLP)

11.1.2 . Mixture

No toxicological data available for the mixture.

Monograph(s) from the IARC (International Agency for Research on Cancer):

CAS 67-63-0: IARC Group 3: The agent is not classifiable as to its carcinogenicity to humans.

SECTION 12: ECOLOGICAL INFORMATION

Very toxic to aquatic life with long lasting effects.

The product must not be allowed to run into drains or waterways.

12.1. Toxicity

12.1.1. Substances

D-TETRAMETHRINE (CAS: 1166-46-7)

Fish toxicity: LC50 = 0.01 mg/l

Factor M = 100

Duration of exposure: 96 h

Crustacean toxicity: EC50 = 0.11 mg/l

Species : Daphnia magna Duration of exposure : 48 h

Algae toxicity: ECr50 = 2.3 mg/l

Duration of exposure : 72 h

Version: N°1 (28/02/2018)

GISS

INSECTICIDE RAMPANTS - 863359

Date: 01/03/2018 Page 8/10 Revision: N° 10 (28/02/2018)

CYPHENOTHRIN (2,2-DIMETHYL-3-(2-METHYLPROP-1-ENYL)CYCLOPROPANECARBOXYLATE DE ALPHA-CYANO-3-PHENOXYBENZYLE) (CAS: 39515-40-7)

Fish toxicity: LC50 = 0.00034 mg/l

Factor M = 1000

Duration of exposure: 96 h

Crustacean toxicity: EC50 = 0.00043 mg/l

Factor M = 1000

Duration of exposure: 48 h

Algae toxicity: ECr50 = 0.014 mg/l

Factor M = 10

Duration of exposure: 72 h

12.1.2 . Mixtures

No aquatic toxicity data available for the mixture.

12.2. Persistence and degradability

12.2.1 . Substances

D-TETRAMETHRINE (CAS: 1166-46-7)

Biodegradability: no degradability data is available, the substance is considered as not degrading

quickly.

CYPHENOTHRIN (2,2-DIMETHYL-3-(2-METHYLPROP-1-ENYL)CYCLOPROPANECARBOXYLATE DE

ALPHA-CYANO-3-PHENOXYBENZYLE) (CAS: 39515-40-7)

Biodegradability: no degradability data is available, the substance is considered as not

degrading quickly.

12.3 . Bioaccumulative potential

No data available.

12.4. Mobility in soil

12.5. Results of PBT and vPvB assessment

No data available.

12.6. Other adverse effects

SECTION 13 : DISPOSAL CONSIDERATIONS

Proper waste management of the mixture and/or its container must be determined in accordance with Directive 2008/98/EC.

13.1. Waste treatment methods

Do not pour into drains or waterways.

Waste:

Waste management is carried out without endangering human health, without harming the environment and, in particular without risk to water, air, soil, plants or animals.

Recycle or dispose of waste in compliance with current legislation, preferably via a certified collector or company.

Do not contaminate the ground or water with waste, do not dispose of waste into the environment.

Soiled packaging:

Empty container completely. Keep label(s) on container.

Give to a certified disposal contractor.

SECTION 14: TRANSPORT INFORMATION

Transport product in compliance with provisions of the ADR for road, RID for rail, IMDG for sea and ICAO/IATA for air transport (ADR 2017 - IMDG 2016 - ICAO/IATA 2017).

14.1. UN number

1950

14.2. UN proper shipping name

UN1950=AEROSOLS, flammable

GISS

Date: 01/03/2018 Page 9/10 Revision: N° 10 (28/02/2018)

INSECTICIDE RAMPANTS - 863359

14.3 . Transport hazard class(es)

- Classification:



2.1

14.4 . Packing group

-

14.5. Environmental hazards

- Environmentally hazardous material:



14.6. Special precautions for user

ADR/RID	Class	Code	Pack gr.	Label	Ident.	LQ	Provis.	EQ	Cat.	Tunnel
	2	5F	-	2.1	-	1 L	190 327 344 625	E0	2	D
IMDG	Class	2°Label	Pack gr.	LQ	EMS	Provis.	EQ			1
	2	See SP63	-	See SP277	F-D,S-U	63 190 277 327 344 381 959	E0			
IATA	Class	2°Label	Pack gr.	Passager	Passager	Cargo	Cargo	note	EQ	
	2.1	-	-	203	75 kg	203	150 kg	A145 A167 A802	E0	
	2.1	-	-	Y203	30 kg G	-	-	A145 A167 A802	E0	

For limited quantities, see part 2.7 of the OACI/IATA and chapter 3.4 of the ADR and IMDG.

For excepted quantities, see part 2.6 of the OACI/IATA and chapter 3.5 of the ADR and IMDG.

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code No data available.

SECTION 15: REGULATORY INFORMATION

15.1 . Safety, health and environmental regulations/legislation specific for the substance or mixture

- Classification and labelling information included in section 2:

The following regulations have been used:

- Directive 75/324/CEE modified by directive 2013/10/UE
- EU Regulation No. 1272/2008 amended by EU Regulation No. 2016/1179. (ATP $\,9)$
- Container information: No data available.
- **Particular provisions**: No data available.
- Labelling for biocidal products (Regulation 1896/2000, 1687/2002, 2032/2003, 1048/2005, 1849/2006, 1451/2007 and Directive 98/8/EC):

Name	CAS	%	Product-type
CYPHENOTHRIN	39515-40-7	2.30 g/kg	18
(2 ,2-DIMETHYL-3-(2-METHYLPROP-1-			
ENYL			
)CYCLOPROPANECARBOXYLATE DE			
ALPHA-CYANO-3-PHENOXYBENZYLE)			
D-TETRAMETHRINE	1166-46-7	0.75 g/kg	18

Product-type 18: Insecticides, acaricides and products to control other arthropods.

10

Version: N°1 (28/02/2018) Revision: N° 10 (28/02/2018)

Date: 01/03/2018 Page 10/

GISS

INSECTICIDE RAMPANTS - 863359

15.2. Chemical safety assessment

No data available.

SECTION 16: OTHER INFORMATION

Since the user's working conditions are not known by us, the information supplied on this safety data sheet is based on our current level of knowledge and on national and community regulations.

The mixture must not be used for other uses than those specified in section 1 without having first obtained written handling instructions.

It is at all times the responsibility of the user to take all necessary measures to comply with legal requirements and local regulations. The information in this safety data sheet must be regarded as a description of the safety requirements relating to the mixture and not as a guarantee of the properties thereof.

Wording of the phrases mentioned in section 3:

ĕ •	
H220	Extremely flammable gas.
H225	Highly flammable liquid and vapour.
H280	Contains gas under pressure; may explode if heated.
H302	Harmful if swallowed.
H304	May be fatal if swallowed and enters airways.
H319	Causes serious eye irritation.
H336	May cause drowsiness or dizziness.
H400	Very toxic to aquatic life.
H410	Very toxic to aquatic life with long lasting effects.
EUH066	Repeated exposure may cause skin dryness or cracking.

Abbreviations:

ADR: European agreement concerning the international carriage of dangerous goods by Road.

IMDG: International Maritime Dangerous Goods. IATA: International Air Transport Association. ICAO: International Civil Aviation Organisation

RID: Regulations concerning the International carriage of Dangerous goods by rail.

WGK: Wassergefahrdungsklasse (Water Hazard Class).

GHS02 : Flame GHS09 : Environment

PBT: Persistent, bioaccumulable and toxic. vPvB: Very persistent, very bioaccumulable. SVHC: Substances of very high concern.