





Similar to illustration



- M8 sensor/actuator box, 8-way
- 3-pole (1 signal per contact)
- M16 connector (14-pole)
- Green LED operating indicator
- Yellow LED status indicator
- incl. marking strips (WMB markers can also be used)
- incl. M8 protective caps (2 pcs)

Technical data	
Contact resistance (max.)	0.01 Ω
Supply voltage	10 ... 30 VDC; Rated voltage: 32 V ~ rms
Current carrying capacity (signal connections)	2 A
Current carrying capacity (supply connections)	6 A
Rated value of electrical isolation	500 V
Functionally separated potential groups	Kontakt/Kontakt
Insulation resistance	>10 ⁹ Ω
Signal characteristics	PNP
Indicators	LED yellow: Signal status (1 x per contact); LED (U) green: Sensor/actuator box status



Connection data		
Connection technology: inputs/outputs	8 x M8 socket; 3-pole	
Connection technology: trunk cable	1 x M16 plug; 14-pole	
Physical data		
Width	30 mm / 1.181 inches	
Height	26 mm / 1.024 inches	
Depth	152 mm / 5.984 inches	
Mechanical data		
Mounting type	Screw mount	
Weight	141 g	
Material data		
Housing material	PA 66 (UL 94 V0); RAL 7035; silicon and halogen free	
Material properties of the connections	Contact: CuSn, nickel base-coat plating and 0.8 µm gold-plated; Threaded bush: die-cast Zn, nickel-plated; Seal: Viton; 50 mating cycles	
Encapsulation	Fully encapsulated with conformal coating (UL 94 V0)	
Environmental requirements		
Ambient temperature (operation)	-25 ... +80 °C	
Protection type	IP67	
Note on protection type	per EN 60529 (NEMA 6 & 6P) in fully locked position with its plugs or protective caps	
Pollution degree	3 per VDE 0110	
Vibration resistance	per IEC 60068-2-6	
Shock resistance	per IEC 60068-2-27	
Commercial data		
Product Group	23 (I/O passive and accessories)	
eCl@ss 10.0	27-44-01-11	
eCl@ss 9.0	27-44-01-08	
ETIM 9.0	EC003558	
ETIM 8.0	EC003558	
PU (SPU)	1 pcs	
Packaging type	Box	
Country of origin	DE	
GTIN	4044918978699	
Customs tariff number	85366990990	
Environmental Product Compliance		
CAS-No.	7439-92-1	
REACH Candidate List Substance	Lead	
RoHS Compliance Status	Compliant,With Exemption	
RoHS Exemption	6(c)	
SCIP notification number (Austria)	93f172a8-21e0-4301-9fb3-aaeb0cb95761	
SCIP notification number (Belgium)	ea4425fe-333e-45eb-9ec6-9ded6a7223bc	
SCIP notification number (Bulgaria)	c8eda647-26e9-47ee-bda2-e008ebbcecc58	
SCIP notification number (Czech Republic)	7a416f2a-cd42-4d1b-9c91-2716bc306cce	
SCIP notification number (Denmark)	81a866d5-8c15-440a-8142-7f97d006e86b	
SCIP notification number (Finland)	3016e444-3bd3-44f6-b840-d338eac13597	
SCIP notification number (France)	879b8b3e-3171-4789-a4c6-7fa40158cea6	
SCIP notification number (Germany)	7587f86a-5e83-4723-bf2d-f3d608d6a37b	



Environmental Product Compliance	
SCIP notification number (Hungary)	04fbc13b-89c9-4e5c-a2d3-4e0154bcda7b
SCIP notification number (Italy)	41a4560e-9178-402f-a068-a0e2081cc653
SCIP notification number (Netherlands)	54b9903b-b1be-494b-9c1d-bfd9ff9d8368
SCIP notification number (Poland)	421b7591-98d0-44d9-bed5-4c02bc245622
SCIP notification number (Romania)	081173c6-d21e-4925-83f9-a46729116242
SCIP notification number (Sweden)	5a757ef5-ca24-4895-a883-0816184759de

Approvals / Certificates

General approvals



Approval	Standard	Certificate Name
UL UL International Germany GmbH (ORDINARY LOCA- TIONS)	UL 508	E175199 Sec.5