



- NOTES: FINISH (PLATING THICKNESS IN MICRO-INCHES)
1. BRASS PER QQ-B-626
 2. GOLD PL. 3 MIN. THICK OVER NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
 3. BERYLLIUM COPPER PER QQ-C-530
 4. GOLD PL. 30 MIN. THICK OVER NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
 5. TEFLON MIL-P-19468

1. CRIMPED FERRULE
HEX CRIMP SIZE .128"
2. CONTACT PIN TO SOLDER

9	HEAT SHRINK TUBING		BLACK	1	HT-46/4X15
8	FERRULE	COPPER	NOTE 2	1	FR-38/3X7C
7	CONTACT PIN	NOTE 3	NOTE 4	1	SMB6121B2-5-096/04-D
6	SHELL	NOTE 1	NOTE 2	1	SMB5003-1-75
5	RETAINER RING	NOTE 3	NATURAL	1	SMB5003-8-75
4	BARREL	NOTE 1	NOTE 2	1	SMB6121A6-4-23/17
3	INSULATOR	NOTE 5	NATURAL	1	SMB6121A6-3T-75
2	INSULATOR	NOTE 5	NATURAL	1	SMB6121A6-2T-75
1	BODY	NOTE 1	NOTE 2	1	SMB6121A6-1
NO.	DESCRIPTION	MATERIAL	FINISH	Q'TY	DRAWING NO.

DIMENSIONS ARE IN MILLIMETERS			PART NO. SMZ6121A6-3GT30G-6-75	
UNLESS OTHERWISE SPECIFIED TOLERANCES			216121AAA19GE7E	
0.5-6	= ±0.2	APPROVED	DATE 10-11-01'	
6-30	= ±0.4	CHECKED	DATE 10-11-01'	
30-120	= ±0.6	DRAWN	DATE 10-11-01'	
120-315	= ±1	FILE NO		
315-1000	= ±1.6			
1000-2000	= ±2.4			

Amphenol	
TITLE SMZ CRIMP PLUG (FOR RG-179/U, 187A/U)	
DRAWING NO. KJ-SMZ6121A6-3GT30G-179U-75	
ITEM NO.	