










**Position switch, 1N/O+1N/C, wide, IP65\_x, roller plunger**

**Part no.** AT0-11-1-IA/RS  
**Catalog No.** 045561  
**Eaton Catalog No.** AT0-11-1-IA/RS

### Delivery program

|   |    |  |
|---|----|--|
| Basic function  |    | Position switches<br>Safety position switches  |
| Part group reference  |    | AT0  |
| Product range   |    | Roller plunger   |
| Degree of Protection  |    | IP65   |
| Features  |    | Complete unit  |
| Ambient temperature   | °C | -25 - +70  |
| Design  |    | EN 50047 Form C  |
| Approval  |    | <b>totally insulated</b>   |
| <b>Contacts</b>   |    |  |
| N/O = Normally open   |    | 1 N/O  |
| N/C = Normally closed   |    | 1 NC    |
| Notes   |    |  = safety function, by positive opening to IEC/EN 60947-5-1 |
| Contact sequence  |    |   |
| Contact travel  = Contact closed  = Contact open      |    |    |
| Positive opening (ZW)   |    | yes  |
| <b>Colour</b>   |    |  |
| Enclosure covers  |    | Grey   |
| Enclosure covers  |    |    |
| Housing   |    | Insulated material   |
| Connection type   |    | Screw terminal   |
| <b>Notes</b> The operating head can be rotated at 90° intervals to adapt to the specified approach direction.<br>For degree of protection IP65, use V-M20 (206910) cable glands with connecting thread of max. 9 mm length. |    |  |

### Technical data

|                       |                 |  |
|-----------------------|-----------------|--|
| <b>General</b>        |                 |  |
| Standards             |                 | IEC/EN 60947   |
| Climatic proofing     |                 | Damp heat, constant, to IEC 60068-2-78; damp heat, cyclical, to IEC 60068-2-30 |
| Ambient temperature   | °C              | -25 - +70  |
| Mounting position     |                 | As required  |
| Degree of Protection  |                 | IP65   |
| Terminal capacities   | mm <sup>2</sup> |  |
| Solid                 | mm <sup>2</sup> | 1 x (0.75 - 2.5)<br>2 x (0.75 - 1.5)   |
| Flexible with ferrule | mm <sup>2</sup> | 1 x (0.5 - 1.5)<br>2 x (0.5 - 1.5)   |

## Contacts/switching capacity

|  |           |         |          |
|--|-----------|---------|----------|
| Rated impulse withstand voltage          | $U_{imp}$ | V AC    | 6000     |
| Rated insulation voltage                 | $U_i$     | V       | 500      |
| Overvoltage category/pollution degree    |           |         | III/3    |
| Rated operational current                | $I_e$     | A       |          |
| AC-15                                    |           |         |          |
| 24 V                                     | $I_e$     | A       | 10       |
| 220 V 230 V 240 V                        | $I_e$     | A       | 6        |
| 380 V 400 V 415 V                        | $I_e$     | A       | 4        |
| DC-13                                    |           |         |          |
| 24 V                                     | $I_e$     | A       | 10       |
| 110 V                                    | $I_e$     | A       | 1        |
| 220 V                                    | $I_e$     | A       | 0.5      |
| Supply frequency                         |           | Hz      | max. 400 |
| Short-circuit rating to IEC/EN 60947-5-1 |           |         |          |
| max. fuse                                |           | A gG/gL | 6        |
| Repetition accuracy                      |           | mm      | 0.02     |

## Mechanical variables

|  |              |               |             |
|--|--------------|---------------|-------------|
| Lifespan, mechanical                                       | Operations   | $\times 10^6$ | 20          |
| Contact temperature of roller head                         |              | °C            | $\leq 100$  |
| Mechanical shock resistance (half-sinusoidal shock, 20 ms) |              |               |             |
| Standard-action contact                                    |              | g             | 25          |
| Snap-action contact  |              | g             | 2           |
| Operating frequency  | Operations/h |               | $\leq 6000$ |

## Actuation

|  |  |     |  |
|--|--|-----|--|
| Mechanical                                 |  |     |  |
| Actuating force at beginning/end of stroke |  | N   | 1.0/8.0  |
| Actuating torque of rotary drives          |  | Nm  | 0.2  |
| Max. operating speed with DIN cam          |  | m/s | 1/1  |
| <b>Notes</b>                               |  |     | for angle of actuation $\alpha = 0^\circ/30^\circ$ |

## Design verification as per IEC/EN 61439

|  |            |    |  |
|--|------------|----|--|
| Technical data for design verification   |            |    |  |
| Rated operational current for specified heat dissipation   | $I_n$      | A  | 6  |
| Heat dissipation per pole, current-dependent   | $P_{vid}$  | W  | 0.13   |
| Equipment heat dissipation, current-dependent  | $P_{vid}$  | W  | 0  |
| Static heat dissipation, non-current-dependent   | $P_{vs}$   | W  | 0  |
| Heat dissipation capacity  | $P_{diss}$ | W  | 0  |
| Operating ambient temperature min.   |            | °C | -25  |
| Operating ambient temperature max.   |            | °C | 70   |
| IEC/EN 61439 design verification   |            |    |  |
| 10.2 Strength of materials and parts   |            |    |  |
| 10.2.2 Corrosion resistance  |            |    | Meets the product standard's requirements.                         |
| 10.2.3.1 Verification of thermal stability of enclosures   |            |    | Meets the product standard's requirements.                         |
| 10.2.3.2 Verification of resistance of insulating materials to normal heat   |            |    | Meets the product standard's requirements.                         |
| 10.2.3.3 Verification of resistance of insulating materials to abnormal heat and fire due to internal electric effects |            |    | Meets the product standard's requirements.                         |
| 10.2.4 Resistance to ultra-violet (UV) radiation   |            |    | Meets the product standard's requirements.                         |
| 10.2.5 Lifting   |            |    | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.2.6 Mechanical impact   |            |    | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.2.7 Inscriptions  |            |    | Meets the product standard's requirements.                         |
| 10.3 Degree of protection of ASSEMBLIES  |            |    | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.4 Clearances and creepage distances   |            |    | Meets the product standard's requirements.                         |
| 10.5 Protection against electric shock   |            |    | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.6 Incorporation of switching devices and components   |            |    | Does not apply, since the entire switchgear needs to be evaluated. |

|  |  |  |
|--|--|--|
| 10.7 Internal electrical circuits and connections        |  | Is the panel builder's responsibility.   |
| 10.8 Connections for external conductors                 |  | Is the panel builder's responsibility.   |
| 10.9 Insulation properties                               |  |  |
| 10.9.2 Power-frequency electric strength                 |  | Is the panel builder's responsibility.   |
| 10.9.3 Impulse withstand voltage                         |  | Is the panel builder's responsibility.   |
| 10.9.4 Testing of enclosures made of insulating material |  | Is the panel builder's responsibility.   |
| 10.10 Temperature rise                                   |  | The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices. |
| 10.11 Short-circuit rating                               |  | Is the panel builder's responsibility. The specifications for the switchgear must be observed.                                   |
| 10.12 Electromagnetic compatibility                      |  | Is the panel builder's responsibility. The specifications for the switchgear must be observed.                                   |
| 10.13 Mechanical function                                |  | The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.                         |

## Technical data ETIM 7.0

|   |    |  |                    |
|---|----|--|--------------------|
| Sensors (EG000026) / End switch (EC000030)  |    |  |                    |
| Electric engineering, automation, process control engineering / Binary sensor technology, safety-related sensor technology / Position switch / Position switch (Type 1)<br>(ecI@ss10.0.1-27-27-06-01 [AGZ382015]) |    |  |                    |
| Width sensor  | mm |  | 51                 |
| Diameter sensor   | mm |  | 0                  |
| Height of sensor  | mm |  | 51                 |
| Length of sensor  | mm |  | 0                  |
| Rated operation current I <sub>e</sub> at AC-15, 24 V   | A  |  | 10                 |
| Rated operation current I <sub>e</sub> at AC-15, 125 V  | A  |  | 0                  |
| Rated operation current I <sub>e</sub> at AC-15, 230 V  | A  |  | 6                  |
| Rated operation current I <sub>e</sub> at DC-13, 24 V   | A  |  | 10                 |
| Rated operation current I <sub>e</sub> at DC-13, 125 V  | A  |  | 1                  |
| Rated operation current I <sub>e</sub> at DC-13, 230 V  | A  |  | 0.5                |
| Switching function  |    |  | Slow-action switch |
| Switching function latching   |    |  | No                 |
| Output electronic   |    |  | No                 |
| Forced opening  |    |  | Yes                |
| Number of safety auxiliary contacts   |    |  | 1                  |
| Number of contacts as normally closed contact   |    |  | 1                  |
| Number of contacts as normally open contact   |    |  | 1                  |
| Number of contacts as change-over contact   |    |  | 0                  |
| Type of interface   |    |  | None               |
| Type of interface for safety communication  |    |  | None               |
| Construction type housing   |    |  | Cuboid             |
| Material housing  |    |  | Plastic            |
| Coating housing   |    |  | Other              |
| Type of control element   |    |  | Roller cam         |
| Alignment of the control element  |    |  | Other              |
| Type of electric connection   |    |  | Other              |
| With status indication  |    |  | No                 |
| Suitable for safety functions   |    |  | Yes                |
| Explosion safety category for gas   |    |  | None               |
| Explosion safety category for dust  |    |  | None               |
| Ambient temperature during operating  | °C |  | 25 - 70            |
| Degree of protection (IP)   |    |  | IP65               |
| Degree of protection (NEMA)   |    |  | Other              |