

JALAS® 1548 ROUTE+

EN ISO 20345:2011, S3 SRC CI HRO

PROPERTIES

Highest level of protection, excellent grip, perfect fit, extra comfortable, excellent shock absorption

SPECIFICATION

TYPE OF SHOE Safety footwear, low shoes

NAIL PROTECTION MATERIAL Steel

FITTING Wide

SIZE RANGE 36-48

COLLECTION Gran Premio

PLATFORM Enduro

UPPER MATERIAL PU-coated leather, Cordura®

PRONOSE MATERIAL PU

TOECAP MATERIAL Aluminium

LINING MATERIAL Polyester, polyamide

SOLE MATERIAL PU midsole, rubber outsole

INSOLE FX2 Pro

INSOLE MATERIAL Textile, soft EVA, polyester-based conductive thread, double shock absorption zones in Poron® XRD®

FASTENING Laces

COLOUR Black, grey, blue



SIZE	ART. NO.	EAN NO.	SIZE	ART. NO.	EAN NO.
36	1548-36	6408487441851	48	1548-48	6408487441974
37	1548-37	6408487441868			
38	1548-38	6408487441875			
39	1548-39	6408487441882			
40	1548-40	6408487441899			
41	1548-41	6408487441905			
42	1548-42	6408487441912			
43	1548-43	6408487441929			
44	1548-44	6408487441936			
45	1548-45	6408487441943			
46	1548-46	6408487441950			
47	1548-47	6408487441967			

The product features remain unchanged only when insoles recommended by the manufacturer are used. All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.



JALAS® 1548 ROUTE+

FEATURES

ProNose toe reinforcement, wide fit, heat-resistant outsole, oil-resistant outsole, anti-static properties, polstered shaft edge, ventilating insole, water repellent, double shock absorption zones

PRIMARY PROTECTION

Prevents risk of: toe injuries, nail penetration, antistatic

PRIMARY ENVIRONMENTS OF USE

Outdoors, environments with risk for outsole penetration

CE



Aluminium toecap



ErgoShan Shock Absorption System



Nail protection in steel



Anti-static properties



Heat-resistant outsole



Water repellent



Oil-resistant outsole



ProNose toe reinforcement



Wide fit

The product features remain unchanged only when insoles recommended by the manufacturer are used. All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

2015-12-04

ejendals
PROTECTING HANDS AND FEET

EJENDALS AB

Box 7, SE-793 21 Leksand, Sweden

Phone +46 (0) 247 360 00

Fax +46 (0) 247 360 10

info@ejendals.com

order@ejendals.com

www.ejendals.com

JALAS® 1548 ROUTE+

COMPLIANCE
EN ISO 20345:2011

COMPLIANCE DESCRIPTION

SB: Footwear with toe protection tested with 200 J impact and 15kN compression force (includes oil resistant outsole)

S1: Footwear made from leather and other materials excluding all-rubber or all-polymeric footwear + closed seat region + SB + A + E

S2: S1 + WRU

S3: S2 + P

WRU: Water-resistant upper

P: Penetration-resistant outsole

HRO: Heat-resistant outsole compound tested at 300°C

CI: Cold insulation

A: Electrical resistance (between 0.1-1000 Mega Ohms)

E: Energy absorption in the heel area (tested at 20 Joules)

SRA: Slip-resistance on ceramic tile floor with Sodium lauryl sulphate solution

SRB: Slip-resistance on steel floor with glycerol

SRC: SRA + SRB

BGR 191: Orthopedic footwear adjustment according to German BGR 191. Footwear is tested with adjusted orthopedic insoles in accordance with EN ISO 20345 standard



CE



Aluminium toecap



Ergothan Shock Absorption System



Nail protection in steel



Anti-static properties



Heat-resistant outsole



Water repellent



Oil-resistant outsole



ProNose toe reinforcement



Wide fit

The product features remain unchanged only when insoles recommended by the manufacturer are used. All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

2015-12-04

3(3)

ejendals
PROTECTING HANDS AND FEET

EJENDALS AB

Box 7, SE-793 21 Leksand, Sweden

Phone +46 (0) 247 360 00

Fax +46 (0) 247 360 10

info@ejendals.com

order@ejendals.com

www.ejendals.com