

Dot laser, green, 520 nm, 5 mW

DG520-5-5(8x35)-QCW
Order Number: 70118445

Main Parameters (*)	min	typ	max	Unit
Wavelength	510	520	525	nm
Optical Output Power		5		mW
Operating Voltage	4.7	5	5.3	V DC
Operating Current	120	150	200	mA
Operating Temperature	-10		60	°C
Storage Temperature	-40		80	°C

Main Data

Warranty 1 years

Technical Parameters

Lifetime > 6,000 h
RoHS yes

Optical Parameters

Beam Shape	Dot
Laser Class	3R
Divergence	G - 0.8 mrad
Size of Laserdot	<8mm@10m
Operating Distance	30 m
Optics	glass lens AR coated
Laser technology	Single Mode Diode
Stability	+/- 3% @ -10-50°C
Focus	collimated
internal modulation frequency	1 kHz

Electrical Parameters

Potential of Housing isolated

Mechanical Parameters

Size	Ø8x35 mm
Material	aluminium
Cable length	100 mm
Wire type	26AWG, 0,14mm ²
Output Aperture	3 mm
Housing Color	black
Weight	16 g
Stripping of wire	5 mm

(*) Over the complete operating temperature range

Features



- Operating Voltage 5 V DC
- Compact size
- Laser Class 3R
- High Power
- Fixed focus


Picture



Cable color

Ground		blue	GND
positive		red	4.7 - 5.3, typ 5 V DC

Safety Label



Valid Revision

22 | 11-FEB-2019