



**SAFETY DATA SHEET**  
SAPPHIRE EXTREME

Page: 1

Compilation date: 10/09/2014

Revision No: 5

**Section 1: Identification of the substance/mixture and of the company/undertaking**

**1.1. Product identifier**

**Product name:** SAPPHIRE EXTREME

**1.2. Relevant identified uses of the substance or mixture and uses advised against**

**Use of substance / mixture:** PC24: Lubricants, greases, release products.

**1.3. Details of the supplier of the safety data sheet**

**Company name:** ROCOL

ROCOL House

Swillington

Leeds

West Yorkshire

LS26 8BS

ENGLAND

**Tel:** +44 (0) 113 232 2700

**Fax:** +44 (0) 113 232 2740

**Email:** [customer-service@rocol.com](mailto:customer-service@rocol.com)

**1.4. Emergency telephone number**

**Emergency tel:** +44 (0) 113 232 2600

**Section 2: Hazards identification**

**2.1. Classification of the substance or mixture**

**Classification under CLP:** This product has no classification under CLP.

**2.2. Label elements**

**Label elements:** This product has no label elements.

**2.3. Other hazards**

**PBT:** This product is not identified as a PBT/vPvB substance.

**Section 3: Composition/information on ingredients**

**3.2. Mixtures**

**Hazardous ingredients:**

[cont...]

# SAFETY DATA SHEET

SAPPHIRE EXTREME

Page: 2

SOLVENT REFINED BASE OIL (NOTE L- LESS THAN 3% DMSO EXTRACT)

EINECS	CAS	CHIP Classification	CLP Classification	Percent
265-166-0	64742-62-7	Substance with a Community workplace exposure limit.	-	30-50%

LUBRICATING OILS (LESS THAN 3% DMSO EXTRACT)

278-012-2	74869-22-0	Substance with a Community workplace exposure limit.	-	30-50%
-----------	------------	--	---	--------

PROPYLENE CARBONATE

203-572-1	108-32-7	-	Eye Irrit. 2: H319	2-10%
-----------	----------	---	--------------------	-------

## Section 4: First aid measures

### 4.1. Description of first aid measures

**Skin contact:** Wash immediately with plenty of soap and water.

**Eye contact:** Bathe the eye with running water for 15 minutes.

**Ingestion:** Wash out mouth with water.

### 4.2. Most important symptoms and effects, both acute and delayed

**Skin contact:** There may be mild irritation at the site of contact.

**Eye contact:** There may be irritation and redness.

**Ingestion:** There may be irritation of the throat.

**Inhalation:** No symptoms.

### 4.3. Indication of any immediate medical attention and special treatment needed

## Section 5: Fire-fighting measures

### 5.1. Extinguishing media

**Extinguishing media:** Use water spray to cool containers. Suitable extinguishing media for the surrounding fire should be used.

### 5.2. Special hazards arising from the substance or mixture

**Exposure hazards:** In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

### 5.3. Advice for fire-fighters

**Advice for fire-fighters:** Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

## Section 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

**Personal precautions:** Refer to section 8 of SDS for personal protection details.

[cont...]

# SAFETY DATA SHEET

SAPPHIRE EXTREME

Page: 3

## 6.2. Environmental precautions

**Environmental precautions:** Do not discharge into drains or rivers.

## 6.3. Methods and material for containment and cleaning up

**Clean-up procedures:** Transfer to a closable, labelled salvage container for disposal by an appropriate method.

## 6.4. Reference to other sections

## Section 7: Handling and storage

### 7.1. Precautions for safe handling

**Handling requirements:** Avoid direct contact with the substance.

### 7.2. Conditions for safe storage, including any incompatibilities

**Storage conditions:** Store in a cool, well ventilated area.

**Suitable packaging:** Must only be kept in original packaging.

### 7.3. Specific end use(s)

## Section 8: Exposure controls/personal protection

### 8.1. Control parameters

**Hazardous ingredients:**

**SOLVENT REFINED BASE OIL (NOTE L- LESS THAN 3% DMSO EXTRACT)**

**Workplace exposure limits:**

**Respirable dust**

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
EU	-	5 mg/m <sup>3</sup>	-	-

**LUBRICATING OILS (LESS THAN 3% DMSO EXTRACT)**

UK	5mg/m <sup>3</sup>	10mg/m <sup>3</sup>	-	-
----	--------------------	---------------------	---	---

### DNEL/PNEC Values

**DNEL / PNEC** No data available.

### 8.2. Exposure controls

**Respiratory protection:** Respiratory protection not normally required.

**Hand protection:** Gloves (oil-resistant). Nitrile gloves.

**Eye protection:** Safety glasses with side-shields.

**Skin protection:** Protective clothing.

## Section 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

**State:** Paste

[cont...]

# SAFETY DATA SHEET

SAPPHIRE EXTREME

Page: 4

**Colour:** Blue-black

**Odour:** Odourless

**Evaporation rate:** Negligible

**Oxidising:** Non-oxidising (by EC criteria)

**Solubility in water:** Insoluble

**Viscosity:** Highly viscous

**Melting point/range°C:** > 200

**Flash point°C:** > 200

**Autoflammability°C:** > 200

**Relative density:** < 1

## 9.2. Other information

**Other information:** No data available.

## Section 10: Stability and reactivity

### 10.1. Reactivity

### 10.2. Chemical stability

**Chemical stability:** Stable under normal conditions.

### 10.3. Possibility of hazardous reactions

### 10.4. Conditions to avoid

**Conditions to avoid:** Heat.

### 10.5. Incompatible materials

**Materials to avoid:** Strong oxidising agents. Strong reducing agents.

### 10.6. Hazardous decomposition products

**Haz. decomp. products:** In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

## Section 11: Toxicological information

### 11.1. Information on toxicological effects

**Hazardous ingredients:**

#### PROPYLENE CARBONATE

ORL	MUS	LD50	20700	mg/kg
ORL	RAT	LD50	29100	µl/kg

**Toxicity values:** No data available.

### Symptoms / routes of exposure

**Skin contact:** There may be mild irritation at the site of contact.

**Eye contact:** There may be irritation and redness.

**Ingestion:** There may be irritation of the throat.

**Inhalation:** No symptoms.

[cont...]

# SAFETY DATA SHEET

SAPPHIRE EXTREME

Page: 5

## Section 12: Ecological information

### 12.1. Toxicity

**Ecotoxicity values:** No data available.

### 12.2. Persistence and degradability

**Persistence and degradability:** Only slightly biodegradable.

### 12.3. Bioaccumulative potential

**Bioaccumulative potential:** No bioaccumulation potential.

### 12.4. Mobility in soil

**Mobility:** Non-volatile. Absorbed only slowly into soil.

### 12.5. Results of PBT and vPvB assessment

**PBT identification:** This product is not identified as a PBT/vPvB substance.

### 12.6. Other adverse effects

## Section 13: Disposal considerations

### 13.1. Waste treatment methods

**Disposal of packaging:** Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.

**NB:** The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

## Section 14: Transport information

**Transport class:** This product does not require a classification for transport.

## Section 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

### 15.2. Chemical Safety Assessment

## Section 16: Other information

### Other information

**Other information:** This safety data sheet is prepared in accordance with Commission Regulation (EU) No 453/2010.

Compiled in accordance with REACH.

**Phrases used in s.2 and s.3:** H319: Causes serious eye irritation.

**Legend to abbreviations:** PNEC = predicted no effect level

DNEL = derived no effect level

LD50 = median lethal dose

LC50 = median lethal concentration

EC50 = median effective concentration

[cont...]

## SAFETY DATA SHEET

SAPPHIRE EXTREME

Page: 6

IC50 = median inhibitory concentration

dw = dry weight

bw = body weight

cc = closed cup

oc = open cup

MUS = mouse

GPG = guinea pig

RBT = rabbit

HAM = hamster

HMN = human

MAM = mammal

PGN = pigeon

IVN = intravenous

SCU = subcutaneous

SKN = skin

DRM = dermal

OCC = ocular/corneal

PCP = physico-chemical properties

**Legal disclaimer:** The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.