

## LD40 diamond cutting disc – ideal for flexible applications in soft to hard materials

Segment height 12.0 mm

# RHODIUS

### Application:

For cutting reinforced concrete, stone and similar materials. Suitable for wet and dry sanding

### Execution:

- Laser-welded
- Segmented
- Reducing rings for bore diameters 20.0 mm and 22.2 mm are included with each 300 mm and 350 mm disc



<b>Art. no.</b>	<b>76119 180</b>
<b>Brand</b>	RHODIUS
<b>Manufacturer Part Number</b>	302452
<b>Washer diameter</b>	180 mm
<b>Washer thickness</b>	2.4 mm
<b>Bore diameter</b>	22.23 mm
<b>Max. rotation speed</b>	8500 rpm
<b>Form</b>	Straight
<b>Number of pieces per packet</b>	1 PCS
<b>Material to be processed</b>	Stone, Concrete
<b>Gross Weight</b>	0.300 kg
<b>Product Group</b>	6BB

### EAN

4011890050330