

SECTION 1: Identification of the substance/mixture and of the company/undertaking

- **1.1 Product identifier**
- **Trade name:** PLASTI-KOTE® LEAK DETECTOR 300 ML
- **Article number:** 440.0071028.076
- **1.2 Relevant identified uses of the substance or mixture and uses advised against**
No further relevant information available.
- **Sector of Use**
SU21 Consumer uses: Private households / general public / consumers
SU22 Professional uses: Public domain (administration, education, entertainment, services, craftsmen)
- **Product category**
PC0 Other
UCN R15100
- **Process category**
PROC7 Industrial spraying
PROC11 Non industrial spraying
- **Application of the substance / the mixture** Preparation
- **1.3 Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
MOTIP DUPLI B.V.
Wolfraamweg 2
NL-8471 XC Wolvega
Nederland
Tel : +31 (0)561 694400
Fax: +31 (0)561 694411
e-mail: info@nl.motipdupli.com
- **Further information obtainable from:** Department Product Safety
- **1.4 Emergency telephone number:** +31 (0)561-694400 (09:00h - 17:00h)

SECTION 2: Hazards identification

- **2.1 Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**



GHS08 health hazard

STOT RE 2 H373 May cause damage to the kidneys through prolonged or repeated exposure. Route of exposure: Oral.



GHS07

Eye Irrit. 2 H319 Causes serious eye irritation.

Aerosol 3 H229 Pressurised container: May burst if heated.

- **2.2 Label elements**
- **Labelling according to Regulation (EC) No 1272/2008**
The product is classified and labelled according to the CLP regulation.

(Contd. on page 2)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 22.06.2018

Version number 110

Revision: 18.12.2017

Trade name: PLASTI-KOTE® LEAK DETECTOR 300 ML

(Contd. of page 1)

· **Hazard pictograms**

GHS07 GHS08

· **Signal word** Warning· **Hazard-determining components of labelling:**

ethanediol

· **Hazard statements**

H229 Pressurised container: May burst if heated.

H319 Causes serious eye irritation.

H373 May cause damage to the kidneys through prolonged or repeated exposure. Route of exposure: Oral.

· **Precautionary statements**

P101 If medical advice is needed, have product container or label at hand.

P102 Keep out of reach of children.

P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

P251 Do not pierce or burn, even after use.

P260 Do not breathe spray.

P410+P412 Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.

P501 Dispose of contents / container in accordance with regional regulations.

· **2.3 Other hazards**· **Results of PBT and vPvB assessment**· **PBT:** Not applicable.· **vPvB:** Not applicable.* **SECTION 3: Composition/information on ingredients**· **3.2 Chemical characterisation: Mixtures**· **Description:** Mixture of substances listed below with nonhazardous additions.· **Dangerous components:**

CAS: 107-21-1 EINECS: 203-473-3 Index number: 603-027-00-1 Reg.nr.: 01-2119456816-28	ethanediol	STOT RE 2, H373 Acute Tox. 4, H302	12.5-<20%
CAS: 97043-91-9 EC number: 619-252-3	Alcohols, C9-C16, ethoxylated	Eye Dam. 1, H318 Acute Tox. 4, H302	<2.5%

· **Additional information:** For the wording of the listed hazard phrases refer to section 16.* **SECTION 4: First aid measures**· **4.1 Description of first aid measures**· **General information:**

Symptoms of poisoning may even occur after several hours; therefore medical observation for at least 48 hours after the accident.

· **After inhalation:** Supply fresh air; consult doctor in case of complaints.· **After skin contact:** Generally the product does not irritate the skin.· **After eye contact:**

Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.

· **After swallowing:** Drink plenty of water and provide fresh air. Call for a doctor immediately.· **4.2 Most important symptoms and effects, both acute and delayed** No further relevant information available.

(Contd. on page 3)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 22.06.2018

Version number 110

Revision: 18.12.2017

Trade name: PLASTI-KOTE® LEAK DETECTOR 300 ML

(Contd. of page 2)

- **4.3 Indication of any immediate medical attention and special treatment needed**
No further relevant information available.

SECTION 5: Firefighting measures

- **5.1 Extinguishing media**
- **Suitable extinguishing agents:**
CO₂, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.
- **5.2 Special hazards arising from the substance or mixture**
During heating or in case of fire poisonous gases are produced.
- **5.3 Advice for firefighters -**
- **Protective equipment:** Mouth respiratory protective device.

SECTION 6: Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures**
Mount respiratory protective device.
Wear protective equipment. Keep unprotected persons away.
- **6.2 Environmental precautions:** Do not allow to enter sewers/ surface or ground water.
- **6.3 Methods and material for containment and cleaning up:**
Dispose contaminated material as waste according to item 13.
Ensure adequate ventilation.
- **6.4 Reference to other sections**
No dangerous substances are released.
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.

SECTION 7: Handling and storage

- **7.1 Precautions for safe handling** Ensure good ventilation/exhaustion at the workplace.
- **Information about fire - and explosion protection:**
Do not spray onto a naked flame or any incandescent material.
Keep ignition sources away - Do not smoke.
Keep respiratory protective device available.
Pressurised container: protect from sunlight and do not expose to temperatures exceeding 50°C, i.e. electric lights. Do not pierce or burn, even after use.
- **7.2 Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:**
Observe official regulations on storing packagings with pressurised containers.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** Keep container tightly sealed.
- **Storage class:** 2 B
- **7.3 Specific end use(s)** No further relevant information available.

SECTION 8: Exposure controls/personal protection

- **Additional information about design of technical facilities:** No further data; see item 7.

(Contd. on page 4)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 22.06.2018

Version number 110

Revision: 18.12.2017

Trade name: **PLASTI-KOTE® LEAK DETECTOR 300 ML**

(Contd. of page 3)

· **8.1 Control parameters**

· **Ingredients with limit values that require monitoring at the workplace:**

107-21-1 ethanediol

WEL	Short-term value: 104** mg/m ³ , 40** ppm
	Long-term value: 10* 52** mg/m ³ , 20** ppm
	Sk *particulate **vapour

· **Additional information:** The lists valid during the making were used as basis.

· **8.2 Exposure controls**

· **Personal protective equipment:**

· **General protective and hygienic measures:**

Keep away from foodstuffs, beverages and feed.

Immediately remove all soiled and contaminated clothing

Wash hands before breaks and at the end of work.

Store protective clothing separately.

Do not inhale gases / fumes / aerosols.

Avoid contact with the eyes and skin.

Avoid contact with the eyes.

· **Respiratory protection:**

In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use self-contained respiratory protective device.

· **Protection of hands:**



Protective gloves

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

· **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

· **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

· **Eye protection:**



Tightly sealed goggles

SECTION 9: Physical and chemical properties

· **9.1 Information on basic physical and chemical properties**

· **General Information**

· **Appearance:**

Form: Aerosol

Colour: According to product specification

· **Odour:** Odourless

· **Odour threshold:** Not determined.

(Contd. on page 5)

GB

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 22.06.2018

Version number 110

Revision: 18.12.2017

Trade name: **PLASTI-KOTE® LEAK DETECTOR 300 ML**

(Contd. of page 4)

· pH-value at 20 °C (68 °F):	7.1
· Change in condition	
Melting point/freezing point:	Undetermined.
Initial boiling point and boiling range:	Not applicable, as aerosol.
· Flash point:	>65 °C (>149 °F) Not applicable, as aerosol.
· Flammability (solid, gas):	Not applicable.
· Ignition temperature:	398 °C (748.4 °F)
· Decomposition temperature:	Not determined.
· Auto-ignition temperature:	Product is not selfigniting.
· Explosive properties:	Not determined.
· Explosion limits:	
Lower:	3.2 Vol %
Upper:	53 Vol %
· Vapour pressure at 20 °C (68 °F):	8,500 hPa (6,375.5 mm Hg)
· Density at 20 °C (68 °F):	1.02 g/cm ³ (8.51 lbs/gal)
· Relative density	Not determined.
· Vapour density	Not determined.
· Evaporation rate	Not applicable.
· Solubility in / Miscibility with water:	Not miscible or difficult to mix.
· Partition coefficient: n-octanol/water:	Not determined.
· Viscosity:	
Dynamic:	Not determined.
Kinematic:	Not determined.
· Solvent content:	
Water:	77.9 %
VOC (EC)	---
Solids content:	5.0 %
· 9.2 Other information	No further relevant information available.

SECTION 10: Stability and reactivity

- **10.1 Reactivity** No further relevant information available.
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known.
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** No dangerous decomposition products known.

SECTION 11: Toxicological information

- **11.1 Information on toxicological effects**
- **Acute toxicity** Based on available data, the classification criteria are not met.
- **Primary irritant effect:**
- **Skin corrosion/irritation** Based on available data, the classification criteria are not met.

(Contd. on page 6)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 22.06.2018

Version number 110

Revision: 18.12.2017

Trade name: PLASTI-KOTE® LEAK DETECTOR 300 ML

(Contd. of page 5)

- **Serious eye damage/irritation**
Causes serious eye irritation.
- **Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.
- **CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)**
- **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
- **Carcinogenicity** Based on available data, the classification criteria are not met.
- **Reproductive toxicity** Based on available data, the classification criteria are not met.
- **STOT-single exposure** Based on available data, the classification criteria are not met.
- **STOT-repeated exposure**
May cause damage to the kidneys through prolonged or repeated exposure. Route of exposure: Oral.
- **Aspiration hazard** Based on available data, the classification criteria are not met.

SECTION 12: Ecological information

- **12.1 Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **General notes:**
Water hazard class 1 (German Regulation) (Self-assessment): slightly hazardous for water
Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.
- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **12.6 Other adverse effects** No further relevant information available.

SECTION 13: Disposal considerations

- **13.1 Waste treatment methods**
- **Recommendation**
Must not be disposed together with household garbage. Do not allow product to reach sewage system.

· **European waste catalogue**

15 01 04	metallic packaging
----------	--------------------

- **Uncleaned packaging:**
- **Recommendation:** Non contaminated packagings may be recycled.

SECTION 14: Transport information

- | | |
|---------------------------------------|-------------------------|
| · 14.1 UN-Number | |
| · ADR, IMDG, IATA | UN1950 |
| · 14.2 UN proper shipping name | |
| · ADR | 1950 AEROSOLS |
| · IMDG | AEROSOLS |
| · IATA | AEROSOLS, non-flammable |

(Contd. on page 7)

GB

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 22.06.2018

Version number 110

Revision: 18.12.2017

Trade name: **PLASTI-KOTE® LEAK DETECTOR 300 ML**

(Contd. of page 6)

· **14.3 Transport hazard class(es)**· **ADR**

· **Class** 2 5A Gases.
· **Label** 2.2

· **IMDG, IATA**

· **Class** 2.2
· **Label** 2.2

· **14.4 Packing group**

· **ADR, IMDG, IATA** not regulated

· **14.5 Environmental hazards:**

Not applicable.

· **14.6 Special precautions for user**

Warning: Gases.

· **Danger code (Kemler):**

-

· **EMS Number:**

F-D,S-U

· **Stowage Code**

SW1 Protected from sources of heat.

SW22 For AEROSOLS with a maximum capacity of 1 litre: Category A. For AEROSOLS with a capacity above 1 litre: Category B. For WASTE AEROSOLS: Category C, Clear of living quarters.

· **Segregation Code**

SG69 For AEROSOLS with a maximum capacity of 1 litre: Segregation as for class 9. Stow "separated from" class 1 except for division 1.4. For AEROSOLS with a capacity above 1 litre: Segregation as for the appropriate subdivision of class 2. For WASTE AEROSOLS: Segregation as for the appropriate subdivision of class 2.

· **14.7 Transport in bulk according to Annex II of Marpol and the IBC Code**

Not applicable.

· **Transport/Additional information:**· **ADR**· **Limited quantities (LQ)**

1L

· **Excepted quantities (EQ)**

Code: E0

Not permitted as Excepted Quantity

Code: E0

Not permitted as Excepted Quantity

· **Transport category**

3

· **Tunnel restriction code**

E

· **IMDG**· **Limited quantities (LQ)**

1L

· **Excepted quantities (EQ)**

Code: E0

Not permitted as Excepted Quantity

Code: E0

Not permitted as Excepted Quantity

(Contd. on page 8)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 22.06.2018

Version number 110

Revision: 18.12.2017

Trade name: PLASTI-KOTE® LEAK DETECTOR 300 ML

(Contd. of page 7)

· **UN "Model Regulation":** UN 1950 AEROSOLS, 2.2

SECTION 15: Regulatory information

· **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**

· **Directive 2012/18/EU**

· **Named dangerous substances - ANNEX I** None of the ingredients is listed.

· **REGULATION (EC) No 1907/2006 ANNEX XVII** Conditions of restriction: 3

· **National regulations:**

· **Other regulations, limitations and prohibitive regulations**

· **Substances of very high concern (SVHC) according to REACH, Article 57**

None of the ingredients is listed.

· **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· **Relevant phrases**

H302 Harmful if swallowed.

H318 Causes serious eye damage.

H373 May cause damage to the kidneys through prolonged or repeated exposure. Route of exposure: Oral.

· **Abbreviations and acronyms:**

RID: Règlement international concernant le transport des marchandises dangereuses par chemin de fer (Regulations Concerning the International Transport of Dangerous Goods by Rail)

ICAO: International Civil Aviation Organisation

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

GHS: Globally Harmonised System of Classification and Labelling of Chemicals

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

VOC: Volatile Organic Compounds (USA, EU)

PBT: Persistent, Bioaccumulative and Toxic

SVHC: Substances of Very High Concern

vPvB: very Persistent and very Bioaccumulative

Aerosol 3: Aerosols – Category 3

Acute Tox. 4: Acute toxicity – Category 4

Eye Dam. 1: Serious eye damage/eye irritation – Category 1

Eye Irrit. 2: Serious eye damage/eye irritation – Category 2

STOT RE 2: Specific target organ toxicity (repeated exposure) – Category 2

· *** Data compared to the previous version altered.**