

# CLEENOL

For a cleaner, safer world

## SAFETY DATA SHEET LEMON DISINFECTANT

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

Product name	LEMON DISINFECTANT
Internal identification	062302X5
Container size	2x5L

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses	Disinfectant.
-----------------	---------------

#### 1.3. Details of the supplier of the safety data sheet

Supplier	Cleenol Group Ltd Neville House Beaumont Road Banbury Oxon OX16 1RB UK Tel: +44 (0)1295 251721 sales@cleenol.co.uk
----------	---

#### 1.4. Emergency telephone number

Emergency telephone	In case of a medical emergency following exposure to a chemical, call NHS Direct in England or Wales 0845 46 47 or NHS 24 in Scotland 08454 24 24 24 (UK only).
---------------------	---

### SECTION 2: Hazards identification

#### 2.1. Classification of the substance or mixture

##### Classification (EC 1272/2008)

Physical hazards	Not Classified
Health hazards	Skin Irrit. 2 - H315 Eye Irrit. 2 - H319
Environmental hazards	Aquatic Chronic 3 - H412

#### 2.2. Label elements

##### Hazard pictograms



Signal word	Warning
Hazard statements	H315 Causes skin irritation. H319 Causes serious eye irritation. H412 Harmful to aquatic life with long lasting effects.

## LEMON DISINFECTANT

<b>Precautionary statements</b>	<p>P273 Avoid release to the environment.</p> <p>P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.</p> <p>P302+P352 IF ON SKIN: Wash with plenty of water.</p> <p>P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.</p> <p>P332+P313 If skin irritation occurs: Get medical advice/ attention.</p> <p>P362+P364 Take off contaminated clothing and wash it before reuse.</p>
<b>Detergent labelling</b>	Contains CITRAL
<b>Supplementary precautionary statements</b>	<p>P264 Wash contaminated skin thoroughly after handling.</p> <p>P321 Specific treatment (see medical advice on this label).</p> <p>P337+P313 If eye irritation persists: Get medical advice/ attention.</p> <p>P501 Dispose of contents/ container in accordance with national regulations.</p>

### 2.3. Other hazards

#### SECTION 3: Composition/information on ingredients

##### 3.2. Mixtures

<p>Alkyl (C12-16) dimethylbenzyl ammonium chloride (ADBAC/BKC (C12-16))</p> <p>CAS number: 68424-85-1                      EC number: 270-325-2</p> <p>M factor (Acute) = 10                              M factor (Chronic) = 1</p>	<b>1.3%</b>
<p><b>Classification</b></p> <p>Acute Tox. 4 - H302</p> <p>Skin Corr. 1A - H314</p> <p>Eye Dam. 1 - H318</p> <p>Aquatic Acute 1 - H400</p> <p>Aquatic Chronic 1 - H410</p>	

The full text for all hazard statements is displayed in Section 16.

#### SECTION 4: First aid measures

##### 4.1. Description of first aid measures

<b>Inhalation</b>	Unlikely route of exposure as the product does not contain volatile substances.
<b>Ingestion</b>	Do not induce vomiting unless under the direction of medical personnel. Rinse mouth thoroughly with water. Give plenty of water to drink. Give milk instead of water if readily available. Keep affected person under observation. Get medical attention if a large quantity has been ingested.
<b>Skin contact</b>	Remove contaminated clothing. Wash skin thoroughly with soap and water. Get medical attention if symptoms are severe or persist after washing.
<b>Eye contact</b>	Rinse cautiously with water for several minutes. Remove any contact lenses and open eyelids wide apart. Continue to rinse. Get medical attention if any discomfort continues.

##### 4.2. Most important symptoms and effects, both acute and delayed

<b>Inhalation</b>	No adverse effects known. Considered to be a low inhalation hazard at normal workplace temperatures.
<b>Ingestion</b>	No adverse effects known. May be harmful if swallowed.
<b>Skin contact</b>	Causes skin irritation.
<b>Eye contact</b>	Causes serious eye irritation.

## LEMON DISINFECTANT

### 4.3. Indication of any immediate medical attention and special treatment needed

Notes for the doctor No specific recommendations.

Specific treatments Treat symptomatically.

### SECTION 5: Firefighting measures

#### 5.1. Extinguishing media

Suitable extinguishing media The product is not flammable. Use fire-extinguishing media suitable for the surrounding fire.

Unsuitable extinguishing media None known.

#### 5.2. Special hazards arising from the substance or mixture

Specific hazards Irritating gases or vapours.

#### 5.3. Advice for firefighters

Protective actions during firefighting No specific firefighting precautions known.

Special protective equipment for firefighters Wear chemical protective suit.

### SECTION 6: Accidental release measures

#### 6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions Avoid contact with eyes and prolonged skin contact. Do not touch or walk into spilled material. Take care as floors and other surfaces may become slippery. Wash thoroughly after dealing with a spillage.

#### 6.2. Environmental precautions

Environmental precautions Harmful to aquatic life with long lasting effects. Avoid discharge to the aquatic environment.

#### 6.3. Methods and material for containment and cleaning up

Methods for cleaning up Absorb in vermiculite, dry sand or earth and place into containers. Flush contaminated area with plenty of water. Avoid contamination of ponds or watercourses with washing down water. Discharge of small quantities to the sewer with plenty of water may be permitted.

#### 6.4. Reference to other sections

Reference to other sections For personal protection, see Section 8. For waste disposal, see Section 13.

### SECTION 7: Handling and storage

#### 7.1. Precautions for safe handling

Usage precautions For professional users only. Avoid contact with eyes and prolonged skin contact. Do not breathe spray. Avoid spilling. Avoid release to the environment.

Advice on general occupational hygiene Wash contaminated skin thoroughly after handling.

#### 7.2. Conditions for safe storage, including any incompatibilities

Storage precautions Store in tightly-closed, original container. Keep containers upright. Store at room temperature. Protect from freezing and direct sunlight.

Storage class Chemical storage.

## LEMON DISINFECTANT

### 7.3. Specific end use(s)

**Specific end use(s)** The identified uses for this product are detailed in Section 1.2. Refer to Product Use Guide (PUG) for further information.

### SECTION 8: Exposure controls/Personal protection

#### 8.1. Control parameters

**Ingredient comments** No exposure limits known for ingredient(s).

#### 8.2. Exposure controls

##### Protective equipment



**Appropriate engineering controls** No specific ventilation requirements.

**Eye/face protection** Eyewear complying with an approved standard should be worn if a risk assessment indicates eye contact is possible.

**Hand protection** It is recommended that chemical-resistant, impervious gloves are worn. Wear protective gloves made of the following material: Rubber (natural, latex). Nitrile rubber. Polyvinyl chloride (PVC). To protect hands from chemicals, gloves should comply with European Standard EN374.

**Hygiene measures** Wash contaminated skin thoroughly after handling.

**Respiratory protection** No specific requirements are anticipated under normal conditions of use.

**Environmental exposure controls** Keep container tightly sealed when not in use. Residues and empty containers should be taken care of as hazardous waste according to local and national provisions.

### SECTION 9: Physical and chemical properties

#### 9.1. Information on basic physical and chemical properties

<b>Appearance</b>	Clear liquid.
<b>Colour</b>	Yellow.
<b>Odour</b>	Lemon.
<b>pH</b>	pH (concentrated solution): 6.5 - 7.5
<b>Initial boiling point and range</b>	100°C
<b>Flash point</b>	Not applicable.
<b>Relative density</b>	1.00 @ 20°C
<b>Solubility(ies)</b>	Soluble in water.
<b>Auto-ignition temperature</b>	Not applicable.
<b>Decomposition Temperature</b>	Not determined.
<b>Viscosity</b>	Non-viscous.
<b>Explosive properties</b>	Not applicable.
<b>Oxidising properties</b>	Does not meet the criteria for classification as oxidising.

## LEMON DISINFECTANT

### 9.2. Other information

Refractive index	1.5 - 2.5
Volatile organic compound	Not applicable.

### SECTION 10: Stability and reactivity

#### 10.1. Reactivity

Reactivity	There are no known reactivity hazards associated with this product.
------------	---

#### 10.2. Chemical stability

Stability	Stable at normal ambient temperatures and when used as recommended.
-----------	---

#### 10.3. Possibility of hazardous reactions

Possibility of hazardous reactions	Under normal conditions of storage and use, no hazardous reactions will occur.
------------------------------------	--

#### 10.4. Conditions to avoid

Conditions to avoid	There are no known conditions that are likely to result in a hazardous situation.
---------------------	---

#### 10.5. Incompatible materials

Materials to avoid	No specific material or group of materials is likely to react with the product to produce a hazardous situation.
--------------------	--

#### 10.6. Hazardous decomposition products

Hazardous decomposition products	Does not decompose when used and stored as recommended.
----------------------------------	---

### SECTION 11: Toxicological information

#### 11.1. Information on toxicological effects

Toxicological effects	Information given is based on data of the components and of similar products.
-----------------------	---

#### Acute toxicity - oral

ATE oral (mg/kg)	40,000.0
------------------	----------

#### Skin corrosion/irritation

Skin corrosion/irritation	Causes skin irritation.
---------------------------	-------------------------

#### Extreme pH

Moderate pH (> 2 and < 11.5).

#### Serious eye damage/irritation

Serious eye damage/irritation	Causes serious eye irritation.
-------------------------------	--------------------------------

#### Inhalation

Considered to be a low inhalation hazard at normal workplace temperatures.

#### Ingestion

No harmful effects expected from quantities likely to be ingested by accident.

#### Skin contact

Causes skin irritation.

#### Eye contact

Causes serious eye irritation.

#### Route of exposure

Skin and/or eye contact

### SECTION 12: Ecological information

Ecotoxicity	Harmful to aquatic life with long lasting effects.
-------------	--

## LEMON DISINFECTANT

### 12.1. Toxicity

Toxicity Harmful to Aquatic Organisms

### 12.2. Persistence and degradability

Persistence and degradability Moderately biodegradable.

### 12.3. Bioaccumulative potential

Bioaccumulative potential The product does not contain any substances expected to be bioaccumulating.

### 12.4. Mobility in soil

Mobility The product is water-soluble and may spread in water systems.

### 12.5. Results of PBT and vPvB assessment

Results of PBT and vPvB assessment This product does not contain any substances classified as PBT or vPvB.

### 12.6. Other adverse effects

Other adverse effects None known.

## SECTION 13: Disposal considerations

### 13.1. Waste treatment methods

General information Dispose of surplus products and those that cannot be recycled via a licensed waste disposal contractor.

Disposal methods Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority.

## SECTION 14: Transport information

General The product is not covered by international regulations on the transport of dangerous goods (IMDG, IATA, ADR/RID).

### 14.1. UN number

Not applicable.

### 14.2. UN proper shipping name

Not applicable.

### 14.3. Transport hazard class(es)

No transport warning sign required.

### 14.4. Packing group

Not applicable.

### 14.5. Environmental hazards

Environmentally hazardous substance/marine pollutant  
No.

### 14.6. Special precautions for user

Not applicable.

## LEMON DISINFECTANT

### 14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code Not applicable.

### SECTION 15: Regulatory information

#### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

<b>EU legislation</b>	<p>Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) (as amended).</p> <p>Regulation (EU) No 528/2012 of the European Parliament and of the Council of 22 May 2012 concerning the making available on the market and use of biocidal products (as amended).</p> <p>Regulation (EC) No 648/2004 of the European Parliament and of the Council of 31 March 2004 on detergents (as amended).</p> <p>Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures (as amended).</p> <p>Commission Directive 2000/39/EC of 8 June 2000 establishing a first list of indicative occupational exposure limit values in implementation of Council Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work (as amended).</p>
<b>Guidance</b>	<p>EH40/2005 Workplace exposure limits</p> <p>Containing the list of workplace exposure limits for use with the Control of Substances Hazardous to Health Regulations 2002 (as amended)</p> <p>Health and Safety Executive</p>

#### 15.2. Chemical safety assessment

A chemical safety assessment has been carried out.

### SECTION 16: Other information

<b>Issued by</b>	Regulatory Chemist
<b>Revision date</b>	28/05/2021
<b>Revision</b>	10
<b>Supersedes date</b>	29/03/2021
<b>SDS number</b>	10387
<b>Hazard statements in full</b>	<p>H302 Harmful if swallowed.</p> <p>H314 Causes severe skin burns and eye damage.</p> <p>H315 Causes skin irritation.</p> <p>H318 Causes serious eye damage.</p> <p>H319 Causes serious eye irritation.</p> <p>H400 Very toxic to aquatic life.</p> <p>H410 Very toxic to aquatic life with long lasting effects.</p> <p>H412 Harmful to aquatic life with long lasting effects.</p>

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty, guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.