

Data sheet

PM013xxVBHC Type 424

Page 1/5

P/N

314241xx22

xx=number of poles


2024/05/23

Version: E


Illustrations



Dimensional drawing



PCB-Layout



See enlarged drawings at the end of document

Product specification

- pin header, SMT solderable
- centerline 3.50 mm, direction of connection vertical 0°
- fittable without loss of poles
- color black
- Tape & Reel packaging



U | Contact

Data sheet PM013xxVBHC Type 424

Page 2/5

P/N
314241xx22

xx=number of poles

2024/05/23

Version: E

Technical Data

General Data			
min. number of poles	2		
max. number of poles	12		
Insulating material class	CTI 400		
clearance/creepage dist.	1.5 mm		
Protection category	IP00		
Rated current	12 A		
Overvoltage category	III	III	II
Pollution degree	2	2	2
Rated voltage	32 V	200 V	200 V
Rated test voltage	2.5 kV	2.5 kV	2.5 kV
Approvals			
 V / A	300 / 15		
approval UL - File No.	E121004		
Material			
insulating material	PA46		
flammability class	V0		
contact pin material	CuZnPb		
contact pin surface	Ni + Sn		
Glow-Wire Flammability GWFI	-		
Glow-Wire Flammability GWIT	-		
Climatic Data			
upper limit temperature	125 °C		
lower limit temperature	-40 °C		
general			
Tolerance	ISO 2768 -mH		
Solderability	reflowable		

U | Contact

Data sheet

PM013xxVBHC Type 424

Page 3/5

P/N

314241xx22

xx=number of poles

2024/05/23

Version: E

Counterpart of

P/N	Designation
311661	RP023xxHBWC Type 166

U | Contact

Data sheet

PM013xxVBHC Type 424

Page 4/5

P/N

314241xx22


xx=number of poles

2024/05/23

Version: E

Illustrations

Dimensional drawing



$L = (\text{pole size} - 1) \times \text{centerline} + 2.7 \text{ mm } [0.106]$

U | Contact

Data sheet

PM013xxVBHC Type 424

Page 5/5

P/N

314241xx22

xx=number of poles

2024/05/23

Version: E

Illustrations

PCB-Layout

