

Fixed centring point

With half and flattened point



Application:

For centring and supporting long and narrow workpieces on lathes and grinding machines.

Execution:


- Tip angle 60°.
- Taper hardened and precision-ground.
- Carbide-tipped.
- Concentricity tolerance on cemented carbide $\leq 0.8 \mu\text{m}$.

Advantage:

- Very good accessibility to workpieces.
- Wear-resistant carbide tip.

Delivery:

1x centring point MK 1.



Art. no.	22113 040
Brand	BRUCKNER
Manufacturer Part Number	2814H
Morse taper size	MK 4
Programming size	57.5 mm
Diameter of flat area	14 mm
Length of flat area	50 mm
Height of flat area	7.5 mm
Concentricity tolerance	0.008 mm
DIN	806
Gross Weight	0.752 kg
Product Group	2AA