

SERIES 1930 - DOUBLE-POLE ROCKER SWITCHES IP 65

TO 20 (4) A 250 V AC






PRODUCT FEATURES

- ◆ Illuminated and non-illuminated variants with various switching functions
- ◆ IP 65 with integrated gasket for high dust and water protection
- ◆ Inrush current (capacitive) up to 120 A
- ◆ Approval for 400 V
- ◆ 100 million times proven switching principle
- ◆ Modern rocker design
- ◆ High, flexible variety

ON REQUEST


- ◆ Other switching functions (e.g. Changeover switch)
- ◆ Other terminal types
- ◆ Other colors (e.g. red)
- ◆ Other printing variants
- ◆ Other lamp variants
- ◆ Cable assembly

Mechanical life endurance	5E4
Operating force	3 - 8 N
Inrush current (capacitive)	120 A 100 A (basic type 1939) 50 A (basic type 1934)
Contact resistance (new condition)	< 100 mOhm (1 A 12 V DC)
Insulation resistance (new condition)	> 100 MOhm (500 V DC)
Proof tracking	250 PTI
Protection type	IP 65 (recessed installation)
Ambient temperature	terminal side -30 °C ... +105 °C actuating side -30 °C ... +55 °C
Flammability	UL 94 V-2 UL 94 V-0 (housing and socket only)
Glow wire test temperature	850 °C
Material	actuator PC / TPU (bellows) housing PA terminals silver plated
Plug force of the terminals	≤ 80 N
Approval marks	 /  / 
Suitable for appliances of protection class II	



SERIES 1930 - DOUBLE-POLE ROCKER SWITCHES IP 65


TO 20 (4) A 250 V AC

<div style="text-align: center;">  <p>double-pole</p> </div>	ON / OFF switch (DPST)								Normally open contact (DPNO)	ON / OFF switch (DPST)							
	1935.3135	1935.3137	1935.3112	1935.3113	1935.3114	1935.3118	1935.3119	1935.3129		1935.3218	1935.3134	1935.3128	1935.3131	1935.3133	1935.3138		
Lighting voltage in V	400	400	250	250	250	250	250	250	250	125-250	125	125	24	12			
Actuator color / printing																	
Housing color	Black	Black	Black	Black	Black	Black	Black	Black	Black	Black	Black	Black	Black	Black			
20 (4) A 250 V AC 1E4	•	•	•	•	•	•	•	•		•	•	•					
12 (4) A 250 V AC 1E4																	
10 (8) A 400 V AC 5E4	•	•															
10 (8) A 250 V AC 5E4	•	•	•	•	•	•	•	•		•	•	•					
10 A 24 V DC													•				
10 A 12 V DC														•			
6 (4) A 250 V AC 5E4																	
16 A 250 V AC 1 HP	•	•	•	•	•	•	•	•		•	•	•					
16 A 125 V AC 3/4 HP	•	•	•	•	•	•	•	•		•	•	•					
16 A 125 V AC 1/3 HP												•					
14 A 250 V AC 3/4 HP																	
14 A 250 V AC 1/2 HP																	
14 A 125 V AC 1/3 HP																	
14 A 125 V AC 1/4 HP																	
12 A 250 V AC 1 HP																	
12 A 125 V AC 1/2 HP																	
Terminal type																	
Terminal description	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3			
Contact distance in mm	≥ 3	≥ 3	≥ 3	≥ 3	≥ 3	≥ 3	≥ 3	≥ 3	≥ 3	≥ 3	≥ 3	≥ 3	≥ 3	≥ 3			
Contact material	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag			
EN 60335 cap. 30 conform "G"																	
Miscellaneous									below anthracite								
Stock version			•	•	•	•											

ROCKER SWITCHES
PUSHBUTTON SWITCHES
TOGGLE SWITCHES
SLIDE SWITCHES
ROTARY SWITCHES
FOOT SWITCHES
FACT AND KEY SWITCHES
SNAP-ACTION SWITCHES
MICRO-SIGNAL SWITCHES
SENSORS

SERIES 1930 - DOUBLE-POLE ROCKER SWITCHES IP 65

TO 20 (4) A 250 V AC

 double-pole	ON / OFF switch (DPST)										Normally closed contact (DPNC)		Normally open contact (DPNO)	
	1932.1113	1932.3112	1932.3113	1932.3114	1932.3116	1932.3118	1932.3130	1932.3131	1932.3132	1932.3412	1932.3312	1932.3314	1932.3413	
Lighting voltage in V														
Actuator color / printing														
Housing color	Black	Black	Black	Black	Black	Black	Black	Black	Black	Black	Black	Black	Black	Black
20 (4) A 250 V AC 1E4	•	•	•	•	•	•	•	•	•	•				
12 (4) A 250 V AC 1E4														
10 (8) A 400 V AC 5E4														
10 (8) A 250 V AC 5E4	•	•	•	•	•	•	•	•	•	•				
10 A 24 V DC														
10 A 12 V DC														
6 (4) A 250 V AC 5E4														
16 A 250 V AC 1 HP	•	•	•	•	•	•	•	•	•	•				
16 A 125 V AC 3/4 HP	•	•	•	•	•	•	•	•	•	•				
16 A 125 V AC 1/3 HP							•							
14 A 250 V AC 3/4 HP														
14 A 250 V AC 1/2 HP														
14 A 125 V AC 1/3 HP														
14 A 125 V AC 1/4 HP														
12 A 250 V AC 1 HP														
12 A 125 V AC 1/2 HP														
Terminal type														
Terminal description	4.8	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	
Contact distance in mm	≥ 3	≥ 3	≥ 3	≥ 3	≥ 3	≥ 3	≥ 3	≥ 3	≥ 3	≥ 3	≥ 3	≥ 3	≥ 3	
Contact material	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	
EN 60335 cap. 30 conform "G"							•	•	•	•				
Miscellaneous									single-pole occupied					
Stock version						•								•

ROCKER SWITCHES

PUSHBUTTON SWITCHES

TOGGLE SWITCHES

SLIDE SWITCHES

ROTARY SWITCHES

FOOT SWITCHES

FACT AND KEY SWITCHES


















SNAP-ACTION SWITCHES

MICRO-SIGNAL SWITCHES

SENSORS

SERIES 1930 - DOUBLE-POLE ROCKER SWITCHES IP 65

TO 20 (4) A 250 V AC

 double-pole	Changeover switch (DPDT)	1934.3112	1934.3114	1934.2114	Changeover switch with OFF position in the center (DPDT - Center OFF)	1939.3119	1939.3312	1939.3314	1939.3318	1939.0454
		Lighting voltage in V								
Actuator color / printing										
Housing color										
20 (4) A 250 V AC 1E4										
12 (4) A 250 V AC 1E4						●	●	●	●	
10 (8) A 400 V AC 5E4										
10 (8) A 250 V AC 5E4		●	●							
10 A 24 V DC										
10 A 12 V DC										
6 (4) A 250 V AC 5E4				●						
16 A 250 V AC 1 HP										
16 A 125 V AC 3/4 HP										
16 A 125 V AC 1/3 HP										
14 A 250 V AC 3/4 HP						●				
14 A 250 V AC 1/2 HP							●	●	●	
14 A 125 V AC 1/3 HP						●				
14 A 125 V AC 1/4 HP							●	●	●	
12 A 250 V AC 1 HP		●	●	●						
12 A 125 V AC 1/2 HP		●	●	●						
Terminal type										
Terminal description		6.3	6.3			6.3	6.3	6.3	6.3	
Contact distance in mm		≥ 3	≥ 3	≥ 3		≥ 3	< 3	< 3	< 3	< 3
Contact material		Ag	Ag	Ag		Ag	Ag	Ag	Ag	Au
EN 60335 cap. 30 conform "G"										
Miscellaneous							momentary function both sides	momentary function both sides	momentary function both sides	single-pole occupied momentary function both sides
Stock version										

ROCKER SWITCHES

PUSHBUTTON SWITCHES

TOGGLE SWITCHES

SLIDE SWITCHES

ROTARY SWITCHES

FOOT SWITCHES

FACT AND KEY SWITCHES

SNAP-ACTION SWITCHES

MICRO-SIGNAL SWITCHES

SENSORS

SERIES 1930 - DOUBLE-POLE ROCKER SWITCHES IP 65

T0 20 (4) A 250 V AC

ROCKER SWITCHES

PUSHBUTTON SWITCHES

TOGGLE SWITCHES

SLIDE SWITCHES

ROTARY SWITCHES

FOOT SWITCHES

FACT AND KEY SWITCHES


SNAP-ACTION SWITCHES

MICRO-SIGNAL SWITCHES


SENSORS




Basic types 1932, 1934, 1935 and 1939 double-pole




X	Y	Z
0.75 ... 1.25	30 ^{-0.1}	22 ^{+0.2}
1.25 ... 3	30.2 ^{-0.1}	22 ^{+0.2}




Quick-connect terminal 4.8 x 0.8 basic type 1932




Quick-connect terminal 6.3 x 0.8 basic type 1939




Quick-connect terminal 6.3 x 0.8 basic types 1932, 1934 and 1935



Solder terminal basic type 1939



PCB terminal basic type 1934



Sunken installation recommended for IP 65

A correct assembly and examination on tightness according to IP 65 in the equipment must be ensured by the customer.