

FIBERPOINT® 250MD

Part Number: 1400000030Q / 1400000030E



Patented universal port 2.5 mm

- Applications:**
- The compact design of the visual fault locator is very suitable for **daily use** in all fiber optic applications e.g. **in the field, in industrial environment as well as in laboratory.**
 - To check **singlemode/multimode** optical fibers and other fiber optic components on faults.
 - **Patching** of fibers.



D (mm)	12
L (mm)	167

Parameter	Min.	Typ.	Max.
Wavelength		635 nm	
Operation temperature	- 10 °C		45 °C
Storage temperature	- 40 °C		70 °C
Fiber coupled power	(Singlemode fiber 9/125 µm) (Multimode fiber 50/125 µm)	500 µW 500 µW	700 µW 800 µW
Optical output power			1 mW
Operation current		40 mA	
Retention force for ferrule		1 - 2 N	
Weight incl. batteries		60 g	
Operation time - one battery pack ¹ (Pulsed mode)		40 hours	
Battery type		AAA	
Operation mode	continuous wave; pulsed mode: frequency 2 - 3 Hz		
Laser protection class	2		
Suitable ferrule 2.5 mm	DIN, E2000, FC, SC, ST		

- Included in delivery:**
- Dust cap
 - One battery pack
 - Instruction manual

Accessories (not included): - Adapters please see page 8/9 this brochure

Order number:

- 1400000030Q: Individually packed in "Quadrosafe"
- 1400000030E: Individually packed in etui style plastic packaging

Feature:

- Private labelling is available
- Minimum order quantity applies

Notes: Do not use rechargeable batteries.
Compliant with RoHS-requirements (2002/95/EG vom 27.01.2003)
 The above product specifications are subject to change without notice.

¹⁾ Battery: VARTA Industrial Alkaline No. 4003; 1.5 V; AAA; LR03 Micro; AM4; MN2400