

RELAY, 1 NO AS REPLACEMENT FOR 24 V
COMPLETE UNIT

General technical data:		
Type of voltage		DC
Control supply voltage		
<ul style="list-style-type: none"> • for DC Rated value — minimum — maximum 	V V	12 12
Switching behavior		monostable
Number of NC contacts for auxiliary contacts		0
Number of NO contacts for auxiliary contacts		0
Number of CO contacts for auxiliary contacts		1
Operating current of the auxiliary contacts		
<ul style="list-style-type: none"> • at DC-13 — at 24 V — at 110 V — at 230 V • at AC-15 — at 230 V 	A A A A	1 0.2 0.1 3
Equipment marking acc. to DIN 40719 extended according to IEC 204-2 acc. to IEC 750		K
Equipment marking acc. to DIN EN 61346-2		K
Mechanical data:		
Type of electrical connection Plug-in socket		No
Design of the relay operating mechanism		poled
Design of the switching function positively driven		No
Product component Plug-in socket		No
Ambient conditions:		
Protection class IP		IP00
Ambient temperature during operation	°C	-25 ... +55
Certificates/ approvals:		

[Declaration of Conformity](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)<http://www.siemens.com/industrial-controls/catalogs>**Industry Mall (Online ordering system)**<http://www.siemens.com/industrymall>**Cax online generator**<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mfb=3TX70147BQ00>**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**<https://support.industry.siemens.com/cs/ww/en/ps/3TX70147BQ00>**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**http://www.automation.siemens.com/bilddb/cax_de.aspx?mfb=3TX70147BQ00&lang=en

last modified:

15.01.2015