

Product Technical Data Sheet - Cable Tie Bases

Description

Partex self-adhesive nylon cable tie bases are designed to compliment our range of cable ties, and offer a simple and effective method of fixing.

They are supplied in bags of 100, and are available in either Black or Natural.

Specification


Material: Nylon 6.6 Polyamide

Temperature Range: -20 C to +60 C


Black bases are U.V. Resistant and suitable for external conditions.

These self adhesive bases are manufactured in pairs, making removal of the backing strip much easier. The adhesive consists of a white polythene foam, coated on both sides with a high performance synthetic rubber adhesive, providing a particularly high level of instant tack combined with high shear adhesion.

Part Number	Dim A	Dim B	Dim C	Dim D
HFC1/4	20 mm	20 mm	4.5 mm	5 mm



Part Number	Dim A	Dim B	Dim C	Dim D	Screw Fix (Optional)
HFC2/4	28mm	28mm	5.5mm	7.1mm	M6



Partex Marking Systems (UK) Ltd
 61-64 Station Road, Coleshill, Birmingham B46 1JT
 Tel: 01675 463670 Fax: 01675 463520 Email: sales@partex.co.uk