

**DICHT-BECHERBLINDNIETE**



FLACHRUNDKOPF (~ DIN EN ISO 15973)

**SEALED BLIND RIVETS**

DOMED HEAD (~ DIN EN ISO 15973)

**RIVETS ÉTANCHES**


TÊTE PLATE (~ DIN EN ISO 15973)









Aluminium AIMG 5  
Aluminium AIMG 5  
Aluminium AIMG 5


Stahl leicht gefettet  
Steel protection layer  
Acier légèrement graissé







**Ø 3,2 mm**

D1 = 3,2 +/- 0,08 mm  
D2 = 6,0 +/- 0,24 mm  
k = ≤ 1,4 mm  
d = 1,7 mm  
P = ≥ 27,0 mm  
L = + 1,0 / - 0,2 mm  
 3,3 mm


		CODE				
3,2 x 6,5 mm	0,5 - 2,0 mm	21701 32600	1050 N	1200 N	1000	10000
3,2 x 8,0 mm	2,0 - 3,5 mm	21701 32800			1000	10000
3,2 x 9,5 mm	3,5 - 5,0 mm	21701 32900			1000	10000
3,2 x 10,5 mm	5,0 - 6,5 mm	21701 32100			1000	10000
3,2 x 12,5 mm	6,5 - 8,0 mm	21701 32120			1000	10000







**Ø 4,0 mm**

D1 = 4,0 +/- 0,08 mm  
D2 = 8,0 +/- 0,29 mm  
k = ≤ 1,7 mm  
d = 2,18 mm  
P = ≥ 27,0 mm  
L = + 1,0 / - 0,2 mm  
 4,1 mm


		CODE				
4,0 x 8,0 mm	0,5 - 3,5 mm	21701 40800	1550 N	2100 N	1000	10000
4,0 x 9,5 mm	3,5 - 4,5 mm	21701 40950			500	5000
4,0 x 11,0 mm	4,5 - 6,5 mm	21701 40110			500	5000
4,0 x 12,0 mm	6,5 - 8,0 mm	21701 40120			500	5000
4,0 x 15,0 mm	8,0 - 10,5 mm	21701 40150			500	5000







**Ø 4,8 mm**

D1 = 4,8 +/- 0,08 mm  
D2 = 9,5 +/- 0,29 mm  
k = ≤ 2,0 mm  
d = 2,63 mm  
P = ≥ 27,0 mm  
L = + 1,0 / - 0,2 mm  
 4,9 mm

		CODE				
4,8 x 8,0 mm	1,0 - 3,0 mm	21701 48800	2100 N	3000 N	500	5000
4,8 x 9,5 mm	3,0 - 4,5 mm	21701 48950			500	5000
4,8 x 11,0 mm	4,5 - 6,0 mm	21701 48110			250	2500
4,8 x 12,5 mm	6,0 - 7,5 mm	21701 48125			250	2500
4,8 x 14,0 mm	7,5 - 9,0 mm	21701 48140			250	2500
4,8 x 16,0 mm	9,0 - 11,0 mm	21701 48160			250	2500
4,8 x 18,0 mm	11,0 - 13,0 mm	21701 48180			250	2500
4,8 x 21,0 mm	13,0 - 16,0 mm	21701 48210			250	2500
4,8 x 25,0 mm	16,0 - 20,0 mm	21701 48250	250	2500		

**Ø 6,4 mm**

D1 = 6,4 +/- 0,11 mm  
D2 = 12,7 +/- 0,35 mm  
k = ≤ 2,5 mm  
d = 3,7 mm  
P = ≥ 31,0 mm  
L = + 1,0 / - 0,2 mm  
 6,5 mm

		CODE				
6,4 x 12,5 mm	3,0 - 6,0 mm	21701 64125	3800 N	4800 N	250	2500
6,4 x 16,0 mm	6,0 - 9,0 mm	21701 64160			250	2500