

## Cemented carbide angular milling cutter

**ORION®**

### Application:

For milling ducts and other angular geometries in tool and mechanical engineering.

### Execution:

- Straight shank according to DIN 1835 A
- Cutter angles chamfered 0.5 mm x 60° to planing side



<b>Art. no.</b>	<b>16530 220</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	16530220
<b>Cutting material</b>	Carbide
<b>Number of cutting edges</b>	6 PCS
<b>Chamfer angle</b>	60 Degree
<b>Tool holding device</b>	HA parallel shank
<b>Cutting edge diameter</b>	20 mm
<b>Width of cutting edge</b>	7 mm
<b>Immersion depth</b>	21 mm
<b>Length</b>	56 mm
<b>Shank diameter</b>	12 mm
<b>Form</b>	C
<b>fz steel 1000</b>	0.04 mm
<b>Gross Weight</b>	0.073 kg
<b>Product Group</b>	165

### EAN

4039247104208