

Wet and dry safety vacuum cleaner ATTIX 791-2 M/B 1

Power consumption 1500 watt

Nilfisk
ALTO

Application:

Suction in continuous operation for dust classes L and M and ATEX Zone 22, all non-carcinogenic dust with MAK values > 0.1 mg/m³ and/or combustible dust from Zone 22.

Version:

- Electronic follow-up control
- Secure suction into the filter; the whole system is completely de-dusted
- Variable speed control
- Tilting container for easy emptying
- With socket for power tools

Advantage:

- Brushless long-life motor

Delivery:

With 3.5-m suction hose AntiStatic (diameter 27 mm), tool adapter, filter element and filter bag, cable holder, rubberised 7.5-m mains cable



Art. no.	75524 011
Model	ATTIX 791-2 M/B1
Power input	1500 W
Max. air delivery volume	3800 l/min
Material of bins	Stainless steel
Underpressure	250 mbar
Container capacity	70 l
Sound-pressure level	59 dB
Weight	25 kg
Cable length	7.5 m
Length x width x height	650 x 580 x 970 mm
Inner hose diameter	27 mm
Hose length	3.5 m
Nominal voltage	230 V

EAN-Code

4005337063960