

SIMATIC S7-1500, SYSTEM POWER SUPPLY WITH BUFFER
 FUNCTIONALITY PS 60W 24/48/60V DC hf SUPPLIES
 OPERATING VOLTAGE FOR THE S7-1500 BACKPLANE BUS AND
 ENABLES THE CPU TO KEEP THE WORKING MEMORY (DATA)
 RETAIN



General information	
Product type designation	PS 60 W 24/48/60 V DC HF
HW functional status	E01
Firmware version	V1.0.0
Engineering with	
<ul style="list-style-type: none"> STEP 7 TIA Portal configurable/integrated as of version 	V14 SP1
Supply voltage	
Rated value (DC)	24 V / 48 V / 60 V
permissible range, lower limit (DC)	Static 19.2 V, dynamic 18.5 V
permissible range, upper limit (DC)	Static 72 V, dynamic 75.5 V
Reverse polarity protection	Yes
Short-circuit protection	Yes
Mains buffering	
<ul style="list-style-type: none"> Mains/voltage failure stored energy time 	20 ms
Input current	
Rated value at 24 V DC	3 A
Rated value at 48 V DC	1.5 A

Rated value at 60 V DC	1.2 A
Inrush current, max.	≤ 8 A for t ≤ 1 s
Output current	
Short-circuit protection	Yes
Power	
Infeed power to the backplane bus	60 W
Power loss	
Power loss at nominal rating conditions	12 W
Interrupts/diagnostics/status information	
Status indicator	Yes
Isolation	
Isolation tested with	2 500 V DC (type test)
EMC	
Interference immunity against voltage surge	
<ul style="list-style-type: none"> on the supply lines acc. to IEC 61000-4-5 	Yes; ±1 kV (acc. to IEC 61000-4-5; 1995; surge symm.), ±2 kV (acc. to IEC 61000-4-5; 1995; surge asymm.), no external protective circuit required
Degree and class of protection	
Degree of protection acc. to EN 60529	IP20
Equipment protection class	I, with protective conductor
Dimensions	
Width	105 mm
Height	147 mm
Depth	129 mm
last modified:	10/13/2017