

TECHNICAL DATASHEET


Update : 25/02/2019

CYLINDRICAL CARBIDE MILLING BIT - END TRIMMING FORM B



Description

For use, please refer to the table on page 109



Characteristics

Ref.	EAN	Tail diameter mm	Shape of head	Total length	Teeth	Head diameter	Scope	Capacity length mm
847248	3660338086083	3	Model B	38	Crossed	3	Universal	13
847249	3660338086090	6	Model B	50	Crossed	6	Universal	19
847250	3660338086106	6	Model B	65	Crossed	9,5	Universal	19
847251	3660338086113	6	Model B	70	Crossed	12,7	Universal	25
863116	3660338177309	3	Model B	45	Crossed	6	Universal	13
863117	3660338177316	6	Model B	65	Crossed	8	Universal	19
863118	3660338177323	6	Model B	70	Crossed	16	Universal	25
863119	3660338177330	6	Model B	65	Negative	9,5	Rough outline	19
863120	3660338177347	6	Model B	70	Negative	12,7	Rough outline	25
863121	3660338177354	6	Model B	65	Steel	9,5	Rough outline	19
863122	3660338177361	6	Model B	70	Steel	12,7	Rough outline	25
863123	3660338177378	3	Model B	38	Simple	3	Finish	13
863124	3660338177385	3	Model B	45	Simple	6	Finish	13
863125	3660338177392	6	Model B	50	Simple	6	Finish	19
863126	3660338177408	6	Model B	65	Simple	8	Finish	19
863127	3660338177415	6	Model B	65	Simple	9,5	Finish	19
863128	3660338177422	6	Model B	70	Simple	12,7	Finish	25
863129	3660338177439	6	Model B	65	Diamond	9,5	Finish	19
863130	3660338177446	6	Model B	70	Diamond	12,7	Finish	25
863131	3660338177453	6	Model B	50	Alu	6	Alu	19
863132	3660338177460	6	Model B	65	Alu	9,5	Alu	19
863133	3660338177477	6	Model B	70	Alu	12,7	Alu	25