

T-slot bolts



Application:

For clamping workpieces on machine tables.

Execution:

- Tempered
- Rolled thread
- Forged
- With milled groove guide
- M8 to M12, strength class 10.9
- M16 to M24, strength class 8.8
- DIN 787



Art. no.	26200 330
Brand	AMF
Manufacturer Part Number	8086 1
DIN	787
Thread dimension	M12
Groove width	12 mm
Length excluding head	80 mm
Outer diameter	11.7 mm
Thread length	55 mm
Length of head	18 mm
Head height	7 mm
Gross Weight	0.126 kg
Product Group	260

EAN

4020772080860