

Conical countersink, 90°, HSS, multi-flute cutter

For universal use up to 1000 N/mm²

ATORN®

Application

For producing 90° counterbores up to 1000 N/mm².

Version

- Multi-edge countersink with straight cutting edge

Advantage

- high number of cutting edges for quiet cutting performance
- very good cutting performance and surface quality (chatter-free)



Application	Steel (N/mm ²)			Stainless steel		Alu		Brass		Bronze		Plas-tics	Graphite G(C)FK	GG(G) GJMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	30	20	10	10		40	70	60	50	40	30	30		15					

Art. No.	11495 430
Countersink angle	90 Degree
Cutting material	HSS
Surface	Uncoated
Number of cutting edges	9 PCS
Tool holding device	Morse taper shank
Spot-facer diameter	25 mm
Tip diameter	7 mm
Length	118 mm
Morse taper size	MK 2
f steel 700	0.18 mm/U
DIN	335
Form	B

EAN-Code

4050293346329