



Features & Benefits

- Category 6 performance
- Unique colour coded saddles allow for quick and easy termination
- Industry standard IDCs
- Top quality high performance sockets
- Individually QA tested
- Manufactured in the UK

Specification

Width	483mm (19")
Depth	30mm
Height	1u (44mm)
Fixing Centres	467mm
Material	Mild steel sheet CR4 to BSEN10130-1999 DC01 Plastic inserts ABS thermoplastic resin with grade UL94 V0 at 1.5mm flame retardancy
Finish	Black powder coat to B56496
Socket Labels	9mm numbered card, with acetate cover
IDC Colour Code	IDC colour code to T568B
Cable Guide	Individual cable saddles with cable tie position for left or right cable entry
Sockets	High performance unshielded vertical jacks
IDC Blocks	4 Way industry standard IDC blocks
PCB	Groups of 4 identical circuits on 1.6mm double sided PTH board
Conforms to	ANSI/TIA-568-C Category 6 Specification

Ordering Information

Product Description	Part Number
CCS Elite Cat 6 High Density 24 Way UTP Panel	009-001-009-07
CCS Elite Cat 6 High Density 48 Way UTP Panel	009-001-009-30
CCS Elite Cable Management Tray	009-001-008-30

Connectix Category 6 High Density Elite Patch Panels provide the performance needed for present and next generation data communications networks and applications, including Gigabit Ethernet. The high density format is ideal where cabinet space is at a premium.

Available in a 1u 24 port format and a 2u 48 port format, these Category 6 High Density panels achieve optimum transmission performances by incorporating the highest quality components and innovative on-board compensation techniques. The front of the panel features easy to use slide-in labels. The rear utilises colour coded cable saddles and hook and loop retainers.

All Connectix Category 6 High Density Panels are fully compliant with the ANSI/TIA Category 6 Standard. When used in conjunction with Connectix Category 6 Modules and UTP Cable, the user will get a link performance exceeding Category 6 requirements.

