AF265-30-11-13 100-250V 50/60Hz / DC



General Information

Extended Product Type: AF265-30-11-13 100-250V 50/60Hz / DC

Product ID: 1SFL547002R1311 **EAN:** 7320500481189

Catalog Description: AF265-30-11-13 Contactor

Long Description: A 3-phase Contactor suitable for various applications such as Motor starting, Isolation, By-

pass and Distribution application up to max 1000 V. Operated with wide control voltage

range 100-250 V, 50/60 Hz and DC

Categories

Products » Low Voltage Products and Systems » Control Products » Contactors » Block Contactors

Ordering

 Minimum Order Quantity:
 1 piece

 Customs Tariff Number:
 85364900

 EAN:
 7320500481189

Dimensions

Product Net Depth: 180.0 mm

Product Net Height: 225.0 mm

Product Net Weight: 4.640 kg

Product Net Width: 140.0 mm

Container Information

Package Level 1 Width: 223 mm
Package Level 1 Length: 175 mm
Package Level 1 Height: 270 mm
Package Level 1 Gross Weight: 5.31 kg
Package Level 1 EAN: 7320500481189
Package Level 1 Units: 1 piece

Technical

Number of Main Contacts NC: 0
Number of Auxiliary Contacts NO: 1
Number of Auxiliary Contacts NC: 1

Rated Operational Voltage: Main Circuit 1000 V
Rated Frequency (f): Main Circuit 50/60 Hz

Conventional Free-air Thermal

Current (Ith):

acc. to IEC 60947-4-1, Open Contactors q = 40 $^{\circ}$ C 400 A

Rated Operational Current AC-1 (I_e): (690 V) 55 °C 350 A

(690 V) 40 °C 400 A (1000 V) 40 °C 350 A (1000 V) 55 °C 300 A (690 V) 70 °C 290 A (1000 V) 70 °C 240 A

Rated Operational Current AC-3 (Ie): (1000 V) 55 °C 100 A

(220 / 230 / 240 V) 55 °C 265 A

(690 V) 55 °C 250 A (415 V) 55 °C 265 A (440 V) 55 °C 265 A (380 / 400 V) 55 °C 265 A (500 V) 55 °C 250 A

Rated Operational Power AC-3 (Pe): (500 V) 200 kW

(300 V) 200 kW (1000 V) 132 kW (690 V) 200 kW (220 / 230 / 240 V) 75 kW (380 / 400 V) 132 kW (440 V) 160 kW

Rated Breaking Capacity AC-3 acc. 8 x le AC-3

to IEC 60947-4-1:

c. 0 x 10 70 0

(415 V) 132 kW

Rated Making Capacity AC-3 acc. to 10 x le AC-3

IEC 60947-4-1:

Short-Circuit Protective Devices: gG Type Fuses 500 A

Rated Short-time Withstand Current at 40 °C Ambient Temp, in Free Air, from a Cold State 15 min 400 A (I_{cw}): at 40 °C Ambient Temp, in Free Air, from a Cold State 30 s 1224 A

at 40 °C Ambient Temp, in Free Air, from a Cold State 10 s 2120 A at 40 °C Ambient Temp, in Free Air, from a Cold State 1 s 2650 A at 40 °C Ambient Temp, in Free Air, from a Cold State 1 min 865 A

Maximum Breaking Capacity:

cos phi=0.45 (cos phi=0.35 for le > 100 A) at 440 V 3800 A cos phi=0.45 (cos phi=0.35 for le > 100 A) at 690 V 3300 A

Maximum Electrical Switching

Frequency:

AC-3 300 cycles per hour AC-1 300 cycles per hour AC-2 / AC-4 150 cycles per hour

Rated Operational Current DC-1 (Ie): (110 V) 2 Poles in Series, 40 °C 350 A

(220 V) 3 Poles in Series, 40 °C 350 A

Rated Operational Current DC-3 (Ie): (110 V) 2 Poles in Series, 40 °C 350 A

(220 V) 3 Poles in Series, 40 °C 350 A

Rated Operational Current DC-5 (Ie): (110 V) 2 Poles in Series, 40 °C 350 A

(220 V) 3 Poles in Series, 40 °C 350 A

Rated Insulation Voltage (Ui): acc. to UL/CSA 600 V

acc. to IEC 60947-4-1 and VDE 0110 (Gr. C) 1000 V

Rated Impulse Withstand Voltage

(U_{imp}):

Main Circuit 8 kV

Mechanical Durability: 5 million

Maximum Mechanical Switching

Frequency:

300 cycles per hour

Coil Operating Limits: (acc. to IEC 60947-4-1) 0.85 x Uc Min. ... 1.1 x Uc Max. (at $\theta \le 70$ °C) °C

Rated Control Circuit Voltage (U_c):

60 Hz 100...250 V 50 Hz 100...250 V DC Operation 100...250 V

Pull-in at Max. Rated Control Circuit Voltage 60 Hz 385 V·A **Coil Consumption:**

> Holding at Max. Rated Control Circuit Voltage DC 4.5 W Holding at Max. Rated Control Circuit Voltage 50 Hz 17.5 V·A Pull-in at Max. Rated Control Circuit Voltage DC 410 W Pull-in at Max. Rated Control Circuit Voltage 50 Hz 385 V·A Holding at Max. Rated Control Circuit Voltage 60 Hz 17.5 V·A Between Coil Energization and NO Contact Closing 25...55 ms

Between Coil De-energization and NO Contact Opening 37...47 ms Rigid Al-Cable 1x185...240 mm²

Connecting Capacity Main Circuit:

Rigid Cu-Cable 2x70...185 mm² Flexible 2x70...185 mm²

Connecting Capacity Auxiliary

Circuit:

Operate Time:

Solid 2x1...4 mm²

Flexible with Insulated Ferrule 2x0.75...2.5 mm²

Stranded 1x1...4 mm² Flexible 2x0.75...2.5 mm²

Flexible with Ferrule 2x0.75...2.5 mm²

acc. to IEC 60529. IEC 60947-1. EN 60529 Coil Terminals IP20

acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP00

Terminal Type: Main Circuit: Bars

Number of Main Contacts NO:

Environmental

Degree of Protection:

Maximum Operating Altitude

Permissible:

3000 m

RoHS Status: Ambient Air Temperature:

Following EU Directive 2002/95/EC August 18, 2005 and amendment

Close to Contactor Fitted with Thermal O/L Relay (0.85 ... 1.1 Uc) -25...+50 °C

Close to Contactor without Thermal O/L Relay (0.85 ... 1.1 Uc) -40...+70 °C

Close to Contactor for Storage -40...+70 °C

Technical UL/CSA

General Use Rating UL/CSA: (600 V AC) 350 A

(208 V AC) Three Phase 75 Hp Horsepower Rating UL/CSA:

(440 ... 480 V AC) Three Phase 200 Hp (550 ... 600 V AC) Three Phase 250 Hp (220 ... 240 V AC) Three Phase 100 Hp (200 V AC) Three Phase 75 Hp

Maximum Operating Voltage

UL/CSA:

Main Circuit 600 V

Certificates and Declarations (Document Number)

1SFC100008M0201 Instructions and Manuals: **CB Certificate:** SE-73042M1 Data Sheet, Technical Information: 1SFC101070D0201 **Declaration of Conformity - CE:** 2CMT004749 **RINA Certificate:** ELE060313XG/002 **RoHS Information:** 1SFC101055D0202

Classifications

E-nummer:	3210155
ETIM 4:	EC000066 - Magnet contactor, AC-switching
ETIM 5:	EC000066 - Magnet contactor, AC-switching
UNSPSC:	39121529
Object Classification Code:	Ο

