

Shockproof dial gauges

Application:

For measuring lengths and length differences, e.g. concentricity, flatness, positional measurements.

Execution:

- Measuring pin and clamping shaft made from durable stainless steel

Advantage:

- Impacts against the gauge slide are not transferred to the measuring mechanism; in this way, display accuracy is maintained for a long time.

Delivery:

In a case



| | |
|---|------------------|
| Art. no. | 33078 020 |
| Brand | HK |
| Manufacturer Part Number | 33078020 |
| Length measuring range | 50 mm |
| Scale value | 0.01 mm |
| Measurement travel of one pointer revolution | 1 mm |
| Outer diameter | 58 mm |
| Shock protection | Yes |
| Material of outer ring | Plastic |
| Measurement force | 1.5 N |
| Calibration Group | CE |
| Gross Weight | 0.317 kg |
| Product Group | 331 |

EAN

4039247393138