



D-CT

TE Internal #: EL8092-000

D-CT, Printable Tubing, Continuous Printable Tubing Type, Fluid Resistant Printable Tubing Grade, 3:1 Printable Tubing Shrink Ratio, Yellow

[View on TE.com >](#)

Identification & Labeling > Printable Tubing > CONTINUOUS TUBE FLUID RESISTANT D-CT



Printable Tubing Type: **Continuous**

Printable Tubing Grade: **Fluid Resistant**

Printable Tubing Shrink Ratio: **3:1**

Primary Product Color: **Yellow**

Supplied Inner Diameter: **3.2 mm [ .125 in ]**

[All CONTINUOUS TUBE FLUID RESISTANT D-CT \(16\)](#)

**Features**

**Product Type Features**

Printable Tubing Type	Continuous
Printable Tubing Grade	Fluid Resistant

**Body Features**

Printable Tubing Shrink Ratio	3:1
Primary Product Color	Yellow

**Dimensions**

Supplied Inner Diameter	3.2 mm[.125 in]
Recovered Inside Diameter	1.1 mm[.042 in]
Compatible Cable Diameter Range	1.1 – 2.6 mm[.044 – .105 in]

**Usage Conditions**

Operating Temperature Range	-75 – 135 °C[-103 – 275 °F]
-----------------------------	-----------------------------

**Operation/Application**

Recommended Ribbon	See TE Document 411-121005 the Printer Product Ribbon Matrix
--------------------	--

**Printer/Label Features**

Recommended Printer	See TE Document 411-121005 the Printer
---------------------	--



Product Ribbon Matrix

Printer Technology Thermal Transfer

Packaging Features

Packaging Quantity 50

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU Compliant

EU ELV Directive 2000/53/EC Compliant

China RoHS 2 Directive MIIT Order No 32, 2016 No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006  
 Current ECHA Candidate List: JUL 2021 (219)  
 Candidate List Declared Against: JAN 2021 (211)  
 SVHC > Threshold:  
 Not Yet Reviewed

Halogen Content Not Low Halogen - contains Br or Cl > 900 ppm.

Solder Process Capability Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # 1-2186501-1  
T3212-SWARE-PRINTER



TE Part # 1-2186538-1  
RIB-1982-300-110-L-0



TE Part # 1-2186540-1  
RIB-1982-300-60-L-0



TE Part # 1-2186549-1  
RIB-1982-240-110-L-0-T200

### Also in the Series | D-CT



Printable Tubing(16)

### Customers Also Bought



TE Part #ZPF00000000000000339  
006-0912-16 A



TE Part #185847-1  
AUTOFUSE HOLDER WHITE



TE Part #094518-000  
B-070-19-10CS2822

TE Part #1SNA113550R2400  
EIP



TE Part #1SNA160563R0000  
HD6/9.3G.2G



TE Part #1SNA174781R2500  
BJD P4

TE Part #1SNA168460R1100  
BJH9-2

TE Part #1SNA168461R0600  
BJH9-3

TE Part #1SNA168463R0000  
BJH9-5

TE Part #1SNA168629R1600  
EV5



## Documents

### Product Drawings

[D-CT-50M-3.2-OUT-4](#)

English

[D-CT-50M-3.2-OUT-4](#)

English

---

### Datasheets & Catalog Pages

[D-CT, Continuous Diesel Resistant Heat Shrinkable Identification Tube](#)

English

---

### Product Specifications

[Product Specification](#)

English

---

### Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

English