

SDUC offset steel boring bar, positive, right

For longitudinal and copy turning using DC indexable inserts

ATORN

Application:

For longitudinal and copy turning with DC indexable insert 55°



Execution:

- Precision-manufactured boring bar, **steel**, with internal cooling, offset, shape D, 107.5° pitch angle, 55° tip angle, 7° clearance angle

Advantage:

- Slim contour, optimised for copy turning work
- Positive body geometry ensures low cutting forces

Art. no.	17827 654
Brand	ATORN
Manufacturer Part Number	12232458
ISO name	A0408F SDQC R/L 04
Min. bore diameter	5.2 mm
Tapered diameter	4 mm
Shank diameter	8 mm
Clearance length	15 mm
Length	80 mm
Clamping surface height	7 mm
Programming size	2.6 mm
Suitable for indexable inserts	DC.. 04..
Tool design	Right
DIN	8024
Gross Weight	0.030 kg
Product Group	1AQ

EAN

4050293562002

