

Fixed centring point

With half and flattened point



Application:


For centring and supporting long and narrow workpieces on lathes and grinding machines.

Execution:

- Tip angle 60°.
- Taper hardened and precision-ground.
- Carbide-tipped.
- Concentricity tolerance $\leq 0.8 \mu\text{m}$.
- For flat grinding.

Delivery:

1x centring point MK 4.



Art. no.	22114 021
Brand	BRUCKNER
Manufacturer Part Number	2812H/2,5
Morse taper size	MK 2
Programming size	46 mm
Diameter of flat area	7 mm
Length of flat area	40 mm
Height of flat area	2.5 mm
Concentricity tolerance	0.008 mm
DIN	806
Gross Weight	0.160 kg
Product Group	2AA