

## Air conditioning measuring instrument

Model testo 440



### Application:

For measuring parameters relevant to air conditioning in combination with up to three sensors.

### Advantage:

- automatic sensor detection
- easy operation thanks to structured menu navigation
- wireless measurement with Bluetooth sensors
- USB interface for CSV file export
- Graphic display for displaying three readings

<b>Art. no.</b>	<b>46210 500</b>
<b>Brand</b>	TESTO
<b>Manufacturer Part Number</b>	0560 440 1
<b>Colour</b>	Black, Orange
<b>Gross Weight</b>	0.600 kg
<b>Battery designation</b>	Mignon AA, R6, UM3, LR6
<b>Data transmission type</b>	Bluetooth, USB
<b>Length x width x height</b>	154 x 65 x 32 mm
<b>Measured value memory</b>	7500 measuring results
<b>Number of rechargeable batteries/batteries</b>	3 PCS
<b>Weight</b>	250 g
<b>Product Group</b>	4CF



### EAN

4029547019289