

**Safety Data Sheet**according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830  
Issue date: 10/15/2021 Version: 1.0**SECTION 1: Identification of the substance/mixture and of the company/undertaking****1.1. Product identifier**

Product form : Mixture  
Product name : JENOLITE YELLOW CALIPER PAINT GLOSS  
Product code : 89432 & 89632  
Vaporizer : Aerosol

**1.2. Relevant identified uses of the substance or mixture and uses advised against****1.2.1. Relevant identified uses**

Intended for general public

**1.2.2. Uses advised against**

No additional information available

**1.3. Details of the supplier of the safety data sheet**

JENOLITE UK LTD  
Chater Lea Buildings  
Icknield Way  
Letchworth, Hertfordshire  
SG6 1WT  
Sales@jenolite.com  
01234 924 794

**1.4. Emergency telephone number**

Emergency number : 01234 924 794 (office hours only)

**SECTION 2: Hazards identification****2.1. Classification of the substance or mixture****Classification according to Regulation (EC) No. 1272/2008 [CLP]**

Aerosol, Category 1	H222;H229
Serious eye damage/eye irritation, Category 2	H319
Specific target organ toxicity — Single exposure, Category 3, Narcosis	H336
Hazardous to the aquatic environment — Chronic Hazard, Category 3	H412

Full text of H- and EUH-statements: see section 16

**Adverse physicochemical, human health and environmental effects**

Pressurised container: May burst if heated. Extremely flammable aerosol. May cause drowsiness or dizziness. Causes serious eye irritation.  
Harmful to aquatic life with long lasting effects.

**2.2. Label elements****Labelling according to Regulation (EC) No. 1272/2008 [CLP]**

Hazard pictograms (CLP) :



GHS02

GHS07

Signal word (CLP) :

: Danger

Contains :

: HYDROCARBONS, C9-12, N-ALKANES, ISOALKANES, CYCLICS, (2-25%) AROMATICS, D40 NAPHTHA (PETROLEUM), HYDROTREATED HEAVY, DE-AROMATISED \*, HYDROCARBONS, C9, AROMATICS, ACETONE

Hazard statements (CLP) :

: H222 - Extremely flammable aerosol.  
H229 - Pressurised container: May burst if heated.

# JENOLITE YELLOW CALIPER PAINT GLOSS NPD10947

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Precautionary statements (CLP)	H319 - Causes serious eye irritation. H336 - May cause drowsiness or dizziness. H412 - Harmful to aquatic life with long lasting effects. : P102 - Keep out of reach of children. P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. P211 - Do not spray on an open flame or other ignition source. P251 - Do not pierce or burn, even after use. P271 - Use only outdoors or in a well-ventilated area. P410+P412 - Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.
EUH-statements	: EUH208 - Contains DIPENTENE(138-86-3), 2-BUTANONE OXIME(96-29-7), COBALTBIS(2-ETHYLHEXANOATE)(136-52-7). May produce an allergic reaction.

### 2.3. Other hazards

No additional information available

## SECTION 3: Composition/information on ingredients

### 3.1. Substances

Not applicable

### 3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
ACETONE	CAS-No.: 67-64-1 EC-No.: 200-662-2 EC Index-No.: 606-001-00-8	30 – 50	Flam. Liq. 2, H225 Eye Irrit. 2, H319 STOT SE 3, H336
PETROLEUM GASES, LIQUEFIED (Propellant gas (Aerosol))	CAS-No.: 68476-85-7 EC-No.: 270-704-2 EC Index-No.: 649-202-00-6	30 – 50	Flam. Gas 1, H220
HYDROCARBONS, C9-12, N-ALKANES, ISOALKANES, CYCLICS, (2-25%) AROMATICS	EC-No.: 919-446-0 REACH-no: 01-2119458049-33	1 – 10	Flam. Liq. 3, H226 STOT SE 3, H336 Asp. Tox. 1, H304 Aquatic Chronic 2, H411
D40 NAPHTHA (PETROLEUM), HYDROTREATED HEAVY, DE-AROMATISED *	CAS-No.: 64742-48-9 EC-No.: 919-857-5 REACH-no: 01-2119463258-33	1 – 10	Flam. Liq. 3, H226 STOT SE 3, H336 Asp. Tox. 1, H304
HYDROCARBONS, C9, AROMATICS	EC-No.: 918-668-5	1 – 10	Flam. Liq. 3, H226 STOT SE 3, H336 STOT SE 3, H335 Asp. Tox. 1, H304 Aquatic Chronic 2, H411
DIPENTENE	CAS-No.: 138-86-3 EC-No.: 205-341-0 EC Index-No.: 601-029-00-7	< 1	Flam. Liq. 3, H226 Skin Irrit. 2, H315 Skin Sens. 1, H317 Aquatic Acute 1, H400 Aquatic Chronic 1, H410

# JENOLITE YELLOW CALIPER PAINT GLOSS NPD10947

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
2-BUTANONE OXIME	CAS-No.: 96-29-7 EC-No.: 202-496-6 EC Index-No.: 616-014-00-0	< 1	Acute Tox. 3 (Oral), H301 Acute Tox. 4 (Dermal), H312 Skin Irrit. 2, H315 Eye Dam. 1, H318 Skin Sens. 1, H317 Carc. 2, H351 STOT SE 1, H370 STOT SE 3, H336 STOT RE 2, H373
COBALT BIS(2-ETHYLHEXANOATE)	CAS-No.: 136-52-7 EC-No.: 205-250-6	< 1	Eye Irrit. 2, H319 Skin Sens. 1, H317 Repr. 1A, H360 Repr. 2, H361 Aquatic Acute 1, H400 Aquatic Chronic 3, H412
2-ETHYLHEXANOIC ACID, ZIRCONIUM SALT	CAS-No.: 22464-99-9 EC-No.: 245-018-1	< 1	Repr. 2, H361d

Product subject to CLP Article 1.1.3.7. The disclosure rules of the components is modified in this case.

Full text of H- and EUH-statements: see section 16

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

- First-aid measures general : Call a poison center or a doctor if you feel unwell.
- First-aid measures after inhalation : Remove person to fresh air and keep comfortable for breathing.
- First-aid measures after skin contact : Wash skin with plenty of water.
- First-aid measures after eye contact : Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
- First-aid measures after ingestion : Call a poison center or a doctor if you feel unwell.

### 4.2. Most important symptoms and effects, both acute and delayed

- Symptoms/effects : May cause drowsiness or dizziness.
- Symptoms/effects after eye contact : Eye irritation.

### 4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

## SECTION 5: Firefighting measures

### 5.1. Extinguishing media

- Suitable extinguishing media : Water spray. Dry powder. Foam. Carbon dioxide.

### 5.2. Special hazards arising from the substance or mixture

- Fire hazard : Extremely flammable aerosol.
- Explosion hazard : Pressurised container: May burst if heated.
- Hazardous decomposition products in case of fire : Toxic fumes may be released.

### 5.3. Advice for firefighters

- Protection during firefighting : Do not attempt to take action without suitable protective equipment. Self-contained breathing apparatus. Complete protective clothing.

# JENOLITE YELLOW CALIPER PAINT GLOSS NPD10947

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

### SECTION 6: Accidental release measures

#### 6.1. Personal precautions, protective equipment and emergency procedures

##### 6.1.1. For non-emergency personnel

Emergency procedures : Ventilate spillage area. No open flames, no sparks, and no smoking. Avoid breathing dust/fume/gas/mist/vapours/spray. Avoid contact with skin and eyes.

##### 6.1.2. For emergency responders

Protective equipment : Do not attempt to take action without suitable protective equipment. For further information refer to section 8: "Exposure controls/personal protection".

#### 6.2. Environmental precautions

Avoid release to the environment.

#### 6.3. Methods and material for containment and cleaning up

Methods for cleaning up : Mechanically recover the product.  
Other information : Dispose of materials or solid residues at an authorized site.

#### 6.4. Reference to other sections

For further information refer to section 13.

### SECTION 7: Handling and storage

#### 7.1. Precautions for safe handling

Precautions for safe handling : Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. Do not spray on an open flame or other ignition source. Do not pierce or burn, even after use. Use only outdoors or in a well-ventilated area. Avoid breathing dust/fume/gas/mist/vapours/spray. Avoid contact with skin and eyes. Wear personal protective equipment.  
Hygiene measures : Do not eat, drink or smoke when using this product. Always wash hands after handling the product.

#### 7.2. Conditions for safe storage, including any incompatibilities

Storage conditions : Protect from sunlight. Do not expose to temperatures exceeding 50 °C/ 122 °F. Store locked up. Store in a well-ventilated place. Keep container tightly closed. Keep cool.

#### 7.3. Specific end use(s)

No additional information available

### SECTION 8: Exposure controls/personal protection

#### 8.1. Control parameters

##### 8.1.1 National occupational exposure and biological limit values

No additional information available

##### 8.1.2. Recommended monitoring procedures

No additional information available

##### 8.1.3. Air contaminants formed

No additional information available

##### 8.1.4. DNEL and PNEC

No additional information available

##### 8.1.5. Control banding

No additional information available

# JENOLITE YELLOW CALIPER PAINT GLOSS NPD10947

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

### 8.2. Exposure controls

#### 8.2.1. Appropriate engineering controls

**Appropriate engineering controls:**

Ensure good ventilation of the work station.

#### 8.2.2. Personal protection equipment

**Personal protective equipment symbol(s):**



##### 8.2.2.1. Eye and face protection

**Eye protection:**

Safety glasses

##### 8.2.2.2. Skin protection

**Skin and body protection:**

Wear suitable protective clothing

**Hand protection:**

Protective gloves

##### 8.2.2.3. Respiratory protection

**Respiratory protection:**

In case of insufficient ventilation, wear suitable respiratory equipment

##### 8.2.2.4. Thermal hazards

No additional information available

#### 8.2.3. Environmental exposure controls

**Environmental exposure controls:**

Avoid release to the environment.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

Physical state	: Liquid
Colour	: Yellow.
Odour	: Characteristic.
Odour threshold	: No data available
pH	: No data available
Relative evaporation rate (butylacetate=1)	: No data available
Melting point	: Not applicable
Freezing point	: No data available
Boiling point	: No data available
Flash point	: < 23 °C
Auto-ignition temperature	: No data available
Decomposition temperature	: No data available
Flammability (solid, gas)	: Extremely flammable aerosol.
Vapour pressure	: No data available
Relative vapour density at 20 °C	: No data available
Relative density	: No data available
Solubility	: No data available
Partition coefficient n-octanol/water (Log Pow)	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available
Explosive properties	: Pressurised container: May burst if heated.
Oxidising properties	: No data available

# JENOLITE YELLOW CALIPER PAINT GLOSS NPD10947

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Explosive limits : No data available

### 9.2. Other information

No additional information available

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

Extremely flammable aerosol. Pressurised container: May burst if heated.

### 10.2. Chemical stability

Stable under normal conditions.

### 10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

### 10.4. Conditions to avoid

Avoid contact with hot surfaces. Heat. No flames, no sparks. Eliminate all sources of ignition.

### 10.5. Incompatible materials

No additional information available

### 10.6. Hazardous decomposition products

Under normal conditions of storage and use, hazardous decomposition products should not be produced.

## SECTION 11: Toxicological information

### 11.1 Information on toxicological effects

Acute toxicity (oral) : Not classified  
Acute toxicity (dermal) : Not classified  
Acute toxicity (inhalation) : Not classified

#### D40 NAPHTHA (PETROLEUM), HYDROTREATED HEAVY, DE-AROMATISED \* (64742-48-9)

LD50 oral rat	> 5000 mg/kg
LD50 dermal	> 5000 mg/kg

Skin corrosion/irritation : Not classified  
Serious eye damage/irritation : Causes serious eye irritation.  
Respiratory or skin sensitisation : Not classified  
Germ cell mutagenicity : Not classified  
Carcinogenicity : Not classified  
Reproductive toxicity : Not classified  
STOT-single exposure : May cause drowsiness or dizziness.

#### HYDROCARBONS, C9-12, N-ALKANES, ISOALKANES, CYCLICS, (2-25%) AROMATICS

STOT-single exposure : May cause drowsiness or dizziness.

#### D40 NAPHTHA (PETROLEUM), HYDROTREATED HEAVY, DE-AROMATISED \* (64742-48-9)

STOT-single exposure : May cause drowsiness or dizziness.

#### HYDROCARBONS, C9, AROMATICS

STOT-single exposure : May cause drowsiness or dizziness. May cause respiratory irritation.

# JENOLITE YELLOW CALIPER PAINT GLOSS NPD10947

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

<b>2-BUTANONE OXIME (96-29-7)</b>	
STOT-single exposure	Causes damage to organs. May cause drowsiness or dizziness.
<b>ACETONE (67-64-1)</b>	
STOT-single exposure	May cause drowsiness or dizziness.
STOT-repeated exposure	: Not classified
<b>2-BUTANONE OXIME (96-29-7)</b>	
STOT-repeated exposure	May cause damage to organs through prolonged or repeated exposure.
Aspiration hazard	: Not classified
<b>JENOLITE YELLOW CALIPER PAINT GLOSS NPD10947</b>	
Vaporizer	Aerosol

## SECTION 12: Ecological information

### 12.1. Toxicity

Ecology - general : Harmful to aquatic life with long lasting effects.  
Hazardous to the aquatic environment, short-term (acute) : Not classified  
Hazardous to the aquatic environment, long-term (chronic) : Harmful to aquatic life with long lasting effects.  
Not rapidly degradable

<b>D40 NAPHTHA (PETROLEUM), HYDROTREATED HEAVY, DE-AROMATISED * (64742-48-9)</b>	
LC50 - Fish [1]	> 1000 mg/l
EC50 - Other aquatic organisms [1]	> 1000 mg/l
<b>HYDROCARBONS, C9, AROMATICS</b>	
LC50 - Fish [1]	9.2 mg/l
EC50 - Other aquatic organisms [1]	3.2 mg/l

### 12.2. Persistence and degradability

No additional information available

### 12.3. Bioaccumulative potential

No additional information available

### 12.4. Mobility in soil

No additional information available

### 12.5. Results of PBT and vPvB assessment

No additional information available

### 12.6. Other adverse effects

No additional information available

## SECTION 13: Disposal considerations

### 13.1. Waste treatment methods

Waste treatment methods : Dispose of contents/container in accordance with licensed collector's sorting instructions.


# JENOLITE YELLOW CALIPER PAINT GLOSS NPD10947

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

### SECTION 14: Transport information

In accordance with ADR

ADR
<b>14.1. UN number</b>
UN 1950
<b>14.2. UN proper shipping name</b>
AEROSOLS
<b>Transport document description</b>
UN 1950 AEROSOLS, 2.1, (D)
<b>14.3. Transport hazard class(es)</b>
2.1

<b>14.4. Packing group</b>
Not applicable
<b>14.5. Environmental hazards</b>
Dangerous for the environment: No
No supplementary information available

### 14.6. Special precautions for user

#### Overland transport

Classification code (ADR)	: 5F
Special provisions (ADR)	: 190, 327, 344, 625
Limited quantities (ADR)	: 1I
Excepted quantities (ADR)	: E0
Packing instructions (ADR)	: P207, LP200
Special packing provisions (ADR)	: PP87, RR6, L2
Mixed packing provisions (ADR)	: MP9
Transport category (ADR)	: 2
Special provisions for carriage - Packages (ADR)	: V14
Special provisions for carriage - Loading, unloading and handling (ADR)	: CV9, CV12
Special provisions for carriage - Operation (ADR)	: S2
Tunnel restriction code (ADR)	: D

### 14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable

### SECTION 15: Regulatory information

#### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

##### 15.1.1. EU-Regulations

Contains no REACH substances with Annex XVII restrictions

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

Contains no substance subject to Regulation (EU) No 649/2012 of the European Parliament and of the Council of 4 July 2012 concerning the export and import of hazardous chemicals.



# JENOLITE YELLOW CALIPER PAINT GLOSS NPD10947

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Contains no substance subject to Regulation (EU) No 2019/1021 of the European Parliament and of the Council of 20 June 2019 on persistent organic pollutants

Contains substance subject to Regulation (EU) 2019/1148 of the European Parliament and of the Council of 20 June 2019 on the marketing and use of explosives precursors.

### ANNEX II REPORTABLE EXPLOSIVES PRECURSORS

List of substances on their own or in mixtures or in substances for which suspicious transactions and significant disappearances and thefts are to be reported to the relevant national contact point within 24 hours.

Name	CAS-No.	Combined Nomenclature code (CN)	Combined Nomenclature code for mixture without constituents which would determine classification under another CN code
Acetone	67-64-1	2914 11 00	ex 3824 99 92

Please see [https://ec.europa.eu/home-affairs/system/files/2021-11/list\\_of\\_competent\\_authorities\\_and\\_national\\_contact\\_points\\_en.pdf](https://ec.europa.eu/home-affairs/system/files/2021-11/list_of_competent_authorities_and_national_contact_points_en.pdf)

### 15.1.2. National regulations

France	
Occupational diseases	
Code	Description
RG 84	Conditions caused by liquid organic solvents for professional use: saturated or unsaturated aliphatic or cyclic liquid hydrocarbons and mixtures thereof; liquid halogenated hydrocarbons; nitrated derivatives of aliphatic hydrocarbons; alcohols; glycols, glycol ethers; ketones; aldehydes; aliphatic and cyclic ethers, including tetrahydrofuran; esters; dimethylformamide and dimethylacetamine; acetonitrile and propionitrile; pyridine; dimethylsulfone and dimethylsulfoxide

#### Germany

Employment restrictions : Observe restrictions according Act on the Protection of Working Mothers (MuSchG)  
Observe restrictions according Act on the Protection of Young People in Employment (JArbSchG)

Water hazard class (WGK) : WGK 3, Highly hazardous to water (Classification according to AwSV, Annex 1)

Hazardous Incident Ordinance (12. BImSchV) : Is not subject of the Hazardous Incident Ordinance (12. BImSchV)

#### Netherlands

SZW-lijst van kankerverwekkende stoffen : 2-BUTANONE OXIME,PETROLEUM GASES, LIQUEFIED are listed

SZW-lijst van mutagene stoffen : PETROLEUM GASES, LIQUEFIED is listed

SZW-lijst van reprotoxische stoffen – Borstvoeding : None of the components are listed

SZW-lijst van reprotoxische stoffen – : None of the components are listed

Vruchtbaarheid

SZW-lijst van reprotoxische stoffen – Ontwikkeling : None of the components are listed

#### Denmark

Class for fire hazard : Class II-1

Store unit : 5 liter

Classification remarks : R10 <H222;H229;H319;H336;H412>; Emergency management guidelines for the storage of flammable liquids must be followed

Danish National Regulations : Young people below the age of 18 years are not allowed to use the product  
Pregnant/breastfeeding women working with the product must not be in direct contact with the product  
The requirements from the Danish Working Environment Authorities regarding work with carcinogens must be followed during use and disposal

#### Switzerland

Storage class (LK) : LK 2 - Liquefied or pressurized gases

### 15.2. Chemical safety assessment

No chemical safety assessment has been carried out

# JENOLITE YELLOW CALIPER PAINT GLOSS NPD10947

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

### SECTION 16: Other information

Abbreviations and acronyms:	
ADN	European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways
ADR	European Agreement concerning the International Carriage of Dangerous Goods by Road
ATE	Acute Toxicity Estimate
BCF	Bioconcentration factor
BLV	Biological limit value
BOD	Biochemical oxygen demand (BOD)
COD	Chemical oxygen demand (COD)
DMEL	Derived Minimal Effect level
DNEL	Derived-No Effect Level
EC-No.	European Community number
EC50	Median effective concentration
EN	European Standard
IARC	International Agency for Research on Cancer
IATA	International Air Transport Association
IMDG	International Maritime Dangerous Goods
LC50	Median lethal concentration
LD50	Median lethal dose
LOAEL	Lowest Observed Adverse Effect Level
NOAEC	No-Observed Adverse Effect Concentration
NOAEL	No-Observed Adverse Effect Level
NOEC	No-Observed Effect Concentration
OECD	Organisation for Economic Co-operation and Development
OEL	Occupational Exposure Limit
PBT	Persistent Bioaccumulative Toxic
PNEC	Predicted No-Effect Concentration
RID	Regulations concerning the International Carriage of Dangerous Goods by Rail
SDS	Safety Data Sheet
STP	Sewage treatment plant
ThOD	Theoretical oxygen demand (ThOD)
TLM	Median Tolerance Limit
VOC	Volatile Organic Compounds
CAS-No.	Chemical Abstract Service number
N.O.S.	Not Otherwise Specified
vPvB	Very Persistent and Very Bioaccumulative
ED	Endocrine disrupting properties

Full text of H- and EUH-statements:	
Acute Tox. 3 (Oral)	Acute toxicity (oral), Category 3

# JENOLITE YELLOW CALIPER PAINT GLOSS NPD10947

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Full text of H- and EUH-statements:	
Acute Tox. 4 (Dermal)	Acute toxicity (dermal), Category 4
Aquatic Acute 1	Hazardous to the aquatic environment — Acute Hazard, Category 1
Aquatic Chronic 1	Hazardous to the aquatic environment — Chronic Hazard, Category 1
Aquatic Chronic 2	Hazardous to the aquatic environment — Chronic Hazard, Category 2
Aquatic Chronic 3	Hazardous to the aquatic environment — Chronic Hazard, Category 3
Asp. Tox. 1	Aspiration hazard, Category 1
Carc. 2	Carcinogenicity, Category 2
EUH208	Contains DIPENTENE(138-86-3), 2-BUTANONE OXIME(96-29-7), COBALT BIS(2-ETHYLHEXANOATE)(136-52-7). May produce an allergic reaction.
Eye Dam. 1	Serious eye damage/eye irritation, Category 1
Eye Irrit. 2	Serious eye damage/eye irritation, Category 2
Flam. Gas 1	Flammable gases, Category 1
Flam. Liq. 2	Flammable liquids, Category 2
Flam. Liq. 3	Flammable liquids, Category 3
H220	Extremely flammable gas.
H222	Extremely flammable aerosol.
H225	Highly flammable liquid and vapour.
H226	Flammable liquid and vapour.
H229	Pressurised container: May burst if heated.
H301	Toxic if swallowed.
H304	May be fatal if swallowed and enters airways.
H312	Harmful in contact with skin.
H315	Causes skin irritation.
H317	May cause an allergic skin reaction.
H318	Causes serious eye damage.
H319	Causes serious eye irritation.
H335	May cause respiratory irritation.
H336	May cause drowsiness or dizziness.
H351	Suspected of causing cancer.
H360	May damage fertility or the unborn child.
H361	Suspected of damaging fertility or the unborn child.
H361d	Suspected of damaging the unborn child.
H370	Causes damage to organs.
H373	May cause damage to organs through prolonged or repeated exposure.
H400	Very toxic to aquatic life.
H410	Very toxic to aquatic life with long lasting effects.
H411	Toxic to aquatic life with long lasting effects.
H412	Harmful to aquatic life with long lasting effects.
Repr. 1A	Reproductive toxicity, Category 1A

# JENOLITE YELLOW CALIPER PAINT GLOSS NPD10947

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Full text of H- and EUH-statements:	
Repr. 2	Reproductive toxicity, Category 2
Skin Irrit. 2	Skin corrosion/irritation, Category 2
Skin Sens. 1	Skin sensitisation, Category 1
STOT RE 2	Specific target organ toxicity — Repeated exposure, Category 2
STOT SE 1	Specific target organ toxicity — single exposure, Category 1
STOT SE 3	Specific target organ toxicity — Single exposure, Category 3, Narcosis

Safety Data Sheet (SDS), EU

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.