

ROLINE Industrial Ethernet to Serial Media Converters (RS-232), 1x SFP

Product No.	21.13.1138
Manufacturer	ROLINE
Manufacturer No.	21.13.1138
EAN (single piece)	7611990176366



Network media converter from Ethernet (RJ-45) to serial (RS-232), for use in industrial environments - including an additional SFP port!

- Ethernet interface provides combo port of 10/100Mbps copper RJ-45 and 100M fiber SFP slot
- Serial interface RS-232
- Serial port supports baud-rate up to 230400bps
- Galvanic isolation on serial interface
- Data conversion throughput up to 230Kbps
- Wide range of direct power voltage support, DC 8V-60V
- Powered over Ethernet through RJ-45 interface (PoE-enabled)
- Alarm relay output for power failure, port link down and failure in connecting to server
- Application support for remote COM port, serial server over TCP, reverse telnet, pair connection, and serial broadcast
- Remote COM driver support for Windows PC
- Web-based and serial-based console configuration
- Event notification over SMTP and SNMP traps
- Designed for industrial environments with:
 - Terminal block and DC plug (6.3 mm/2.0 mm) power connectors
 - Fanless, rugged metal housing
- Power: Input: 8 - 60 VDC
- Power over Ethernet:

- IEEE 802.3af, voltage input range: +36 - +57VDC
- Operating Temperature: - 30 °C - +70 °C

Technical specifications	
Manufacturer	ROLINE
Product group	Network converters
Product type	Media Converter
Colour	black
Quantity of fibre ST ports	1
Fibre	Multimode
Managed	No
Technical particularity	- 30 °C - +70 °C