


## CopyMax® die-sinking cutter with thread, conical

For indexable milling inserts CMR .. SR/DR

**KIENINGER**

### Application:

The CopyMax family has been specially developed for die and mould making. With the CopyMax® 1 one-sided indexable insert and CopyMax® 2 with two fully functional blades, the customer can optimise savings potential according to the requirements of the component. The system demonstrates its qualities in particular during rough machining and in the subsequent semi-finishing process. Both tools are produced in the HQS (High Quality Sintering) manufacturing process and have precision-sintered cutting edges.



### Execution:

- Steel shank
- For round indexable milling inserts
- Conical neck

<b>Art. no.</b>	<b>16123 020</b>
<b>Brand</b>	KIENINGER
<b>Manufacturer Part Number</b>	7177699
<b>Cutting edge diameter</b>	20 mm
<b>Clearance length</b>	20 mm
<b>Length</b>	62 mm
<b>Thread dimension</b>	M12
<b>Gross Weight</b>	0.080 kg
<b>Product Group</b>	1K2