

## DDJN clamp holder, negative, left

For copy and longitudinal turning with DN indexable insert

**ATORN**<sup>®</sup>

### Application

For copy and longitudinal turning with DN indexable insert, 55°.

### Version

- Precision-manufactured steel support, burnished, hardened, adjustable clamping system, type D, working angle 93°, tip angle 55°, clearance angle 0°

### Advantage

- Streamlined geometry, optimised for contour lathe work with large feed depths and unfavourable conditions
- Negative geometry of the body ensures good stability and force absorption at large cutting depths
- Broad range of use: suitable for both finishing and roughing operations
- Adjustable clamp minimises vibrations and ensures good force transfer



<b>Art. No.</b>	<b>17826 111</b>
<b>ISO name</b>	DDJN R/L 2020 K15
<b>Shaft height</b>	20 mm
<b>Shank width</b>	20 mm
<b>Length of head</b>	34 mm
<b>Length</b>	125 mm
<b>Programming size</b>	25 mm
<b>Suitable for indexable inserts</b>	DN.. 1506..
<b>Tool design</b>	Left
<b>DIN</b>	4983

### EAN-Code

4050293127232