



SAFETY DATA SHEET

Swarfega Jizer

According to Regulation (EC) No 1907/2006, Annex II, as amended by Regulation (EU) No 453/2010

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name Swarfega Jizer

Product number SJZ100L,SJZ200L,SJZ25L,SJZ5L,SJZ5LFR,SJZ5LRS,SJZ750MLRS,8057,SJZ750SFX,7118511,7118515

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Detergent.

1.3. Details of the supplier of the safety data sheet

Supplier Deb Ltd
Denby Hall Way
Denby
Derbyshire
DE5 8JZ
Main Tel. 01773 855100
Technical Tel 01773 855105
reach@deb.co.uk

1.4. Emergency telephone number

Emergency telephone National Poisons Information Service (UK) 0844 8920111

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification

Physical hazards Not Classified

Health hazards Eye Irrit. 2 - H319 Asp. Tox. 1 - H304

Environmental hazards Not Classified

Classification (67/548/EEC or 1999/45/EC) Xn;R65. R66.

Environmental The product does not meet the requirement for classification as an environmental hazard in accordance with directive 1999/45/EEC

2.2. Label elements

Pictogram



Signal word Danger

Swarfega Jizer

Hazard statements	H304 May be fatal if swallowed and enters airways. H319 Causes serious eye irritation.
Precautionary statements	P264 Wash contaminated skin thoroughly after handling. P280 Wear protective gloves/protective clothing/eye protection/face protection. P301+P310 IF SWALLOWED: Immediately call a POISON CENTER/doctor. P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. P331 Do NOT induce vomiting. P337+P313 If eye irritation persists: Get medical advice/attention. P405 Store locked up. P501 Dispose of contents/container in accordance with national regulations.
Supplemental label information	EUH066 Repeated exposure may cause skin dryness or cracking.
Contains	DISTILLATES PETROLEUM HYDROCARBON LIGHT
Detergent labelling	aliphatic hydrocarbons, < 5% non-ionic surfactants
Supplementary precautionary statements	P264 Wash contaminated skin thoroughly after handling. P405 Store locked up.

2.3. Other hazards

This substance is not classified as PBT or vPvB according to current EU criteria.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

DISTILLATES PETROLEUM HYDROCARBON LIGHT		60-100%
CAS number: 64742-47-8	EC number: 926-141-6	REACH registration number: 01-2119456620-43-XXXX
Classification Asp. Tox. 1 - H304	Classification (67/548/EEC or 1999/45/EC) Xn;R65. R66.	
ISOTRIDECANOL, ETHOXYLATED (2-5EO)		1-5%
CAS number: 68439-45-2		
Classification Eye Dam. 1 - H318	Classification (67/548/EEC or 1999/45/EC) Xi;R41.	

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation	Move affected person to fresh air at once. Get medical attention.
Ingestion	Never give anything by mouth to an unconscious person. Do not induce vomiting. Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing. Get medical attention immediately.
Skin contact	Remove contaminated clothing. Wash skin thoroughly with soap and water. Get medical attention promptly if symptoms occur after washing.

Swarfega Jizer

Eye contact Remove any contact lenses and open eyelids wide apart. Continue to rinse for at least 15 minutes and get medical attention.

4.2. Most important symptoms and effects, both acute and delayed

Inhalation Vapours in high concentrations are anaesthetic. Symptoms following overexposure may include the following: Headache. Fatigue. Dizziness. Central nervous system depression. Irritation of nose, throat and airway.

Ingestion Fumes from the stomach contents may be inhaled resulting in the same symptoms as inhalation. Central nervous system depression. May cause stomach pain or vomiting. Diarrhoea.

Skin contact Prolonged contact may cause redness, irritation and dry skin.

Eye contact May cause temporary eye irritation.

4.3. Indication of any immediate medical attention and special treatment needed

Notes for the doctor No specific recommendations.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media Extinguish with foam, carbon dioxide, dry powder or water fog.

Unsuitable extinguishing media Do not use water jet as an extinguisher, as this will spread the fire.

5.2. Special hazards arising from the substance or mixture

Hazardous combustion products Protection against nuisance dust must be used when the airborne concentration exceeds 10 mg/m³. Oxides of carbon.

5.3. Advice for firefighters

Protective actions during firefighting Wear positive-pressure self-contained breathing apparatus (SCBA) and appropriate protective clothing.

Special protective equipment for firefighters Wear positive-pressure self-contained breathing apparatus (SCBA) and appropriate protective clothing.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions For personal protection, see Section 8.

6.2. Environmental precautions

Environmental precautions Do not discharge into drains or watercourses or onto the ground.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up Wear suitable protective equipment, including gloves, goggles/face shield, respirator, boots, clothing or apron, as appropriate. Absorb in vermiculite, dry sand or earth and place into containers. Avoid the spillage or runoff entering drains, sewers or watercourses.

6.4. Reference to other sections

Reference to other sections For personal protection, see Section 8.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Usage precautions Avoid spilling. Avoid contact with skin and eyes. Provide adequate ventilation.

Swarfega Jizer

7.2. Conditions for safe storage, including any incompatibilities

Storage precautions Store in tightly closed original container in a dry, cool and well-ventilated place.

7.3. Specific end use(s)

Specific end use(s) The identified uses for this product are detailed in Section 1.2.

SECTION 8: Exposure Controls/personal protection

8.1. Control parameters

Ingredient comments None.

8.2. Exposure controls

Protective equipment



Appropriate engineering controls Provide adequate general and local exhaust ventilation.

Eye/face protection The following protection should be worn: Chemical splash goggles.

Hand protection Use protective gloves. The most suitable glove should be chosen in consultation with the glove supplier/manufacturer, who can provide information about the breakthrough time of the glove material. **SPECIFIC RECOMMENDATIONS.** Wear protective gloves made of the following material: Nitrile rubber. Polyvinyl alcohol (PVA).

Other skin and body protection Wear appropriate clothing to prevent any possibility of liquid contact and repeated or prolonged vapour contact.

Hygiene measures **DO NOT SMOKE IN WORK AREA!** Wash hands at the end of each work shift and before eating, smoking and using the toilet. Promptly remove any clothing that becomes contaminated. Wash promptly with soap and water if skin becomes contaminated. Use appropriate skin cream to prevent drying of skin.

Respiratory protection No specific recommendations. Respiratory protection may be required if excessive airborne contamination occurs. In confined or poorly-ventilated spaces, a supplied-air respirator must be worn.

SECTION 9: Physical and Chemical Properties

9.1. Information on basic physical and chemical properties

Appearance	Liquid
Colour	Red.
Odour	Characteristic.
Odour threshold	Not determined. Not determined.
pH	Scientifically unjustified.
Melting point	Not determined.
Initial boiling point and range	Not determined.
Flash point	Not determined.
Evaporation rate	Not determined.

Swarfega Jizer

Upper/lower flammability or explosive limits	Not determined. : : Not determined.
Vapour pressure	Not determined.
Vapour density	Not determined.
Relative density	0.798-0.818 @ 25 C°C
Partition coefficient	Not determined.
Auto-ignition temperature	Not determined.
Decomposition Temperature	Not determined.
Viscosity	Not determined.
Explosive properties	Not determined.
Oxidising properties	Does not meet the criteria for classification as oxidising.

9.2. Other information

Other information None.

SECTION 10: Stability and reactivity

10.1. Reactivity

Reactivity There are no known reactivity hazards associated with this product.

10.2. Chemical stability

Stability Stable at normal ambient temperatures.

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions Does not decompose when used and stored as recommended. No potentially hazardous reactions known.

10.4. Conditions to avoid

Conditions to avoid Avoid heat, flames and other sources of ignition.

10.5. Incompatible materials

Materials to avoid Avoid contact with strong oxidising agents. Strong acids.

10.6. Hazardous decomposition products

Hazardous decomposition products Fire creates: Toxic gases/vapours/fumes of: Carbon monoxide (CO). Carbon dioxide (CO₂).

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity - dermal

Notes (dermal LD₅₀) No information available.

Acute toxicity - inhalation

Notes (inhalation LC₅₀) Not determined.

Skin corrosion/irritation

Animal data Based on available data the classification criteria are not met.

Skin sensitisation

Skin sensitisation Based on available data the classification criteria are not met.

Swarfega Jizer

Germ cell mutagenicity

Genotoxicity - in vivo Based on available data the classification criteria are not met.

Carcinogenicity

Carcinogenicity Does not contain any substances known to be carcinogenic.

Reproductive toxicity

Reproductive toxicity - development Does not contain any substances known to be toxic to reproduction.

Specific target organ toxicity - single exposure

STOT - single exposure No information available.

Specific target organ toxicity - repeated exposure

STOT - repeated exposure No information available.

Inhalation Prolonged inhalation of high concentrations may damage respiratory system.

Ingestion Harmful: may cause lung damage if swallowed.

Skin contact Prolonged contact may cause dryness of the skin.

Eye contact May cause temporary eye irritation.

Toxicological information on ingredients.

DISTILLATES PETROLEUM HYDROCARBON LIGHT

Acute toxicity - oral

Acute toxicity oral (LD₅₀) 5,000.0
mg/kg

Acute toxicity - dermal

Acute toxicity dermal (LD₅₀) 5,000.0
mg/kg

Acute toxicity - inhalation

Notes (inhalation LC₅₀) LC50 (8h) >5000mg/m³ rat OECD 403

Skin corrosion/irritation

Animal data Erythema/eschar score: Well defined erythema (2). Oedema score: Very slight oedema - barely perceptible (1).

Serious eye damage/irritation

Serious eye damage/irritation Based on available data the classification criteria are not met.

Respiratory sensitisation

Respiratory sensitisation Guinea pig: Not sensitising.

Skin sensitisation

Skin sensitisation Guinea pig maximization test (GPMT) - Guinea pig: Not sensitising. Repeated exposure may cause skin dryness or cracking.

Germ cell mutagenicity

Swarfega Jizer

Genotoxicity - in vitro	Genome mutation: Negative.
Genotoxicity - in vivo	Based on available data the classification criteria are not met.
<u>Carcinogenicity</u>	
Carcinogenicity	NOAEC \geq 2200/1100 mg/m ³ , ,
<u>Reproductive toxicity</u>	
Reproductive toxicity - fertility	- NOAEL 750 mg/kg/day, Oral, Rat F1
Reproductive toxicity - development	- NOAEL: \geq 5220 mg/m ³ , Inhalation, Rat
<u>Specific target organ toxicity - single exposure</u>	
STOT - single exposure	Based on available data the classification criteria are not met.
<u>Specific target organ toxicity - repeated exposure</u>	
STOT - repeated exposure	Based on available data the classification criteria are not met.
<u>Aspiration hazard</u>	
Aspiration hazard	May be fatal if swallowed and enters airways.

ISOTRIDECANOL, ETHOXYLATED (2-5EO)

<u>Acute toxicity - oral</u>	
Acute toxicity oral (LD₅₀ mg/kg)	5,050.0
Species	Rat
ATE oral (mg/kg)	5,050.0
<u>Acute toxicity - dermal</u>	
Acute toxicity dermal (LD₅₀ mg/kg)	2,000.0
Species	Rat

OLEOYL SARCOSINE

<u>Acute toxicity - inhalation</u>	
ATE inhalation (vapours mg/l)	11.0

SECTION 12: Ecological Information

Ecotoxicity	Not regarded as dangerous for the environment.
<u>12.1. Toxicity</u>	
Toxicity	The product does not meet the requirement for classification as an environmental hazard in accordance with directive 1999/45/EEC
Acute toxicity - fish	LC ₅₀ , 96 hours: >1000 mg/l, Fish

Swarfega Jizer

Acute toxicity - aquatic invertebrates EC₅₀, 48 hours: >1000 mg/l, Daphnia magna

Acute toxicity - aquatic plants IC₅₀, 72 hours: >1000 mg/l, Algae

Acute toxicity - terrestrial Not known.

Ecological information on ingredients.

DISTILLATES PETROLEUM HYDROCARBON LIGHT

Acute toxicity - fish LC₅₀, 96 hours: >1000 mg/l, Fish

Acute toxicity - aquatic invertebrates EC₅₀, 48 hours: >1000 mg/l, Daphnia magna

Acute toxicity - aquatic plants IC₅₀, 72 hours: >1000 mg/l, Algae

Acute toxicity - microorganisms EL50, 48 hour: >10000 mg/l,

Chronic toxicity - aquatic invertebrates , 21 days, 21 days: 1.22 mg/l, Daphnia magna

OLEOYL SARCOSINE

Acute aquatic toxicity

LE(C)₅₀ 0.1 < L(E)C₅₀ ≤ 1

M factor (Acute) 1

Acute toxicity - fish LC₅₀, 96 hours, 96 hours: 1.7 mg/l, Brachydanio rerio (Zebra Fish)

Acute toxicity - aquatic invertebrates EC₅₀, : 0.68 mg/l, Daphnia magna

12.2. Persistence and degradability

Persistence and degradability The product is biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential No data available on bioaccumulation.

Partition coefficient Not determined.

12.4. Mobility in soil

Mobility The product contains volatile substances, which may spread in the atmosphere.

12.5. Results of PBT and vPvB assessment

Results of PBT and vPvB assessment This product does not contain any substances classified as PBT or vPvB.

12.6. Other adverse effects

Other adverse effects Not determined.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Swarfega Jizer

General information	Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority.
Disposal methods	Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority. Avoid the spillage or runoff entering drains, sewers or watercourses. Residues and empty containers should be taken care of as hazardous waste according to local and national provisions.

SECTION 14: Transport information

General	The product is not covered by international regulations on the transport of dangerous goods (IMDG, IATA, ADR/RID).
Road transport notes	Not classified.
Rail transport notes	Not classified.
Sea transport notes	Not classified.
Air transport notes	Not classified.
<u>14.1. UN number</u>	
Not applicable.	
UN No. (IMDG)	
UN No. (ICAO)	
<u>14.2. UN proper shipping name</u>	
Not applicable.	
<u>14.3. Transport hazard class(es)</u>	
ADR/RID class	
ADR/RID subsidiary risk	
ADR/RID label	
IMDG class	
IMDG subsidiary risk	
ICAO class/division	
ICAO subsidiary risk	
Transport labels	
<u>14.4. Packing group</u>	
Not applicable.	
ADR/RID packing group	
IMDG packing group	
ICAO packing group	
<u>14.5. Environmental hazards</u>	
Environmentally hazardous substance/marine pollutant	
No.	
<u>14.6. Special precautions for user</u>	

Swarfega Jizer

Not applicable.

EmS

Emergency Action Code

**Hazard Identification Number
(ADR/RID)**

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

**Transport in bulk according to
Annex II of MARPOL 73/78
and the IBC Code** Not relevant.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

EU legislation

Commission Directive 2000/39/EC of 8 June 2000 establishing a first list of indicative occupational exposure limit values in implementation of Council Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work (as amended).

Commission Directive 91/322/EEC of 29 May 1991 on establishing indicative limit values by implementing Council Directive 80/1107/EEC on the protection of workers from the risks related to exposure to chemical, physical and biological agents at work.

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) (as amended).

Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures (as amended).

15.2. Chemical safety assessment

No chemical safety assessment has been carried out.

SECTION 16: Other information

General information

Only trained personnel should use this material.

**Key literature references and
sources for data**

Where Exposure Scenarios for the substances listed in Section 3 are available they have been assessed for the uses identified in this data sheet or on the product label and the appropriate relevant information is incorporated into this Safety Data Sheet.

Revision comments

New REACH Annex 2 Compliant MSDS

Revision date

21/10/2015

Revision

2

Supersedes date

09/05/2015

Risk phrases in full

R41 Risk of serious damage to eyes.
R65 Harmful: may cause lung damage if swallowed.
R66 Repeated exposure may cause skin dryness or cracking.

Hazard statements in full

H304 May be fatal if swallowed and enters airways.
H318 Causes serious eye damage.
H319 Causes serious eye irritation.

**Notes for Risk Phrases and
Hazard Statements in Full**

The full text for Risk Phrases and Hazard Statements in section 16 relates to the reference numbers in sections 2 and 3 and not necessarily the finished product classification.