



Figure similar

SIMATIC S7-1500, CM PTP RS232 HF Communication module for Serial connection RS232, Freeport, 3964 (R), USS, MODBUS RTU Master, Slave, 115200 Kbit/s, 9-pin D-sub connector

General information	
Product type designation	CM PtP RS 232 HF
Product function	
<ul style="list-style-type: none"> I&M data Fast startup 	Yes; I&M 0 Yes
Engineering with	
<ul style="list-style-type: none"> STEP 7 TIA Portal configurable/integrated from version STEP 7 configurable/integrated from version PROFIBUS from GSD version/GSD revision PROFINET from GSD version/GSD revision 	V12 / V12 V5.5 SP2 with GSD file - / - V2.3 / -
Installation type/mounting	
Rail mounting	Yes; S7-1500 mounting rail
Supply voltage	
Design of the power supply	system power supply
Input current	
Current consumption (rated value)	50 mA; From the backplane bus
Power	
Power available from the backplane bus	0.75 W
Power loss	
Power loss, typ.	0.6 W
Address area	
Address space per module	
<ul style="list-style-type: none"> Inputs 	8 byte
Interface types	
RS 232	
<ul style="list-style-type: none"> Transmission rate, max. Cable length, max. RS 232 auxiliary signals 	115.2 kbit/s 15 m RTS, CTS, DTR, DSR, RI, DCD
Protocols	
Integrated protocols	
Freeport	
<ul style="list-style-type: none"> Telegram length, max. Bits per character Number of stop bits Parity 	4 kbyte 7 or 8 1 or 2 bit None, even, odd, always 1, always 0, any
3964 (R)	
<ul style="list-style-type: none"> Telegram length, max. 	4 kbyte

— Bits per character	7 or 8
— Number of stop bits	1 or 2 bit
— Parity	None, even, odd, always 1, always 0, any
Modbus RTU master	
— Address area	1 to 247, extended 1 to 65535
— Number of slaves, max.	1
MODBUS RTU slave	
— Address area	1 to 247, extended 1 to 65535
Telegram buffer	
• Buffer memory for telegrams	8 kbyte
• Number of telegrams which can be buffered	255
Interrupts/diagnostics/status information	
Diagnostics function	Yes
Alarms	
• Diagnostic alarm	Yes
• Hardware interrupt	No
Diagnoses	
• Wire-break	Yes
Diagnostics indication LED	
• RUN LED	Yes; green LED
• ERROR LED	Yes; red LED
• Receive RxD	Yes; Yellow LED
• Transmit TxD	Yes; Yellow LED
Potential separation	
between backplane bus and interface	Yes
Isolation	
Isolation tested with	707 V DC (type test)
Ambient conditions	
Ambient temperature during operation	
• horizontal installation, min.	0 °C
• horizontal installation, max.	60 °C
• vertical installation, min.	0 °C
• vertical installation, max.	40 °C
Altitude during operation relating to sea level	
• Installation altitude above sea level, max.	5 000 m; restrictions for installation altitudes > 2 000 m, see ET 200MP system manual
Decentralized operation	
to SIMATIC S7-300	Yes
to SIMATIC S7-400	Yes
to SIMATIC S7-1500	Yes
to standard PROFINET controller	Yes
Dimensions	
Width	35 mm
Height	147 mm
Depth	127 mm
Weights	
Weight, approx.	0.22 kg
last modified:	11/3/2021 