

Safety data sheet according to 1907/2006/EC, Article 31

Printing date 25.01.2017




Version number 68

Revision: 23.12.2016

SECTION 1: Identification of the substance/mixture and of the company/undertaking

- **1.1 Product identifier**
- **Trade name:** PLASTI-KOTE® FABRIC PROTECTOR 116001 6UC EU 400 ML
- **Article number:** 440.0116001.076
- **1.2 Relevant identified uses of the substance or mixture and uses advised against**
- **Sector of Use**
 - SU21 Consumer uses: Private households / general public / consumers
 - SU22 Professional uses: Public domain (administration, education, entertainment, services, craftsmen)
- **Product category** PC34 Textile dyes, and impregnating products
- **Process category**
 - PROC7 Industrial spraying
 - PROC11 Non industrial spraying
- **Environmental release category**
 - ERC8a Widespread use of non-reactive processing aid (no inclusion into or onto article, indoor)
 - ERC8d Widespread use of non-reactive processing aid (no inclusion into or onto article, outdoor)
- **Application of the substance / the mixture** Preparation
- **1.3 Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
 - MOTIP DUPLI B.V.
 - Wolfraamweg 2
 - NL-8471 XC Wolvega
 - Nederland
 - Tel : +31 (0)561 694400
 - Fax: +31 (0)561 694411
 - e-mail: info@nl.motipdupli.com
- **Further information obtainable from:** Department Product Safety
- **1.4 Emergency telephone number:** +31 (0)561-694400 (09:00h - 17:00h)

SECTION 2: Hazards identification

- **2.1 Classification of the substance or mixture**
 - **Classification according to Regulation (EC) No 1272/2008**
-  **GHS02 flame**
- Aerosol 1 H222-H229 Extremely flammable aerosol. Pressurised container: May burst if heated.
-  **GHS09 environment**
- Aquatic Chronic 2 H411 Toxic to aquatic life with long lasting effects.
-  **GHS07**
- | | | |
|---------------|------|------------------------------------|
| Skin Irrit. 2 | H315 | Causes skin irritation. |
| Eye Irrit. 2 | H319 | Causes serious eye irritation. |
| STOT SE 3 | H336 | May cause drowsiness or dizziness. |

(Contd. on page 2)

GB

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 25.01.2017

Version number 68

Revision: 23.12.2016

Trade name: **PLASTI-KOTE® FABRIC PROTECTOR 116001 6UC EU 400 ML**

(Contd. of page 1)

· **2.2 Label elements**· **Labelling according to Regulation (EC) No 1272/2008**

The product is classified and labelled according to the CLP regulation.

· **Hazard pictograms**

GHS02 GHS07 GHS09

· **Signal word** *Danger*· **Hazard-determining components of labelling:***Naphtha (petroleum), hydrotreated light**propan-2-ol**n-butyl acetate*· **Hazard statements***H222-H229 Extremely flammable aerosol. Pressurised container: May burst if heated.**H315 Causes skin irritation.**H319 Causes serious eye irritation.**H336 May cause drowsiness or dizziness.**H411 Toxic to aquatic life with long lasting effects.*· **Precautionary statements***P102 Keep out of reach of children.**P260 Do not breathe spray.**P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.**P251 Do not pierce or burn, even after use.**P211 Do not spray on an open flame or other ignition source.**P410+P412 Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.**P501 Dispose of contents/container in accordance with local regulations.*· **2.3 Other hazards**· **Results of PBT and vPvB assessment**· **PBT:** Not applicable.· **vPvB:** Not applicable.* **SECTION 3: Composition/information on ingredients**· **3.2 Chemical characterisation: Mixtures**· **Description:** Mixture of substances listed below with nonhazardous additions.· **Dangerous components:**

EC number: 921-024-6 Reg.nr.: 01-2119475514-35	<i>Naphtha (petroleum), hydrotreated light</i> ----- Flam. Liq. 2, H225 Asp. Tox. 1, H304 Aquatic Chronic 2, H411 Skin Irrit. 2, H315; STOT SE 3, H336	50-75%
CAS: 74-98-6 EINECS: 200-827-9 Index number: 601-003-00-5 Reg.nr.: 01-2119486944-21-xxxx	<i>propane</i> ----- Flam. Gas 1, H220 Press. Gas C, H280	12.5-20%
CAS: 67-63-0 EINECS: 200-661-7 Index number: 603-117-00-0 Reg.nr.: 01-2119457558-25-xxxx	<i>propan-2-ol</i> ----- Flam. Liq. 2, H225 Eye Irrit. 2, H319; STOT SE 3, H336	10-12.5%

(Contd. on page 3)

GB

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 25.01.2017

Version number 68

Revision: 23.12.2016

Trade name: PLASTI-KOTE® FABRIC PROTECTOR 116001 6UC EU 400 ML

(Contd. of page 2)

CAS: 106-97-8 EINECS: 203-448-7 Index number: 601-004-00-0 Reg.nr.: 01-2119474691-32-xxxx	butane ----- ⚠ Flam. Gas 1, H220 ⚠ Press. Gas C, H280	5-10%
CAS: 75-28-5 EINECS: 200-857-2 Index number: 601-004-00-0 Reg.nr.: 01-2119485395-27-xxxx	isobutane ----- ⚠ Flam. Gas 1, H220 ⚠ Press. Gas C, H280	5-10%
CAS: 123-86-4 EINECS: 204-658-1 Index number: 607-025-00-1 Reg.nr.: 01-2119485493-29-xxxx	n-butyl acetate ----- ⚠ Flam. Liq. 3, H226 ⚠ STOT SE 3, H336	2.5-5%

· **Additional information:** For the wording of the listed hazard phrases refer to section 16.

SECTION 4: First aid measures

- **4.1 Description of first aid measures**
- **After inhalation:** Supply fresh air; consult doctor in case of complaints.
- **After skin contact:** Generally the product does not irritate the skin.
- **After eye contact:** Rinse opened eye for several minutes under running water. Then consult a doctor.
- **After swallowing:** Drink plenty of water and provide fresh air. Call for a doctor immediately.
- **4.2 Most important symptoms and effects, both acute and delayed** No further relevant information available.
- **4.3 Indication of any immediate medical attention and special treatment needed**
No further relevant information available.

SECTION 5: Firefighting measures

- **5.1 Extinguishing media**
- **Suitable extinguishing agents:**
CO₂, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.
- **For safety reasons unsuitable extinguishing agents:** Water with full jet
- **5.2 Special hazards arising from the substance or mixture** No further relevant information available.
- **5.3 Advice for firefighters**
- **Protective equipment:** No special measures required.

SECTION 6: Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures**
Ensure adequate ventilation
Keep away from ignition sources.
- **6.2 Environmental precautions:**
Do not allow product to reach sewage system or any water course.
Inform respective authorities in case of seepage into water course or sewage system.
Do not allow to enter sewers/ surface or ground water.
- **6.3 Methods and material for containment and cleaning up:** Ensure adequate ventilation.
- **6.4 Reference to other sections**
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.

SECTION 7: Handling and storage

- **7.1 Precautions for safe handling** Ensure good ventilation/exhaustion at the workplace.

(Contd. on page 4)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 25.01.2017

Version number 68

Revision: 23.12.2016

Trade name: **PLASTI-KOTE® FABRIC PROTECTOR 116001 6UC EU 400 ML**

(Contd. of page 3)

- **Information about fire - and explosion protection:**
Do not spray onto a naked flame or any incandescent material.
Keep ignition sources away - Do not smoke.
Protect against electrostatic charges.
Pressurised container: protect from sunlight and do not expose to temperatures exceeding 50 °C, i.e. electric lights. Do not pierce or burn, even after use.
- **7.2 Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:**
Store in a cool location.
Observe official regulations on storing packagings with pressurised containers.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** Protect from heat and direct sunlight.
- **7.3 Specific end use(s):** No further relevant information available.

SECTION 8: Exposure controls/personal protection

- **Additional information about design of technical facilities:** No further data; see item 7.

8.1 Control parameters

- **Ingredients with limit values that require monitoring at the workplace:**

67-63-0 propan-2-ol

WEL	Short-term value: 1250 mg/m ³ , 500 ppm Long-term value: 999 mg/m ³ , 400 ppm
-----	--

106-97-8 butane

WEL	Short-term value: 1810 mg/m ³ , 750 ppm Long-term value: 1450 mg/m ³ , 600 ppm Carc (if more than 0.1% of buta-1.3-diene)
-----	---

123-86-4 n-butyl acetate

WEL	Short-term value: 966 mg/m ³ , 200 ppm Long-term value: 724 mg/m ³ , 150 ppm
-----	---

- **Additional information:** The lists valid during the making were used as basis.

8.2 Exposure controls

- **Personal protective equipment:**
- **General protective and hygienic measures:**
Wash hands before breaks and at the end of work.
Do not inhale gases / fumes / aerosols.
- **Respiratory protection:** Not required.
- **Protection of hands:** Not required.
- **Material of gloves:** Not required.
- **Penetration time of glove material:** Not required.
- **Eye protection:**



Tightly sealed goggles

SECTION 9: Physical and chemical properties

- **9.1 Information on basic physical and chemical properties**

General Information

- **Appearance:**

Form: Aerosol

(Contd. on page 5)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 25.01.2017

Version number 68

Revision: 23.12.2016

Trade name: **PLASTI-KOTE® FABRIC PROTECTOR 116001 6UC EU 400 ML**

(Contd. of page 4)

Colour:	Light yellow
· Odour:	Solvent-like
· Odour threshold:	Not determined.
· pH-value:	Not determined.
· Change in condition	
Melting point/Melting range:	Undetermined.
Boiling point/Boiling range:	Not applicable, as aerosol.
· Flash point:	<0 °C (<32 °F) Not applicable, as aerosol.
· Flammability (solid, gaseous):	Not applicable.
· Ignition temperature:	> 200 °C (> 392 °F)
· Decomposition temperature:	Not determined.
· Self-igniting:	Product is not selfigniting.
· Danger of explosion:	Product is not explosive. However, formation of explosive air/vapour mixtures are possible.
· Explosion limits:	
Lower:	0.6 Vol %
Upper:	12.0 Vol %
· Vapour pressure at 20 °C (68 °F):	3500 hPa (2625 mm Hg)
· Density at 20 °C (68 °F):	0.668 g/cm ³ (5.574 lbs/gal)
· Relative density	Not determined.
· Vapour density	Not determined.
· Evaporation rate	Not applicable.
· Solubility in / Miscibility with water:	Not miscible or difficult to mix.
· Partition coefficient (n-octanol/water):	Not determined.
· Viscosity:	
Dynamic:	Not determined.
Kinematic:	Not determined.
· Solvent content:	
Organic solvents:	98.7 %
· EU-VOC:	659.6 g/l
· EU-VOC in %:	98.75 %
· Solids content:	1.3 %
· 9.2 Other information	No further relevant information available.

SECTION 10: Stability and reactivity

- **10.1 Reactivity** No further relevant information available.
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known.
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** No dangerous decomposition products known.

GB

(Contd. on page 6)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 25.01.2017

Version number 68

Revision: 23.12.2016

Trade name: PLASTI-KOTE® FABRIC PROTECTOR 116001 6UC EU 400 ML

(Contd. of page 5)

SECTION 11: Toxicological information

- **11.1 Information on toxicological effects**
- **Acute toxicity** Based on available data, the classification criteria are not met.

- **LD/LC50 values relevant for classification:**

Naphtha (petroleum), hydrotreated light

Oral	LD50	>5840 mg/kg (rat)
Dermal	LD50	>2920 mg/kg (rabbit)
Inhalative	LC50 / 4h	> 2 mg/l (rat)

67-63-0 propan-2-ol

Oral	LD50	5045 mg/kg (rat)
Dermal	LD50	12800 mg/kg (rabbit)
Inhalative	LC50 / 4 h	30 mg/m3 (rat)

106-97-8 butane

Inhalative	LC50 / 4 h	658000 mg/m3 (rat)
------------	------------	--------------------

123-86-4 n-butyl acetate

Oral	LD50	10770 mg/kg (rat)
Dermal	LD50	>17600 mg/kg (rabbit)
Inhalative	LC50 / 4 h	>21.0 mg/m3 (rat)

- **Primary irritant effect:**
- **Skin corrosion/irritation**
Causes skin irritation.
- **Serious eye damage/irritation**
Causes serious eye irritation.
- **Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.
- **CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)**
- **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
- **Carcinogenicity** Based on available data, the classification criteria are not met.
- **Reproductive toxicity** Based on available data, the classification criteria are not met.
- **STOT-single exposure**
May cause drowsiness or dizziness.
- **STOT-repeated exposure** Based on available data, the classification criteria are not met.
- **Aspiration hazard** Based on available data, the classification criteria are not met.

SECTION 12: Ecological information

- **12.1 Toxicity**

- **Aquatic toxicity:**

Naphtha (petroleum), hydrotreated light

EC50 / 48 h	3 mg/l (Daphnia magna)
EC50 / 72 h	30-100 mg/l (Pseudokirchneriella Subcapitata)
LC50 / 96 h	11.4 mg/l (fish)

67-63-0 propan-2-ol

EC50 / 48 h	13299 mg/l (daphnia magna)
LC50 / 96 h (dynamic)	4200 mg/l (fish)

123-86-4 n-butyl acetate

EC50 / 48 h	44 mg/l (daphnia magna)
EC50 / 96 h	320 mg/l (algae)
LC50 / 24 h	205 mg/l (daphnia magna)
LC50 / 96 h	18 mg/l (Pimephales promelas)

(Contd. on page 7)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 25.01.2017

Version number 68

Revision: 23.12.2016

Trade name: **PLASTI-KOTE® FABRIC PROTECTOR 116001 6UC EU 400 ML**

(Contd. of page 6)

- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
- **Ecotoxicological effects:**
- **Remark:** Toxic for fish
- **Additional ecological information:**
- **General notes:**
Water hazard class 2 (German Regulation) (Self-assessment): hazardous for water
Do not allow product to reach ground water, water course or sewage system.
Danger to drinking water if even small quantities leak into the ground.
Also poisonous for fish and plankton in water bodies.
Toxic for aquatic organisms
- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **12.6 Other adverse effects** No further relevant information available.

SECTION 13: Disposal considerations





- **13.1 Waste treatment methods**
- **Recommendation**
Must not be disposed together with household garbage. Do not allow product to reach sewage system.

- **European waste catalogue**

14 06 03*	other solvents and solvent mixtures
15 01 04	metallic packaging

- **Uncleaned packaging:**
- **Recommendation:** Non contaminated packagings may be recycled.

SECTION 14: Transport information

- **14.1 UN-Number**
 - **ADR, IMDG, IATA** UN1950
 - **14.2 UN proper shipping name**
 - **ADR** 1950 AEROSOLS, ENVIRONMENTALLY HAZARDOUS
 - **IMDG** AEROSOLS (Naphtha (petroleum), hydrotreated light), MARINE POLLUTANT
 - **IATA** AEROSOLS, flammable
 - **14.3 Transport hazard class(es)**
 - **ADR**
- 

- **Class** 2 5F Gases.
 - **Label** 2.1
-
- **IMDG**
- 

- **Class** 2.1

(Contd. on page 8)

GB

Safety data sheet
according to 1907/2006/EC, Article 31


Printing date 25.01.2017

Version number 68

Revision: 23.12.2016

Trade name: **PLASTI-KOTE® FABRIC PROTECTOR 116001 6UC EU 400 ML**

(Contd. of page 7)

· Label	2.1
· IATA	
	
· Class	2.1
· Label	2.1
· 14.4 Packing group · ADR, IMDG, IATA	Void
· 14.5 Environmental hazards: · Marine pollutant:	No Symbol (fish and tree)
· Special marking (ADR):	Symbol (fish and tree)
· 14.6 Special precautions for user · Danger code (Kemler): · EMS Number: · Stowage Code	Warning: Gases. - F-D,S-U SW1 Protected from sources of heat. SW22 For AEROSOLS with a maximum capacity of 1 litre: Category A. For AEROSOLS with a capacity above 1 litre: Category B. For WASTE AEROSOLS: Category C, Clear of living quarters.
· Segregation Code	SG69 For AEROSOLS with a maximum capacity of 1 litre: Segregation as for class 9. Stow "separated from" class 1 except for division 1.4. For AEROSOLS with a capacity above 1 litre: Segregation as for the appropriate subdivision of class 2. For WASTE AEROSOLS: Segregation as for the appropriate subdivision of class 2.
· 14.7 Transport in bulk according to Annex II of Marpol and the IBC Code	Not applicable.
· Transport/Additional information:	
· ADR · Limited quantities (LQ) · Excepted quantities (EQ)	1L Code: E0 Not permitted as Excepted Quantity
· Transport category · Tunnel restriction code	2 D
· IMDG · Limited quantities (LQ) · Excepted quantities (EQ)	1L Code: E0 Not permitted as Excepted Quantity
· UN "Model Regulation":	UN 1950 AEROSOLS, 2.1, ENVIRONMENTALLY HAZARDOUS

SECTION 15: Regulatory information

- 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture
- Directive 2012/18/EU
- Named dangerous substances - ANNEX I None of the ingredients is listed.

(Contd. on page 9)

GB

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 25.01.2017

Version number 68

Revision: 23.12.2016

Trade name: PLASTI-KOTE® FABRIC PROTECTOR 116001 6UC EU 400 ML

(Contd. of page 8)

- **Seveso category**
P3a **FLAMMABLE AEROSOLS**
E2 *Hazardous to the Aquatic Environment*
- **Qualifying quantity (tonnes) for the application of lower-tier requirements** 150 t
- **Qualifying quantity (tonnes) for the application of upper-tier requirements** 500 t
- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· **Relevant phrases**

- H220 *Extremely flammable gas.*
- H225 *Highly flammable liquid and vapour.*
- H226 *Flammable liquid and vapour.*
- H280 *Contains gas under pressure; may explode if heated.*
- H304 *May be fatal if swallowed and enters airways.*
- H315 *Causes skin irritation.*
- H319 *Causes serious eye irritation.*
- H336 *May cause drowsiness or dizziness.*
- H411 *Toxic to aquatic life with long lasting effects.*

· **Abbreviations and acronyms:**

- RID: *Règlement international concernant le transport des marchandises dangereuses par chemin de fer (Regulations Concerning the International Transport of Dangerous Goods by Rail)*
- ICAO: *International Civil Aviation Organisation*
- ADR: *Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)*
- IMDG: *International Maritime Code for Dangerous Goods*
- IATA: *International Air Transport Association*
- GHS: *Globally Harmonised System of Classification and Labelling of Chemicals*
- EINECS: *European Inventory of Existing Commercial Chemical Substances*
- ELINCS: *European List of Notified Chemical Substances*
- CAS: *Chemical Abstracts Service (division of the American Chemical Society)*
- LC50: *Lethal concentration, 50 percent*
- LD50: *Lethal dose, 50 percent*
- PBT: *Persistent, Bioaccumulative and Toxic*
- vPvB: *very Persistent and very Bioaccumulative*
- Flam. Gas 1: *Flammable gases – Category 1*
- Aerosol 1: *Aerosols – Category 1*
- Press. Gas C: *Gases under pressure – Compressed gas*
- Flam. Liq. 2: *Flammable liquids – Category 2*
- Flam. Liq. 3: *Flammable liquids – Category 3*
- Skin Irrit. 2: *Skin corrosion/irritation – Category 2*
- Eye Irrit. 2: *Serious eye damage/eye irritation – Category 2*
- STOT SE 3: *Specific target organ toxicity (single exposure) – Category 3*
- Asp. Tox. 1: *Aspiration hazard – Category 1*
- Aquatic Chronic 2: *Hazardous to the aquatic environment - long-term aquatic hazard – Category 2*

- *** Data compared to the previous version altered.**